




Relays & Contactors > Relay Accessories



Relay Socket Type: **DIN Rail Mount**
Body Material: **Nylon**
Product Mount Type: **Board Mount**
Pole Configuration: **4**
Relay Accessory Type: **Socket**

Features

Product Type Features

Relay Accessory Type	Socket
----------------------	--------

Body Features

Body Material	Nylon
---------------	-------

Contact Features

Contact Material	Spring Brass
Contact Plating Material	Tin
Terminal Style	Screw
Relay Socket Type	DIN Rail Mount
Pole Configuration	4

Termination Features

Number of Pins	14
Termination Post & Tail Length	69.96 mm[.212 in]

Mechanical Attachment

Product Mounting Feature Type	Mounting Hole
Product Mount Type	Board Mount



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 4-1393118-3 KUP-17A19-24=KU	 TE Part # 6-1393118-7 KUP-5D15-24=KU	 TE Part # 1-1423960-2 KUP-17D19F-110=RELAY,4C,AGCDO, GOLD FLASH	 TE Part # 6-1423960-9 KUP-17D19-48=RELAY,4C,AGCDO, QC.110,DUST
---	--	---	--





TE Part # 4-1393118-2
KUP-17A19-120=KU



TE Part # 5-1393118-9
KUP-5A15-120=KU



TE Part # 4-1393118-9
KUP-17D19-12=KU



TE Part # 3-1393159-9
20C254=SPRING,HOLD-DOWN,KUP,,0



TE Part # 5-1423996-5
KUP-17A39-120=RELAY,4C,AGCDO,
QC.110,LAMP



TE Part # 4-1393118-8
KUP-17D19-110=KU



TE Part # 6-1393118-0
KUP-5A15-24=KU



TE Part # 6-1393118-1
KUP-5A15-240=KU



TE Part # 5-1393118-0
KUP-17D19-24=KU




TE Part # 6-1393118-6
KUP-5D15-12=KU

Also in the Series | **Potter & Brumfield KUP**



AC Relays(31)




DC Relays(35)



Electromechanical Relays(66)



Plug-In Relays(66)



Relay Accessories(10)

Customers Also Bought



TE Part #1-1617128-5
JMSCD-26XPS = M39016/16-044P

TE Part #1589462-6
SSL005L2HN = SMT CONN

TE Part #YDTS26W15-19SAV001
PLUG ASSY

TE Part #7-1393117-8
KUP-14A15-120=KU-

TE Part #1617125-1
JMAW-12XL = M39016/9-016L

TE Part #CG3261-000
CI-FN10050

TE Part #2-1617119-9
J1MSCD-12XL = M39016/25-035L

TE Part #7-1393252-3
W67-X2Q13-5=M6/M7/M9/W6/W7

TE Part #749806-7
KIT,HDP-20,RCPT,SIZE 1, 9 POSN

TE Part #ER9170-000
55LF0144-26-MST4CS3536

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_2-1419106-2_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1419106-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1419106-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KU Sockets & Accessories

English

Product Specifications



Definitions General Purpose Relays

English

Agency Approvals

UL

English