


Geberit Mapress Stainless Steel T-piece with male thread



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For saturated steam ≤ 120 °C
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5
- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	R "	d1, ø mm	arc °	L cm	I cm	I1 cm	H cm	Z cm	Z1 cm
31401	12 / 10 / 12	15	3/8	15	90	6.4	3.2	3.2	5	1.2	1.2
31454	12 / 15 / 12	15	1/2	15	90	6.4	3.2	3.2	4	1.2	1.2
31455	15	18	1/2	18	90	6.8	3.4	3.4	4.2	1.4	1.4
31458	20	22	3/4	22	90	7.4	3.7	3.7	4.8	1.6	1.6

Art. no.	DN	d, ø mm	R "	d1, ø mm	arc °	L cm	I cm	I1 cm	H cm	Z cm	Z1 cm
31461	25	28	1	28	90	8.4	4.2	4.2	5.4	1.9	1.9
31464	32	35	1 1/4	35	90	10	5	5	6	2.4	2.4