

## LOCTITE® SI 5660™

February 2013

### PRODUCT DESCRIPTION

LOCTITE® SI 5660™ provides the following product characteristics:

<b>Technology</b>	Silicone
<b>Chemical Type</b>	Silicone
<b>Appearance (uncured)</b>	Grey paste, lump free <sup>LMS</sup>
<b>Components</b>	One component - requires no mixing
<b>Thixotropic</b>	Reduced migration of liquid product after application to substrate
<b>Cure</b>	Room temperature vulcanizing (RTV)
<b>Application</b>	Sealing
<b>Specific Benefit</b>	Non-corrosive

LOCTITE® SI 5660™ is a moisture curing silicone. The thixotropic nature of LOCTITE® SI 5660™ reduces the migration of liquid product after application to the substrate. It has been designed specially for gasketing applications where good resistance against oils and coolants is required. Typical applications include transmissions and cast metal housings.

### TYPICAL PROPERTIES OF UNCURED MATERIAL

Specific Gravity @ 25 °C 1.5

Extrusion Rate, g/min:

Pressure 0.62 MPa, time 15 seconds, temperature 25 °C:  
Semco Cartridge 200 to 700<sup>LMS</sup>

Flash Point - See MSDS

### TYPICAL CURING PERFORMANCE


#### Surface Cure

Tack Free Time is the time required to achieve a tack free surface

Tack Free Time, minutes:  
Cured @ 25 °C / 50±5 % RH ≤60<sup>LMS</sup>


### Cure Speed

The graph below shows the shear strength developed over time at 22 °C / 50 % RH on Grit Blasted Mild Steel (GBMS) and tested according to ISO 4587.



### Depth of Cure

The graph below shows the increase in depth of cure with time at 23 °C with increase in humidity.



### TYPICAL PROPERTIES OF CURED MATERIAL

Cured for 7 days @ 25 °C / 50% RH

#### Physical Properties:

Shore Hardness, ISO 868, Durometer A	45 to 75 <sup>LMS</sup>
Linear Shrinkage, %	1.13
Coefficient of Thermal Expansion, ISO 11359-2, K <sup>-1</sup>	245×10 <sup>-6</sup>
Coefficient of Thermal Conductivity ISO 8302, W/(m·K)	0.63
Tensile Strength, ISO 37	N/mm <sup>2</sup> 2.4 to 3.8 <sup>LMS</sup> (psi) (348 to 550)
Elongation, at break, ISO 37, %	≥100 <sup>LMS</sup>

**Electrical Properties:**

Surface Resistivity, IEC 60093, Ω 188×10<sup>15</sup>  
 Volume Resistivity, IEC 60093, Ω·cm 100×10<sup>12</sup>

**TYPICAL PERFORMANCE OF CURED MATERIAL**

**Adhesive Properties**

After 7 days @ 22 °C / 50% RH  
 Lap Shear Strength, ISO 4587:


Copper	N/mm <sup>2</sup>	0.7
	(psi)	(100)
Brass	N/mm <sup>2</sup>	0.6
	(psi)	(90)
Mild steel	N/mm <sup>2</sup>	1.8
	(psi)	(260)
Aluminum	N/mm <sup>2</sup>	0.4
	(psi)	(60)
Aluminum (grit blasted)	N/mm <sup>2</sup>	1.7
	(psi)	(245)
Stainless Steel	N/mm <sup>2</sup>	0.9
	(psi)	(130)
ABS	N/mm <sup>2</sup>	0.3
	(psi)	(44)
Nylon	N/mm <sup>2</sup>	0.2
	(psi)	(30)
Silicone	N/mm <sup>2</sup>	0.2
	(psi)	(30)
Phenolic	N/mm <sup>2</sup>	1.0
	(psi)	(145)
Zinc plated steel	N/mm <sup>2</sup>	1.6
	(psi)	(230)
Steel (e-coated)	N/mm <sup>2</sup>	2.0
	(psi)	(290)
Aluminum (Alclad)	N/mm <sup>2</sup>	0.7
	(psi)	(101)

**TYPICAL ENVIRONMENTAL RESISTANCE**

Cured for 7 days @ 25 °C / 50% RH  
 Lap Shear Strength, ISO 4587:  
 Aluminum (grit blasted)


**Hot Strength**

Tested at temperature



**Heat Aging**

Aged at temperature indicated and tested @ 22 °C



**Chemical/Solvent Resistance**

Aged under conditions indicated and tested @ 22 °C.

Environment	°C	% of initial strength			
		100 h	500 h	1000 h	5000 h
Water/glycol 50/50	120	45	55	50	30
Water/glycol 50/50	100	55	55	60	55
ATF	120	75	55	30	35
ATF	150	55	35	15	----
Mineral Oil	150	85	75	55	35
Motor oil (5W30 -Synthetic)	120	105	90	90	75
Motor oil (5W30 -Synthetic)	150	95	85	65	35
Water	60	75	65	65	65
Water	90	70	65	45	55

**GENERAL INFORMATION**

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Material Safety Data Sheet (MSDS).

NOTE: This product is not recommended for contact with gasoline.

**Directions for use:**

1. For best performance bond surfaces should be clean and free from grease.
2. Moisture curing begins immediately after the product is exposed to the atmosphere, therefore parts to be assembled should be mated within a few minutes after the product is dispensed.
3. The bond should be allowed to cure (e.g. seven days), before subjecting to heavy service loads.
4. Excess material can be easily wiped away with non-polar solvents.

**Loctite Material Specification<sup>LMS</sup>**

LMS dated April 02, 2011. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.

**Storage**

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

**Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties.**

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

**Conversions**

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$

$\text{kV/mm} \times 25.4 = \text{V/mil}$

$\text{mm} / 25.4 = \text{inches}$

$\mu\text{m} / 25.4 = \text{mil}$

$\text{N} \times 0.225 = \text{lb}$

$\text{N/mm} \times 5.71 = \text{lb/in}$

$\text{N/mm}^2 \times 145 = \text{psi}$

$\text{MPa} \times 145 = \text{psi}$

$\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$

$\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$

$\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$

$\text{mPa}\cdot\text{s} = \text{cP}$

**Note**

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

**Trademark usage**

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S.

Patent and Trademark Office.

Reference 0.2