



Product Data Sheet

P1019-P1020 Flat Fitting



P1019 / P1020 Test Results.

Part Number	Torque required	Torque achieved	Pass	Fail	Quantity Tested	Comment
P1019	28Nm	68Nm	PASS		1 Pair	No evidence of cracking, breakage, or any failure mode.
P1020	70Nm	140Nm	PASS		1 Pair	No evidence of cracking, breakage, or any failure mode.

Material:

P1019 / P1020 Mild Steel to BS EN 10149-2-S315MC or Asian spec. Q345 grade.
 P1019SS / P1020SS S/Steel BS EN 10088-2-1.4404+1D (S316L)

Finishes:

P1019/ P1020 Hot Dip Galvanized - Process in accordance with BS EN ISO 1461
 P1019SS/P1020SS S/Steel - Self Colour to BS EN 10088-2-1.4404+1D (S316L)

Part Weight:- 0.058 Kg

Box Weight:- 5.8Kg

No. Per Box:- 100