

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00	R	REV PER ECO-07-003704	21FEB07	KW DB
		R1	REVISED PER ECO-09-023313	12OCT09	KK AEG

YES	DIM A	NO. OF CIRCUITS	PART NO.
YES	71.12[2.800]	28	5-640620-8
YES	68.58[2.700]	27	5-640620-7
YES	66.04[2.600]	26	5-640620-6
YES	63.50[2.500]	25	5-640620-5
YES	60.96[2.400]	24	5-640620-4
YES	58.42[2.300]	23	5-640620-3
YES	55.88[2.200]	22	5-640620-2
YES	53.34[2.100]	21	5-640620-1
YES	50.80[2.000]	20	5-640620-0
YES	48.26[1.900]	19	4-640620-9
YES	45.72[1.800]	18	4-640620-8
YES	43.18[1.700]	17	4-640620-7
YES	40.64[1.600]	16	4-640620-6
YES	38.10[1.500]	15	4-640620-5
YES	35.56[1.400]	14	4-640620-4
YES	33.02[1.300]	13	4-640620-3
YES	30.48[1.200]	12	4-640620-2
YES	27.94[1.100]	11	4-640620-1
YES	25.40[1.000]	10	4-640620-0
YES	22.86[.900]	9	3-640620-9
YES	20.32[.800]	8	3-640620-8
YES	17.78[.700]	7	3-640620-7
YES	15.24[.600]	6	3-640620-6
YES	12.70[.500]	5	3-640620-5
YES	10.16[.400]	4	3-640620-4
YES	7.62[.300]	3	3-640620-3
YES	5.08[.200]	2	3-640620-2
NO	71.12[2.800]	28	2-640620-8
NO	68.58[2.700]	27	2-640620-7
NO	66.04[2.600]	26	2-640620-6
NO	63.50[2.500]	25	2-640620-5
NO	60.96[2.400]	24	2-640620-4
NO	58.42[2.300]	23	2-640620-3
NO	55.88[2.200]	22	2-640620-2
NO	53.34[2.100]	21	2-640620-1
NO	50.80[2.000]	20	2-640620-0
NO	48.26[1.900]	19	1-640620-9
NO	45.72[1.800]	18	1-640620-8
NO	43.18[1.700]	17	1-640620-7
NO	40.64[1.600]	16	1-640620-6
NO	38.10[1.500]	15	1-640620-5
NO	35.56[1.400]	14	1-640620-4
NO	33.02[1.300]	13	1-640620-3
NO	30.48[1.200]	12	1-640620-2
NO	27.94[1.100]	11	1-640620-1
NO	25.40[1.000]	10	1-640620-0
NO	22.86[.900]	9	640620-9
NO	20.32[.800]	8	640620-8
NO	17.78[.700]	7	640620-7
NO	15.24[.600]	6	640620-6
NO	12.70[.500]	5	640620-5
NO	10.16[.400]	4	640620-4
NO	7.62[.300]	3	640620-3
NO	5.08[.200]	2	640620-2
LEADFREE	DIM A	NO. OF CIRCUITS	PART NO.




SUPERSEDED

SUPERSEDED

SUPERSEDED

SUPERSEDED

SUPERSEDED



1 MATERIAL: CONNECTOR - NYLON UL94V-2 (RED).
 CONTACTS - 0.30[.012] THICK COPPER ALLOY
 BRIGHT TIN-LEAD .00203[.000080] MIN THICKNESS
 FOR 640620-2 THRU 2-640620-8.
 MATTE WHISKER MITIGATED TIN .00203[.000080] MIN THICKNESS OVER
 NICKEL UNDERPLATE FOR 3-640620-2 THRU 5-640620-8.

2. CONTACTS ACCEPT 22 AWG WIRE WITH 1.52[.060] MAX INSULATION DIAMETER.

3. CONTACTS MUST ACCEPT 0.64±0.03[.025] POST AND REMAIN LOCKED IN POSITION.

4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.

5. DIMENSIONS IN BRACKETS ARE IN INCHES.

6. HOUSING FEATURES ARE: FEED THRU WITH LOCKING RAMP.

7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 11JUN2003	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK D. BOSSI 11JUN2003	NAME MTA 100 CONNECTOR ASSEMBLY, 22 AWG, STANDARD	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BOSSI 11JUN2003	APPLICATION SPEC 108-1050	
0 PLC ±		DRAWING NO 114-1019		
1 PLC ±		CAGE CODE 00779		
2 PLC ±		SCALE 5:1		
3 PLC ± 0.13 [.005]		SHEET 1 OF 1		
4 PLC ±		REV R1		
ANGLES ±		CUSTOMER DRAWING		
FINISH		RESTRICTED TO		