# CRACKERJACKTM



The Crackerjack $^{\text{M}}$  is a stylish single lens spectacle that is lightweight with flat temples providing comfort for extended periods of use. Its design makes it a perfect fit for wearing in conjunction with helmets and ear defenders.

### WEIGHT 24g

#### **FEATURES**

- Ultra-enveloping.
- Lateral protection.
- Flat temples.





















1CRAK23C

1CRAK23Y Yellow

1CRAK230 Orange

1CRAK23S Smoke

1COV23W5 Welding 5

	Reference	Lens Markings	Frame Markings	Lens Treatment	Cor	nformity
$\bigcirc$	1CRAK23C	2C-1.2 > 1 FT CE	EN 166 FT CE	Anti-scratch/Anti-fog	EN 166 EN 170	
	1CRAK23Y	2-1.2 1 FT CE	EN 166 FT CE	Anti-scratch/Anti-fog	EN 166 EN 170	Conforms to EN 166: 2001
	1CRAK23O	2-1.4 1 FT CE	● EN 166 FT CE	Anti-scratch/Anti-fog	EN 166 EN 171	EC Type Examination
•	1CRAK23S	5-2.5 1 FT CE	● EN 166 FT CE	Anti-scratch/Anti-fog	EN 166 EN 172	Certificate Number 78797 issued by BSI
•	1CRAK23W5	5 <b>→</b> 1 FT CE	● EN 166 FT CE	Anti-scratch/Anti-fog	EN 166 EN 169	

For Lens & frames markings details, please refer to pages 7 to 9 in Swiss one catalogue. For Lens technologies and colors details please refer to pages 10 to 12 in Swiss one catalogue.

# CRACKERJACKTM



## DIMENSIONS OF SPECTACLE

Lens Thickness:	2.0mm
Lens Base:	10
Lens Size (Diagonal):	-
Bridge:	30mm
Temple Length (Lens to tip):	156mm
Overall Width:	135mm
Closest point between temple tips:	86.7mm



- 1 Polycarbonate2 Polycarbonate
- **3** Polycarbonate

## INSTRUCTIONS FOR USE

- In use ensure that the safety spectacles fit comfortably and securely on the head
- Ensure that the safety spectacles are in place, before entering the hazard area

#### **CLEANING & MAINTENANCE**

- The safety spectacles may be cleaned with soap and warm water and dried with a soft cloth
- Do not clean with chemical or abrasive cleaners
- The eye shield should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature

## LIMITATIONS OF USE

- Protection will only be offered if the safety spectacles are fitted correctly
- If the safety spectacles become scratched or damaged they should be replaced, likewise if the safety spectacles are subjected to severe impact they should be replaced immediately
- Do not apply paint, solvents, adhesives or self-adhesive labels, except in accordance with instructions from the manufacturer
- The safety spectacles, when in contact with the skin may cause allergic reactions to susceptible individuals. If this occurs leave the hazard area, remove the eye shield and seek medical advice
- The attention of users is also drawn to the dangers of modifying or removing any of the original component parts, other than as recommended by the manufacturer
- Crackerjack™ is not suitable for protection against dusts, liquids or molten metals

#### DIMENSIONS OF INNER PACKAGING

Quantity:	10	
Weight:	0.42kg	



#### DIMENSIONS OF OUTER PACKAGING

Quantity: (30 display boxes of 10 p)	300
Weight: (Approx.)	14kg



- H Height: 61.5cm
- L Length: 97cm
- W Width: 29.8cm

Reference	EAN barcode Unit	EAN barcode inner packaging	
1CRAK23C	7640139970169	5038428324021	
1CRAK23Y	7640139970183	5038428324090	
1CRAK23O	7640139970190	5038428324052	
1CRAK23S	7640139970176	5038428324069	
1CRAK23W5	7640139971326	5038428324083	
		· ·	

EAN barcode outer packaging	Country of origin
5038428287852	Malaysia
5038428287890	Malaysia
5038428287869	Malaysia
5038428287876	Malaysia
5038428287883	Malaysia