

## TruCheck 2, 10 - 260 lbf·ft



TruCheck™ 2 is a cost effective torque wrench checker that has been redesigned to incorporate improved features whilst maintaining ease of use.

The TruCheck™ 2 aims to cut the cost of purchasing a torque wrench checking system and remove the reservations over the complexity of using such equipment.

**Part number:** 43522

**EAN Bar Code:** 5060207566568

**NATO number:** -

**Accuracy:** -

**Operates between:**

10.00 - 260.00 lbf·ft



## TECHNICAL SPECIFICATIONS

- Weight: 2.6 Kg
- Accuracy:  $\pm 1\%$  torque reading accuracy
- Display: LCD Display
- Temp Range - Operating: 0°C to +50°C
- Temp Range - Storage: -20°C to +70°C
- Auto Reset Hold Time: 3 seconds
- Power Consumption: 0.5W
- Environment: IP 40
- Electromagnetic Compatibility (EMC) Directive: Designed to comply with EN 61326-1
- Requires two Hexagon Socket Head Cap Screws ISO 4762 - M10 - 12.9 to fix in position (not included)
- Supplied with a 1/2" female square drive

## FEATURES

- Allows torque tool performance to be monitored and tools kept in peak condition.
- Limited settable options. Ideal for non-expert users with click type torque wrenches
- Inbuilt Micro USB 2.0 port enables power from any USB power source
- If you order a UKAS accredited calibration certificate (available at extra cost) this certificate will be provided in place of the traceable calibration certificate
- Software can be updated remotely, without the need to return the product to Norbar
- Supplied with traceable calibration certificate in clockwise direction. A counter-clockwise calibration is available at additional cost

## DIMENSIONS & WEIGHT

**Tool Weight:** 6.50


**Packed Weight:** 7.50

**Dimensions:** 100 x 100 x 100

**Packed Length:** 620.00

**Packed Height:** 520.00

**Packed Width:** 270.00



---

NORBAR TORQUE TOOLS LTD. Wildmere Road, Banbury, Oxfordshire,  
OX16 3JU, United Kingdom  
Registered Office as above - Registered in England No. 380480 - VAT No.  
GB 119 1060 05

- Tel: + 44 (0) 1295 270333
- Enquiries: + 44 (0) 1295 753600
- After Sales : + 44 (0) 1295 753635
- Fax: + 44 (0) 1295 753609
- Email: [enquiry@norbar.com](mailto:enquiry@norbar.com)
- Repairs: [repairs@norbar.com](mailto:repairs@norbar.com)