




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Tin (Sn)**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Operating Voltage: **600 VDC**

Features

Product Type Features

Discrete Wire Type	Stranded
--------------------	----------

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Contact Orientation	Straight
Mating Pin Diameter	1 mm[.039 in]
Contact Mating Area Plating Material Thickness	.8 µm[31.49 µin]
Wire Contact Termination Area Plating Material Finish	Matte
Wire Contact Termination Area Plating Thickness	.8 µm[31.49 µin]
Barrel Type	Open
Contact Type	Socket
Contact Mating Area Plating Material	Tin (Sn)
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Phosphor Bronze



Contact Current Rating (Max)	7 A
Termination Features	
Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable
Mechanical Attachment	
Wire Insulation Support	Without
Dimensions	
Compatible Insulation Diameter Range	1.19 – 1.75 mm[.047 – .069 in]
Wire Size	.12 – .35 mm²
Usage Conditions	
Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
Operation/Application	
Circuit Application	Power
Industry Standards	
Compatible With Agency/Standards Products	CSA, UL
Packaging Features	
Packaging Quantity	1000
Packaging Method	Bag
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 1-172164-2 MINI UNIVERSAL M-N-L PLUG 1P	 TE Part # 172171-1 15 CIR UNIV M-N-L PLUG	 TE Part # 172166-1 3 CIR UNIV M-N-L PLUG	 TE Part # 90758-1 PROCrimp TL W/DIE MIN UNIV MNL
 TE Part # 1-172159-2 MINI UNIVERSAL M-N-L CAP 4P	 TE Part # 172162-1 12 CIR UNIV M-N-L CAP	 TE Part # 172343-1 MINI UNIVERSAL M-N-L HOUSING	 TE Part # 1-172169-2 MINI UNIVERSAL M-N-L PLUG 9P
 TE Part # 1-172158-2 MINI-U-M-N-L 3P CAP RED	 TE Part # 1-172336-2 UNIVERSAL MATE-N-LOK PLUG 2P	 TE Part # 1-172158-6 MINI-U-M-N-L 3P CAP BLUE	 TE Part # 1-172336-6 UNIVERSAL MATE-N-LOK PLUG 2P
 TE Part # 1-172330-9 UNIVERSAL MATE-N-LOK CAP 4P	 TE Part # 1-172157-6 2CIR MINI U-M-N-L CAP BLUE	 TE Part # 1-172332-9 MUMNL PM CAP 9P	 TE Part # 1-172159-9 MINI UNIVERSAL M-N-L CAP 4P





TE Part # 1-172165-6
2CIR MINI U-M-N-L PLUG BLUE



TE Part # 1-172169-9
9 POS TR MINI UNIV



TE Part # 172327-1
UNIV M-N-L HSG



TE Part # 172328-1
MINI UNIVERSAL MATE-N-LOK CAP HOUSING 2P

Also in the Series | Mini-Universal MATE-N-LOK



Connector Caps & Covers(2)



Connector Contacts(89)



Connector Hardware(4)




Connector Seals & Cavity Plugs(17)



Connector Strain Relief(2)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(93)



Rectangular Power Connectors(196)



Wire-to-Board Headers & Receptacles (93)


Customers Also Bought



TE Part #180599
SOLIS 8 WIRE PIN




TE Part #1-2351981-2
DYNAMIC D8000 REC HSG 2P



TE Part #3-966292-3
FER,WIRE,PL SLV,25.00/4,L16,BLACK, LP



TE Part #2-1393236-2
V23092-A1024-A202



TE Part #1473571-6
RITS.JUNCTION BOX 2D 6P P/M



TE Part #1-172157-2
2CIR MINI U-M-N-L CAP RED



TE Part #2-324061-5
TERMINAL,SOLIS R 8 8 HR



TE Part #170121-1
MATE-N-LOK SKT L.P.



TE Part #175217-3
DYNAMIC REC CONTACT M L/P



TE Part #2373747-5
DYNAMIC D8000 REC CONT SILVER

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170365-4_1_c-170365-4-1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170365-4_1_c-170365-4-1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170365-4_1_c-170365-4-1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Crimping of Mini-Universal MATE-N-LOK Contact

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

Mini-Universal MATE-N-LOK Connector

Japanese



[Agency Approvals](#)

[UL Report](#)

English