

FEATURES

- Swivel castor
- Plate mounting type
- Rubber tyres
- Braked swivel rotation brake included
- Light duty
- Includes top plate fitting
- Four fixing holes of 6mm
- Plain bore hub bearings
- Load capacity of 50kg
- Wheel diameter of 50mm
- Overall height of 72mm
- Wheel width of 18mm
- Fixing plate dimensions of 50mm x 50mm
- Fixing centres of 36mm x 36mm

RS PRO Braked Swivel Swivel Castor, 50kg Load Capacity, 50mm Wheel Diameter

RS Stock No.: 828-6293



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Swivel castors are incredibly versatile little gadgets to have. They can be attached to a wide variety of light-duty equipment to make them transportable. These 50 mm general-purpose swivel castors from RS PRO are able to rotate 360° for total mobility and can bear loads of up to 50 kg.

The castor comes with a rectangular fixing plate and four fixing holes for easy installation to your equipment. As the tyres are made from rubber, they won't scratch the floor. There's also a brake fitted to the castor for safety and manoeuvrability. The polypropylene (PP) hub provides added durability and allows you to use it both indoors and on softer outdoor terrain.

General Specifications

| Rotation | Braked Swivel |
|------------------|--|
| Weight Class | Light Duty |
| Load Capacity | 50kg |
| Tyre Material | Rubber |
| Hub Material | Polypropylene |
| Bracket Material | Pressed steel |
| Includes Brake | Yes |
| Features | Top Plate Fitting |
| Applications | General Purpose, offices, warehouses and other industrial environments |

Mechanical Specifications

| Mounting Type | Plate |
|------------------------|------------|
| Wheel Diameter | 50mm |
| Wheel / Tread Width | 18mm |
| Overall Height | 72mm |
| Number of Fixing Holes | 4 |
| Fixing Hole Size | 6mm |
| Hub Bearing Type | Plain Bore |



| Fixing Centres Specifications | | |
|-------------------------------|-------------|--|
| Fixing Centres | 36mm x 36mm | |
| Fixing Centres (Length) | 36mm | |
| Fixing Centres (Width) | 36mm | |

| Fixing Plate Specifications | | |
|-----------------------------|-------------|--|
| Fixing Plate Dimensions | 50mm x 50mm | |
| Fixing Plate Length | 50mm | |
| Fixing Plate Width | 50mm | |





| Specification | | |
|-------------------------|------------------------------|--|
| Application | General Purpose / Industrial | |
| Features | Ball Bearing Swivel Head | |
| Fixing Centres | 36x36mm | |
| Fixing Centres Length | 36mm | |
| Fixing Centres Width | 36mm | |
| Fixing Hole Size | 6mm | |
| Fixing Plate Dimensions | 50x50mm | |
| Fixing Plate Length | 50mm | |
| Fixing Plate Width | 50mm | |
| Hub Bearing Type | Plain | |
| Hub Material | Polypropylene | |
| Load Capacity | 50kg | |
| Number of Fixing Holes | 4 | |
| Overall Height | 72mm | |
| Rotation | Swivel | |
| Tyre Material | Grey Rubber Tyre | |
| Weight Class | Light Duty | |
| Wheel Diameter | 50mm | |
| Wheel Width | 18mm | |