

C080B4FM

Circuit breaker frame, ComPacT NS800LB,
200kA at 415VAC, 800A, 4P, fixed, manually
operated, without control unit



Main

| | |
|--|--|
| Range | ComPacT |
| Range of product | ComPacT NS630b...1600 new generation |
| Product or component type | Basic frame |
| Device application | Distribution |
| Number of poles | 4P |
| Neutral position | Left |
| [In] rated current | 800 A at 50 °C |
| [Ue] rated operational voltage | 690 V AC 50/60 Hz |
| Network type | AC |
| Network frequency | 50/60 Hz |
| Suitability for isolation | Yes conforming to EN/IEC 60947-2 |
| Utilisation category | Category A |
| [Icu] rated ultimate short-circuit breaking capacity | 200 KA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 200 KA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 200 KA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 100 KA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 75 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 |
| Performance level | LB 200 kA 415 V AC |
| Control type | Manually operated |
| Mounting mode | Fixed |

Complementary

| | |
|---|---|
| [Ui] rated insulation voltage | 800 V AC 50/60 Hz conforming to IEC 60947-2 |
| [Uimp] rated impulse withstand voltage | 8 kV conforming to IEC 60947-2 |
| [Ics] rated service short-circuit breaking capacity | 200 KA at 220/240 V AC 50/60 Hz conforming to EN 60947-2 200 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2 200 KA at 380/415 V AC 50/60 Hz conforming to EN 60947-2 100 KA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 75 kA at 660/690 V AC 50/60 Hz conforming to EN 60947-2 |
| [Icw] rated short-time withstand current | 19.2 kA 1 s conforming to IEC 60947-2 |
| Integral instant protection | 40 kA |
| Mechanical durability | 10000 cycles conforming to IEC 60947-2 |
| Electrical durability | 2000 Cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 3000 Cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 3000 Cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 4000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 |
| Power losses | 20 W |
| Mounting support | Backplate |
| Connection pitch | 70 mm |
| Protection type | Without protection |
| Height (H) | 327 mm |
| Width (W) | 280 mm |
| Depth (D) | 147 mm |

Environment

| | |
|---------------------------------------|------------------------------|
| Standards | IEC 60947-2 |
| Product certifications | IECEE CB Scheme |
| Pollution degree | 3 conforming to IEC 60947 |
| IP degree of protection | IP40 conforming to IEC 60529 |
| IK degree of protection | IK07 conforming to EN 50102 |
| Ambient air temperature for operation | -25...70 °C |
| Ambient air temperature for storage | -50...85 °C |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile |  End Of Life Information |