

Price\* : 21.51 GBP



### Main

Range of product	TeSys
Device short name	GS1AM
Product or component type	Auxiliary contact
Contact application	O and I position signalling
Contacts type and composition	2 C/O
Contact operation	Early-break
[Ith] conventional free air thermal current	16 A at 40 °C
[Ie] rated operational current	12 A at 24 V DC-13 2 A at 440 V AC-15 2 A at 48 V DC-13 3 A at 400/415 V AC-15 4 A at 230 V AC-15 5 A at 127 V AC-15 0.4 A at 220 V DC-13 0.6 A at 110 V DC-13

### Complementary

Mechanical durability	1000000 cycles
Electrical durability	30000 cycles on AC-15
Product compatibility	GS
[In] rated current	100 A 125 A 160 A 200 A 250 A 315 A 400 A 50 A 60 A 63 A
Fuse type	BS DIN NFC
Type of operating handle	Direct right side
Product weight	0.035 kg



## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0724 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

## GS1AM2 is replaced by the following group of products:

	<b>electrical auxiliaries GS1AM101</b> TeSys GS - auxiliary early-break contact - 1 N/C - front side - 32 A Qty 1
	<b>electrical auxiliaries GS1AM110</b> TeSys GS - auxiliary early-break contact - 1 N/O - 32 A Qty 1

Reason for Substitution: End of life | Substitution date: 30 December 2007