



## Laser Pointers

Laser pointers are optical pointers which can also be used from a distance. On the one hand, the presenter can be near to the participants, he can go up to them. On the other hand, he can draw their attention to concrete data shown on the projection screen, he can explain details and specify subjects.



### LP15

- Incl. key ring and snap hook
- Light colour: red
- Range: 50 m
- Wavelength: 640 – 660 nm
- Dimensions (metal housing): 60 x 10 mm
- Weight: 26 g (without batteries)
- Batteries: 3x LR-41 (not included)
- TÜV-/GS tested
- Colour: silver

003531 Qty 25 BC X



### "2in1" LP7

- Laser pointer + LED lamp (colour: white)
- Incl. key ring and snap hook
- Range: 50 m
- Wavelength: 640 – 660 nm
- Dimensions (metal housing): 60 x 10 mm
- Weight: 22 g (without batteries)
- Batteries: 4x LR-41 (not included)
- CE tested
- Colour: silver

003553 Qty 100 BC X



### LP11

- Light colour: green (much more brighter than red laser pointers)
- Range: 50 m
- Wavelength: 540 nm
- Dimensions (metal housing): 124 x 13,5 mm
- Weight: 160 g (without batteries)
- Batteries: 2x R1 N (not included)
- CE tested
- Colour: chromium

003534 Qty 50 BC X



### "2in1" LP14

- Laser pointer and ballpoint pen
- Range: 50 m
- Wavelength: 640 – 660 nm
- Dimensions (metal housing): 140 x 10 mm
- Weight: 34 g (without batteries)
- Batteries: 3x LR-41 (not included)
- TÜV/GS tested
- Colour: silver

003532 Qty 25 BC X




### "3in1" LP10


- Laser pointer, ball point pen and pointer (telescopically extendible)
- Range: 50 m
- Wavelength: 640 – 660 nm
- Dimensions (metal housing): 145 x 10 mm
- Weight: 39 g (without batteries)
- Batteries: 3x LR-41 (not included)
- CE tested
- Colour: silver


003558 Qty 50 BC X

		<p><b>"3in1" LP13</b></p> <ul style="list-style-type: none"> <li>- Laser pointer, ballpoint pen and PDA pen</li> <li>- Range: 50 m</li> <li>- Wavelength: 640 – 660 nm</li> <li>- Dimensions (metal housing): 145 x 10 mm</li> <li>- Weight: 30 g (without batteries)</li> <li>- Batteries: 3x LR-41 (not included)</li> <li>- TÜV-/GS tested</li> <li>- Colour: chromium</li> </ul>			
		<table border="1"> <tr> <td>003533</td> <td>Qty 25</td> <td>BC X</td> </tr> </table>	003533	Qty 25	BC X
003533	Qty 25	BC X			

	<p><b>"4in1" LP8</b></p> <ul style="list-style-type: none"> <li>- Laser pointer, LED lamp (colour: white), ballpoint pen and PDA pen</li> <li>- Range: 50 m</li> <li>- Wavelength: 640 - 660 nm</li> <li>- Dimensions (metal housing): 150 x 10 mm</li> <li>- Weight: 27 g (without batteries)</li> <li>- Batteries: 4x LR-41 (not included)</li> <li>- CE tested</li> <li>- Colour: chromium</li> </ul>				
		<table border="1"> <tr> <td>003554</td> <td>VE 50</td> <td>CB</td> </tr> </table>	003554	VE 50	CB
003554	VE 50	CB			

		<p><b>LP16/17/18</b></p> <ul style="list-style-type: none"> <li>- Light colour: red</li> <li>- Range: 50 m</li> <li>- Wavelength: 640 - 660 nm</li> </ul>								
		<table border="1"> <tr> <td></td> <td></td> <td>Qty 50</td> <td>BC X</td> </tr> <tr> <td>003516</td> <td>003517</td> <td></td> <td></td> </tr> </table>			Qty 50	BC X	003516	003517		
		Qty 50	BC X							
003516	003517									
		<p><b>LP16/LP17</b></p> <ul style="list-style-type: none"> <li>- Dimensions of metal housing: 97 x 13.5 mm</li> <li>- Weight: 35 g (without batteries)</li> <li>- For 2x LR1 batteries (not included in the delivery package)</li> </ul>								

	<p><b>LP18</b></p> <ul style="list-style-type: none"> <li>- Dimensions of metal housing: 126 x 13.5 mm</li> <li>- Weight: 40 g (without batteries)</li> <li>- For 2x AAA batteries (not included in the delivery package)</li> <li>- Colour: black</li> </ul>				
		<table border="1"> <tr> <td>003518</td> <td>Qty 50</td> <td>BC X</td> </tr> </table>	003518	Qty 50	BC X
003518	Qty 50	BC X			

	<p>Laser pointers are optical pointers. According to the EN 60825-1, the laser of these devices has to respect a radiant intensity of under 1 mW. This is always the case when it comes to Hama laser pointers. They are GS tested and are subject to regular quality tests. The radiation intensity is therefore certainly under the prescribed maximum permissible value.</p>
---	---