


## 20A Switches



### Description

This uniquely shaped range is easy to install, with coloured terminals, clear white terminal markings and is supplied in individual protective bags.

This wide range includes engraved, flex outlet and neon versions.

### Features

- unique slim profile with curved top and bottom edges
- concave rockers
- only one size 4mm screwdriver needed
- clear white markings
- colour coded terminals
- grey font engraving
- neon versions available
- neon leads enclosed
- 2 earth terminals
- terminals have large lead-ins
- 25 year guarantee

### Range

20A dual switch	S1218
20A dual switch, neon	S1218P
20A DP	S1390
20A DP 'Water Heater'	S1390WH
20A DP, neon	S1391
20A DP, neon 'Water Heater'	S1391WH
20A DP, front flex outlet	S1392
20A DP, neon & front flex outlet	S1393
20A DP, neon & front flex outlet 'Water Heater'	S1393WH

### Technical Specification

voltage rating	250Vac
current Rating	20A
contact gap	3mm

no user serviceable parts

### Back Boxes

minimum recommended depth

	flush 25mm	dry lining 35mm	surface 25mm
1q	DB162	DB2540	V1221

### Standards

- BS EN 60669-1 : 2000

### Terminal Capacity

	2.5mm <sup>2</sup>	4mm <sup>2</sup>	6mm <sup>2</sup>	10mm <sup>2</sup>
L & N	4	2	1	1

**DETA**

Kingsway House, Laporte Way  
Luton, Beds LU4 8RJ

Tel. +44 1582 544 500 Fax: +44 1582 544 501  
Technical Helpline +44 1582 544 548