

SPANNFIX VICES

with dissipative surface

BERNSTEIN clamping vices SPANNFIX constructed on ball-and-socket joints are rotatable easily in all directions and capable of being set securely with maximum working capacity by simple operation. A set screw below the ball socket allows an individual adjusting of the ball power. Long life is guaranteed by highest black powder-coated aluminium casting and surface-refined steel-parts. With a surface resistance between 10^7 and $10^9 \Omega$ the ESD types ensure a safe dissipation of static charges.

9-205 ESD  BERNSTEIN

SPANNFIX screw-on vice with dissipative surface

for work benches or laboratory tables with max. table thickness of 80 mm
 Technical data:
 Clamping pressure 150 kp
 Clamping capacity 70 mm
 Clamping depth 38 mm
 Jaw width 50 mm
 interchangeable plastic jaws from dissipative material - Art.-No. 9-206-50 ESD

Weight: 1.450 kg



9-205 ESD



9-251 ESD

9-251 ESD Universal clamp base with dissipative surface

with ball joint and threaded stud M 12 x 1.5, for work benches or laboratory tables with max. table thickness of 80 mm
 Weight: 0.950 kg

9-252 ESD Screw-on mounting vice with dissipative surface

Technical data: see 9-205 ESD
 Weight: 0.560 kg



9-252 ESD

9-253 ESD Circuit board holder

adjustable from 25 mm to 270 mm clamping capacity, correct setting by adjusting the centre position, firm clamping of the printed circuit by built-in resilience in the locating arms, height of locating arms 70 mm
 Weight: 0.280 kg



9-253 ESD

9-255 ESD Angular adapter with dissipative surface

to permit a larger turning circle when using 9-253
 Gewicht: 0.095 kg

9-256 Clamping lid for circuit boards with components

covered with 20 mm thick ESD foam
 Components of different sizes are pressed in such a way that soldering can be carried out correctly after the circuit board holder has been turned.
 Size of cover: 240 x 130 mm
 Use: in conjunction with circuit board holder 9-253
 Weight: 0.260 kg



9-256

9-257 ESD Rapid turning device with dissipative surface

with permanently connected angular adapter, permits swift rotation of the circuit board holder with the PCB and clamping lid through 180° .
 Weight: 0.270 kg



9-255 ESD



9-257 ESD