



EXPERIENCE TO PERFORM

## TECHNICAL DATA SHEET

# FULCRON DRAIN UNBLOCKER

### - **PRODUCT DESCRIPTION**

Chemical unblocker for toilets, washbasins, showers, and bidets. Based on concentrated sulfuric acid, it removes all types of organic and inorganic residues that could block the drain. It rapidly dissolves paper, cigarette butts, food remains, hair, soap residues etc... Quick and sure, it is not necessary to dismantle the pipes. The high specific weight formulation enables the product to penetrate through stagnant water and to act only on contact with the blockage.

### - **FIELDS OF USE**

It can be used in all kitchen and bathroom drains (toilet, washbasin, tub, shower, bidet).

### - **METHOD OF USE / DOSAGE**

Beware, the product is based on concentrated sodium hydroxide, carefully read the label before use. Carefully and slowly pour in a quarter of the bottle and wait 2 hours. For the toilet, pour in half a bottle and wait 3-4 hours. After the time required, run lukewarm water abundantly. For dry drains, slightly wet the pipes by running a little water. Take care during use, spurts may occur, work with the face slightly back. **DO NOT POUR WATER ON THE PRODUCT.** Do not mix with other products, hazardous gas may be created. Do not use on steel, aluminum, zinc and chrome. **DO NOT USE A PLUNGER.**

### - **TECHNICAL SPECIFICATIONS**

- |                          |   |
|--------------------------|---|
| • Appearance             | Pink liquid                                 |
| • Composition            | Pure sodium hydroxide, corrosion inhibitors |
| • Specific weight (g/ml) | 1.3 g/ml                                    |
| • pH (1% sol)            | 13-14                                       |
| • Solubility in water    | Complete, with strong exothermic reaction   |

### - **PACKAGING**

1-liter bottle in white PE

Code 2559

### - **STORAGE**

Store unopened and at room temperature away from direct sunlight and moisture.

In these conditions, the product lasts for at least 18 months.

### - **NOTES**

Highly corrosive product, handle with care.

Use the product as it is, do not mix with other substances or water.

For information on product safety, please consult the safety sheet.

T.S. 20.05.2021

The data contained herein are the result of technological research by our laboratories and are given for informative purposes only. We exclude any liability deriving from the incorrect choice or application of the product and from the lack of the necessary precautions, which should be carefully checked by the user. For information, please contact our Technical Dept. on no. +39 02924361

**AREXONS S.p.A. A SOCIO UNICO**  
Via Antica di Cassano, 23  
20063 Cernusco sul Naviglio (MI) Italy  
Capitale Sociale: €15.000.000,00 I.V.  
Registro delle Imprese di Milano n. 09728360968  
Codice Fiscale e Partita IVA 09728360968  
Direzione e coordinamento ex art. 2497 c.c. PLI (Netherlands) B.V.  
Centralino 02 92436.1  
Fax 02 92436.306  
[www.arexons.com](http://www.arexons.com)

A wholly-owned subsidiary of **PETRONAS**

Sistemi di gestione di qualità della società Arexons S.p.A.  
certificati ISO 9001 da LRQA.

Sistemi di gestione di ambiente e sicurezza della società Arexons S.p.A.  
certificati ISO 14001 e OHSAS 18001 da Bureau Veritas.

