

DATA SHEET

For a complete data sheet, please also download:

- The IC04 LOCMOS HE4000B Logic Family Specifications HEF, HEC
- The IC04 LOCMOS HE4000B Logic Package Outlines/Information HEF, HEC

HEF4541B **MSI** Programmable timer

Product specification
File under Integrated Circuits, IC04

January 1995

Programmable timer

HEF4541B
MSI

DESCRIPTION

The HEF4541B is a programmable timer which consists of a 16-stage binary counter, an integrated oscillator to be used with external timing components, an automatic power-on reset and output control logic. The frequency of the oscillator is determined by the external components R_T and C_T within the frequency range 1 Hz to 100 kHz. This oscillator may be replaced by an external clock signal at input RS, the timer advances on the positive-going transition of RS. A LOW on the auto reset input (AR) and a LOW on the master reset input (MR) enables the internal power-on reset. A HIGH level at input MR resets the counter independent on all other inputs. Resetting

disables the oscillator to provide no active power dissipation.

A HIGH at input $\overline{AR}$ turns off the power-on reset to provide a low quiescent power dissipation of the timer. The 16-stage counter divides the oscillator frequency by 2^8 , 2^{10} , 2^{13} or 2^{16} depending on the state of the address inputs (A_0 , A_1). The divided oscillator frequency is available at output O. The phase input (PH) features a complementary output signal. If the mode select input (MODE) is LOW or HIGH the timer can be used respectively as a single transition timer or 2^n frequency divider.




Fig.1 Functional diagram.




Fig.2 Pinning diagram.


HEF4541BP(N):	14-lead DIL; plastic (SOT27-1)
HEF4541BD(F):	14-lead DIL; ceramic (cerdip) (SOT73)
HEF4541BT(D):	14-lead SO; plastic (SOT108-1)
():	Package Designator North America

FAMILY DATA, I_{DD} LIMITS category MSI

See Family Specifications

Programmable timer

HEF4541B
MSI



7Z83070.2

Fig.3 Logic diagram.

Programmable timer

HEF4541B
MSI


PINNING

A ₀ , A ₁	address inputs
MODE	mode select input
$\overline{\text{AR}}$	auto reset input
MR	master reset input
PH	phase input
R _{TC}	external resistor connection (R _t)
C _{TC}	external capacitor connection (C _t)
RS	external resistor connection (R _S) or external clock input

FREQUENCY SELECTION TABLE

A ₀	A ₁	NUMBER OF COUNTER STAGES n	$\frac{f_{\text{osc}}}{f_{\text{out}}} = 2^n$
L	L	13	8 192
L	H	10	1 024
H	L	8	256
H	H	16	65 536

RC oscillator



FUNCTION TABLE

INPUTS				MODE
$\overline{\text{AR}}$	MR	PH	MODE	
H	L	X	X	auto reset disabled
L	L	X	X	auto reset enabled ⁽¹⁾
X	H	X	X	master reset active
X	L	X	H	normal operation selected
X	L	X	L	division to output
X	L	L	X	single-cycle mode ⁽²⁾
X	L	L	X	output initially LOW, after reset
X	L	H	X	output initially HIGH, after reset

Notes

- For correct power-on reset, the supply voltage should be above 8.5 V. For $V_{\text{DD}} < 8.5 \text{ V}$, disable the autoreset and connect $\overline{\text{AR}}$ to V_{DD} .
- The timer is initialized on a reset pulse and the output changes state after 2^{n-1} counts and remains in that state (latched). Reset of this latch is obtained by master reset or by a LOW to HIGH transition on the MODE input.

H = HIGH state (the more positive voltage)
L = LOW state (the less positive voltage)
X = state is immaterial

Timing component limitations

The oscillator frequency is mainly determined by $R_t C_t$, provided $R_t \ll R_S$ and $R_S C_2 \ll R_t C_t$. The function of R_S is to minimize the influence of the forward voltage across the input protection diodes on the frequency. The stray capacitance C_2 should be kept as small as possible. In consideration of accuracy, C_t must be larger than the inherent stray capacitance. R_t must be larger than the LOCMOS 'ON' resistance in series with it, which typically is 500 Ω at $V_{\text{DD}} = 5 \text{ V}$, 300 Ω at $V_{\text{DD}} = 10 \text{ V}$ and 200 Ω at $V_{\text{DD}} = 15 \text{ V}$.

The recommended values for these components to maintain agreement with the typical oscillation formula are:
 $C_t \geq 100 \text{ pF}$, up to any typical value,
 $10 \text{ k}\Omega \leq R_t \leq 1 \text{ M}\Omega$.

Programmable timer

HEF4541B
MSI




Fig.5 RC oscillator frequency as a function of R_t and C_t at $V_{DD} = 5$ to 15 V ; $T_{amb} = 25\text{ }^\circ\text{C}$.

Programmable timer


HEF4541B
MSI

Fig.6 Frequency deviation (Δf) as a function of ambient temperature; referenced at : f_{osc} at $T_{amb} = 25\text{ }^{\circ}\text{C}$ and $V_{DD} = 10\text{ V}$.

Programmable timer

HEF4541B
MSI

DC CHARACTERISTICS

 $V_{SS} = 0 \text{ V}$

	V_{DD} V	V_{OL} V	V_{OH} V	SYMBOL	$T_{amb} (^{\circ}\text{C})$					
					-40		+ 25		+ 85	
					MIN.	MAX.	MIN.	TYP.	MAX.	MIN. MAX.
Supply current	5			I_D	–	80	–	20	80	– 230 μA
power-on reset	10				–	750	–	250	600	– 700 μA
enabled (note)	15				–	1600	–	500	1300	– 1500 μA
Supply voltage for automatic reset initialization (note)				V_{DD}	–	–	8,5	5	–	– – V
Output current HIGH; C_{TC} , R_{TC}	5		4,6	$-I_{OH}$	0,5	–	0,4	–	–	0,3 – mA
	10		9,5		1,4	–	1,2	–	–	0,95 – mA
	15		13,5		4,8	–	4,0	–	–	3,2 – mA
	5		2,5	$-I_{OH}$	1,4	–	1,2	–	–	0,95 – mA
Output current LOW; C_{TC} , R_{TC}	5	0,4		I_{OL}	0,33	–	0,27	–	–	0,20 – mA
	10	0,5			1,00	–	0,85	–	–	0,68 – mA
	15	1,5			3,20	–	2,70	–	–	2,30 – mA

Note

- All inputs at 0 V or V_{DD} ; except input $\overline{AR}$ = input MR = 0 V (power-on reset active).

AC CHARACTERISTICS

 $V_{SS} = 0 \text{ V}$; $T_{amb} = 25 ^{\circ}\text{C}$; input transition times $\leq 20 \text{ ns}$

	V_{DD} V	TYPICAL FORMULA FOR P (μW) ⁽¹⁾			
Dynamic power dissipation per package (P)	5	1 300	$f_i + f_o C_L V_{DD}^2$		
	10	5 300	$f_i + f_o C_L V_{DD}^2$		
	15	12 000	$f_i + f_o C_L V_{DD}^2$		
Total power dissipation when using the on-chip oscillator (P)	5	1 300	$f_{osc} + f_o C_L V_{DD}^2$	$+ 2C_t V_{DD}^2 f_{osc}$	$+ 10 V_{DD}$
	10	5 300	$f_{osc} + f_o C_L V_{DD}^2$	$+ 2C_t V_{DD}^2 f_{osc}$	$+ 100 V_{DD}$
	15	12 000	$f_{osc} + f_o C_L V_{DD}^2$	$+ 2C_t V_{DD}^2 f_{osc}$	$+ 400 V_{DD}$

Notes

- where:

 f_i = input frequency (MHz) f_o = output frequency (MHz) C_L = load capacitance (pF) V_{DD} = supply voltage (V) C_t = timing capacitance (pF) f_{osc} = oscillator frequency (MHz)

Programmable timer

HEF4541B
MSI

AC CHARACTERISTICS

 $V_{SS} = 0\text{ V}$; $T_{amb} = 25\text{ }^{\circ}\text{C}$; $C_L = 50\text{ pF}$; input transition times $\leq 20\text{ ns}$

	V_{DD} V	SYMBOL	MIN.	TYP.	MAX.	TYPICAL EXTRAPOLATION FORMULA
Propagation delays RS $\rightarrow$ O						
2 ⁸ selected	5	t_{PHL} ; t_{PLH}		375	750 ns	348 ns + (0,55 ns/pF) C_L
HIGH to LOW	10			150	300 ns	139 ns + (0,23 ns/pF) C_L
LOW to HIGH	15			110	220 ns	102 ns + (0,16 ns/pF) C_L
RS $\rightarrow$ O						
2 ¹⁰ selected	5	t_{PHL} ; t_{PLH}		425	850 ns	398 ns + (0,55 ns/pF) C_L
HIGH to LOW	10			165	330 ns	154 ns + (0,23 ns/pF) C_L
LOW to HIGH	15			120	240 ns	112 ns + (0,16 ns/pF) C_L
RS $\rightarrow$ O						
2 ¹³ selected	5	t_{PHL} ; t_{PLH}		510	1020 ns	483 ns + (0,55 ns/pF) C_L
HIGH to LOW	10			190	380 ns	179 ns + (0,23 ns/pF) C_L
LOW to HIGH	15			135	270 ns	127 ns + (0,16 ns/pF) C_L
RS $\rightarrow$ O						
2 ¹⁶ selected	5	t_{PHL} ; t_{PLH}		575	1150 ns	548 ns + (0,55 ns/pF) C_L
HIGH to LOW	10			210	420 ns	199 ns + (0,23 ns/pF) C_L
LOW to HIGH	15			150	300 ns	142 ns + (0,16 ns/pF) C_L
Minimum clock pulse width; LOW	5	t_{WRSL}	60	30	ns	
	10		30	15	ns	
	15		24	12	ns	
Minimum reset pulse width; HIGH	5	t_{WMRH}	60	30	ns	
	10		30	15	ns	
	15		24	12	ns	
Maximum clock pulse frequency	5	f_{max}	8	16	MHz	
	10		15	30	MHz	
	15		18	36	MHz	
Oscillator frequency	5	f_{osc}		90	kHz	$R_t = 5\text{ k}\Omega$
	10			90	kHz	$C_t = 1\text{ nF}$
	15			90	kHz	$R_S = 10\text{ k}\Omega$
Oscillator frequency	5	f_{osc}		8	kHz	$R_t = 56\text{ k}\Omega$
	10			8	kHz	$C_t = 1\text{ nF}$
	15			8	kHz	$R_S = 120\text{ k}\Omega$


Package information

Package outlines

SO

SO14: plastic small outline package; 14 leads; body width 3.9 mm

SOT108-1



DIMENSIONS (inch dimensions are derived from the original mm dimensions)

UNIT	A max.	A ₁	A ₂	A ₃	b _p	c	D ⁽¹⁾	E ⁽¹⁾	e	H _E	L	L _p	Q	v	w	y	Z ⁽¹⁾	θ
mm	1.75	0.25 0.10	1.45 1.25	0.25	0.49 0.36	0.25 0.19	8.75 8.55	4.0 3.8	1.27	6.2 5.8	1.05	1.0 0.4	0.7 0.6	0.25	0.25	0.1	0.7 0.3	8° 0°
inches	0.069	0.010 0.004	0.057 0.049	0.01	0.019 0.014	0.0100 0.0075	0.35 0.34	0.16 0.15	0.050	0.244 0.228	0.041	0.039 0.016	0.028 0.024	0.01	0.01	0.004	0.028 0.012	

Note

1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	EIAJ			
SOT108-1	076E06S	MS-012AB				95-01-23 97-05-22


Package information

Package outlines

DIP

DIP14: plastic dual in-line package; 14 leads (300 mil)

SOT27-1



DIMENSIONS (inch dimensions are derived from the original mm dimensions)

UNIT	A max.	A ₁ min.	A ₂ max.	b	b ₁	c	D ⁽¹⁾	E ⁽¹⁾	e	e ₁	L	M _E	M _H	w	Z ⁽¹⁾ max.
mm	4.2	0.51	3.2	1.73 1.13	0.53 0.38	0.36 0.23	19.50 18.55	6.48 6.20	2.54	7.62	3.60 3.05	8.25 7.80	10.0 8.3	0.254	2.2
inches	0.17	0.020	0.13	0.068 0.044	0.021 0.015	0.014 0.009	0.77 0.73	0.26 0.24	0.10	0.30	0.14 0.12	0.32 0.31	0.39 0.33	0.01	0.087

Note

1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	EIAJ			
SOT27-1	050G04	MO-001AA				92-11-17 95-03-11