



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Cavity Plug**
Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**
Primary Product Color: **Black**
Primary Product Material: **PA GF**
Operating Temperature (Max): **120 °C [248 °F]**

Features

Product Type Features

Connector Seal & Plug Type	Cavity Plug
----------------------------	-------------

Body Features

Primary Product Color	Black
Primary Product Material	PA GF

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
Operating Temperature (Max)	120 °C[248 °F]

Packaging Features

Packaging Method	Bag
Packaging Quantity	6000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2141276-1
BLIND PLUG DIA 63,MQS CB, SHORT



TE Part # 1897634-2
ECU 94P PLUG ASS'Y

Customers Also Bought



TE Part #2379277-1
40POS,TH 025,REC HSG ASSY,UNSLD, COD A



TE Part #2299956-1
MCP 6.3MM 4P PLUG ASSY A



TE Part #2109258-4
MCON 1.2 CAVITY PLUG FOR 0.75MM




TE Part #1743059-2
MT-II/JPT SLD 36P PLUG ASSY






TE Part #2201289-1
1.0 SEALED RECEPTACLE CONTACT
SS-SIZE SN



TE Part #936780-2
MT-II/JPT SLD 20P CAP HSG



TE Part #2366531-2
0.64 SERIES,TERMINAL,025K S



TE Part #936471-1
040 III PLUG 16P ASSY NAT



TE Part #2209545-9
94P PLUG ASSY, NORMAL CODING



TE Part #2373974-2
025 14P JOINT CAP ASSY TYPE B

Documents

Product Drawings

SEALING PLUG CONTACT DUMMY(MQS)

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1897421-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1897421-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1897421-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English