

Manifold sub-base VABX-A-S-EL-E12-CTED-MPRJ45-SHUH-XL

Part number: 8208384

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	1 2
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Communication interface, plug pattern	00995789
Position of connection	On the side
Reverse polarity protection	Yes
Diagnostics via LED	Diagnostics per module
Diagnostics per internal communication	Logic supply undervoltage PS Logic supply overvoltage PS
Valve terminal structure	Valve sizes can be mixed
Max. number of valve coils	128
Compatible with	Valve terminal VTUX-A-S
Dimensions (W x L x H)	26 mm x 104 mm x 92 mm
Inductive protective circuit	Integrated
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 50 mA
Note regarding operating voltage	SELV/PELV fixed power supplies required Note the voltage drop
Power consumption at 24VDC	1.2 W
Max. power supply	2 x 4 A (external fuse required)
Nominal DC operating voltage, electronics/sensors	24 V
Nominal operating voltage DC of load	24 V
Power failure bridging	10 ms
Electrical isolation of outputs between channel - internal communication	Yes
Potential separation between the supply voltages electronics/sensor technology and load/valves	Yes
Protocol	CC-Link IE Field Basic EtherCAT® EtherNet/IP Modbus TCP PROFINET
Pollution degree	2
Permissible voltage fluctuations for electronics/sensors	±25%
Permissible voltage fluctuation of load	±10%
Power supply, function	Incoming electronics/sensors and load
Power supply, connection type	Plug

Feature	Value
power supply, connection system	Pin header, 5-pin
Power supply, number of pins/wires	5
Power supply, connection pattern	00997301
Undervoltage load/valves (diagnostic message)	≤21.1 V
Approval	RCM
KC mark	KC-EMV
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 70 °C
Relative air humidity	5 - 95%
Protection against direct and indirect contact	PELV Safety extra-low voltage
Degree of protection	IP20
Overvoltage category	II
Ambient temperature	-5 °C ... 50 °C
Nominal altitude of use	≤ 2000 m NHN
Max. installation height	3500 m
Max. tightening torque wall mounting	6 Nm
Product weight	227 g
Electrical control	AP interface
Max. cable length	100 M
Communication interface, function	System communication XF1 IN / XF2 OUT
Communication interface, connection type	2x socket
Communication interface, connection technology	RJ45
Communication interface, number of pins/cores	4
Communication interface, protocol	CC-Link IE Field Basic EtherCAT® EtherNet/IP Modbus TCP PROFINET
Communication interface, screened	Yes
Cable outlet	Straight
Mounting method for sub-base	With through-hole
Type of mounting	Via through-hole for M5 screw
Pneumatic connection, port 1	For 15 mm cartridge
Pneumatic connection, port 5	For 15 mm cartridge
Note on materials	RoHS compliant
Material sub-base	Reinforced PA
Material cover	Reinforced PA
Material seals	NBR
Material sleeve	High-alloy stainless steel
Material clip	High-alloy stainless steel
Material nut	High-alloy stainless steel