

A50.20.100 0...160°C L1=100x9mm copper alloy CL.2

Bimetallic thermometer TYP48-50

Item number: 12682013

Quantity: 1 pcs.

Order code: A50.20.100-H-C1K-100DMFRGD-1ZZZZZZZQI-ZZZ

2BZTM5003

Overview: A50.20.100 0...160°C L1=100x9mm copper alloy CL.2
Case material: steel, zinc plated
Pointer: aluminium, black Window: flat instrument glass detachable, with retainer screw; Mat.=Cu-alloy G1/2B
Dial background: white
WIKA
Data sheet: TM50.03

Details: Bimetallic thermometer TYP48-50
Model: A50 Standard version
Design: standard, steel case
Nominal size [NG, d1]: 100 mm
Case material: steel, zinc plated
Unit: °C
Scale range: 0 °C ... 160 °C
Insertion length L1: 100 mm
Stem diameter: 9 mm
Stem material: copper alloy
Thermowell: detachable, with retainer screw;
Thermowell material: Cu-alloy
Process connection: G 1/2 B
Manufacturer logo: *WIKA*
Pointer: aluminium, black
Window: flat instrument glass
Accuracy class: class 2 per EN 13190
Dial background: White
Data sheet: TM50.03