


The submersible pumps for clear water of the Flotec line have been designed to drain standing water and domestic waste water, empty and dry flooded rooms and draw water from wells, basins or cisterns. Models with a floating switch can even run automatically.

Flotec®




VIP



Typical features

- Asynchronous single-phase motor with built-in thermal relay
- Class F motor winding
- AISI 303 STAINLESS steel motor shaft
- Single-impeller hydraulic system in NORYL
- IP 68 Protection Class
- All models have a 10 m H05 RNF power cable and Schuko plug
- Colour lithographed package
- All models are available in the automatic version with floating switch
- Suitable for clear water with a maximum temperature of 40° C



MODEL	VIP 100/6 AUTO*	VIP 130/6 AUTO*	VIP 180/7 AUTO
Article	N1041150	N1041100	N1041120
Bar Code	8010583313017 €	8010583126044 €	8010583126068 €
Absorbed power	270 W	320 W	370 W
Head/Max. pressure	6 m / 0,6 bar	6 m / 0,6 bar	7 m / 0,7 bar
Max. Flow rate	6500 l/h	7800 l/h	10800 l/h
Pump Body	Polypropylene	Polypropylene	Polypropylene
Minimum draining level	20 mm (manual)	20 mm (manual)	20 mm (manual)
Max. size of impurities	6 mm	6 mm	6 mm
Pump outlet	Ø 1" 1/4 - M	Ø 1" 1/4 - M	Ø 1" 1/4 - M
Accessories supplied	Adjustable connector for threaded hoses Ø 13 19 e 25 mm	Adjustable connector for threaded hoses Ø 13 19 e 25 mm	Adjustable connector for threaded hoses Ø 13 19 e 25 mm
	€	€	