

FL SWITCH EP6416-HV - Industrial Ethernet Switch



1471544

<https://www.phoenixcontact.com/gb/products/1471544>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Managed switch with 16 SFP ports at 100/1000 Mbps, operating temperature: -40 °C ... +85 °C, 100 V AC/DC ... 240 V AC/DC (Nom.) power supply

Product description

Developed according to IEC 61850-3 (Ambient conditions)

Your advantages

- Network structure according to IEC 61850
- IEEE 1613
- Layer 2 and Layer 3 functions
- IEEE 1588 v2 precision timing support
- Support for Access Control Lists (ACL) for traffic filtering, RADIUS, and TACAC's authentication.

Commercial data

Item number	1471544
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNN512
Product key	DNN512
GTIN	4063151877323
Weight per piece (including packing)	2,632 g
Weight per piece (excluding packing)	2,006 g
Customs tariff number	85176200
Country of origin	CA

1471544

<https://www.phoenixcontact.com/gb/products/1471544>

Technical data

Dimensions

Width	82.7 mm
Height	188.39 mm
Depth	197.12 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Color	gray
Housing material	Metal

Mounting

Mounting type	DIN rail
Mounting type	DIN rail mounting

Interfaces

Ethernet

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100/1000 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)
No. of channels	16 (RJ45 ports)

Output data

Digital:

Output name	Alarm relay output: 24 V DC, 1 A maximum
-------------	--

Product properties

Product type	Switch
Product family	Managed Switch EP6000

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Switch functions

Signal contact control voltage	24 V DC
Signal contact control current	1 A

1471544

<https://www.phoenixcontact.com/gb/products/1471544>

MAC address table	16k
Status and diagnostic indicators	LEDs: POWER, ERROR, Link status

Electrical properties

Local diagnostics	Power Supply voltage Green LED
	Error Alarm signal LED red
	X1...X16 Link status Green LED
Maximum power dissipation for nominal condition	max. 50 W
Transmission medium	Copper

Supply

Supply voltage (AC/DC)	240 V AC/DC
Supply voltage range	100 V AC/DC ... 240 V AC/DC

Function

Signal contact control voltage	24 V DC
Signal contact control current	1 A

Connection data

Connection technology

Connection name	Power supply
-----------------	--------------

Power supply

Connection method	Screw connection
-------------------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (Type tested to 85 °C for 16 hours)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Standards and regulations

Standard designation	Ambient conditions
Standards/specifications	IEC 61850-3
	IEEE 1613

Approvals

Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

EMC data

Noise immunity	IEC 61850-3, IEEE 1613, EN 61000-6-2: 2005
----------------	--

FL SWITCH EP6416-HV - Industrial Ethernet Switch



1471544


<https://www.phoenixcontact.com/gb/products/1471544>

Signaling

Status display	LEDs: POWER, ERROR, Link status
----------------	---------------------------------

Drawings

Connection diagram



FL SWITCH EP6416-HV - Industrial Ethernet Switch



1471544

<https://www.phoenixcontact.com/gb/products/1471544>

Classifications

ECLASS

ECLASS-13.0	19170401
-------------	----------

ETIM

ETIM 9.0	EC000734
----------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I, 7(c)-II

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	1-Methyl-2-pyrrolidone (NMP)(CAS: 872-50-4)
	N,N-dimethylacetamide(CAS: 127-19-5)
	1, 2-dimethoxyethane; ethylene glycol dimethyl ether (EGDME)(CAS: 110-71-4)
	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead titanium zirconium oxide(CAS: 12626-81-2)
	Lead titanium trioxide(CAS: 12060-00-3)
	4,4'-isopropylidenediphenol(CAS: 80-05-7)
	Terphenyl, hydrogenated(CAS: 61788-32-7)
	Lead(CAS: 7439-92-1)
	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one(CAS: 71868-10-5)