

Biscuit Jointer LXT®

DPJ180

18V • 100 mm • 6 500 min⁻¹

Biscuit jointer for carpenters and furnishing fitters

A cordless biscuit jointer with a 100 mm blade and 20 mm bore for carpentry applications. A maximum bore depth of 20 mm. The tool is suitable for making biscuit joints in sheets and other wooden structures.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
No load speed	6500 min ⁻¹
Blade Diameter	100 mm
Max. Plunge Depth	20 mm
Plunge capacity	8 - 20 mm
Bore Size (Arbor Diameter)	22 mm
Kerf dimension	4 mm
Sound Pressure Level (L _{pA})	74 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	2,8 - 3,1 kg
Product Dimensions (L x W x H):	351 x 139 x 149 mm
Vibration Level, Cutting Grooves in MDF	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting Grooves in MDF	1,5 m/s ²

User benefits

- Depth adjustment
- Anti-restart function minimises accidental start-up
- The angle control can be locked in any position between 0 - 90° and has self-locking points at 0, 45, and 90 degrees.
- Electronic overload protection protects the user and the device
- Dust bag for a cleaner work environment
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

123150-5

Dust Bag



821551-8

Makpac case (3)



837648-3

MakPac (3) Inlay



B-20644

T.C.T saw blade 100 x 22 mm, 6 T



P-08838

Biscuit dowel Nr.0, 46 x 15 x 4 mm, 1



P-08844

Biscuit dowel Nr.10, 54 x 19,5 x 4



P-08850

Biscuit dowel Nr. 20, 56 x 23,5 x 4



Other

User manual

Parts drawing