


FEATURES

- Flame retardant
- High tensile strength
- Self-locking design
- Highly durable with excellent chemical resistance

RS PRO Steel Stainless Steel Roller Ball Cable Tie, 360mm x 4.6 mm

RS Stock No.: 123-5037



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO 304 grade stainless steel cable ties are an ideal alternative where Nylon 66 cable ties are not suitable such as harsh environments or places where there is heat. These cable ties have a roller ball design which is self-locking and fast and easy to install. Rollerball ties have a locking ball bearing which grips the tie strap and locks the tie as it is tensioned.

General Specifications

Type	Roller Ball
Colour	Steel
Material	Stainless Steel
Application	in industries such as Oil and gas Marine Chemical Maintenance Automotive Solar
Resistant To	High temperature, chemicals, weather and abrasion
UV Resistant	Yes
Minimum Operating Temperature	- 80 °C
Maximum Operating Temperature	+538 °C
Fire Behaviour	Halogen Free
Quantity	100

Mechanical Specifications

Length	360 mm
Width	4.6mm
Tensile Strength	1112N
Maximum Bundle Strength	100mm



Part No	Colour	Material	UL	Maximum Operating Temperature	Type
123-5034	Self Colour	304 Stainless Steel	UL	+538 °C	Roller Ball
123-5035	Self Colour	304 Stainless Steel	UL	+538 °C	Roller Ball
123-5036	Self Colour	304 Stainless Steel	UL	+538 °C	Roller Ball
123-5037	Self Colour	304 Stainless Steel	UL	+538 °C	Roller Ball

Part No	Maximum Bundle Diameter	Length		Pack Size	Operating Temperature Range	Tensile Strength(factory)
123-5034	50 mm	200 mm	4.6 mm	100	-80 to +538 °C	1112 N
123-5035	102 mm	360 mm	7.9 mm	50	-80 to +538 °C	1559 N
123-5036	25 mm	125 mm	4.6 mm	100	-80 to +538 °C	1112 N
123-5037	102 mm	360 mm	4.6 mm	100	-80 to +538 °C	1112 N