

# UCS CCD 5015 - Corner inlay

1056065

<https://www.phoenixcontact.com/gb/products/1056065>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Corner inlay for UCS housings with integrated screw boss; material: polyamide; color: sky blue, similar to RAL 5015



## Your advantages

- Flexible mounting options for the control cabinet and use in the field
- Can be adapted to suit the application, thanks to identical receptacles in the housing
- Different colors for high recognition value inside and outside the control cabinet

## Commercial data

Item number	1056065
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ACFCAZ
Product key	ACFCAZ
GTIN	4055626695006
Weight per piece (including packing)	13.18 g
Weight per piece (excluding packing)	11.08 g
Customs tariff number	84879090
Country of origin	DE

# UCS CCD 5015 - Corner inlay

1056065

<https://www.phoenixcontact.com/gb/products/1056065>



## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Select corner
Housing type	Universal housings
Housing series	UCS
Type	including flat screws and screws for PCB mounting
Ventilation openings present	no

### Dimensions

Width	16.2 mm
Height	16.2 mm
Depth	27.05 mm

### PCB design

PCB thickness	0.8 mm ... 3 mm
---------------	-----------------

### Material specifications

Color (Housing)	blue (RAL 5015)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Insulating material	PA
Housing material	PA
Surface characteristics	untreated
	galvanized

### Environmental and real-life conditions

#### Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	2g (58.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

#### Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

#### Thermal stability / ball thrust test

# UCS CCD 5015 - Corner inlay

1056065

<https://www.phoenixcontact.com/gb/products/1056065>



Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

## Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	50

## Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Half-sine
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

## Test for substances that would hinder coating with paint or varnish

Specification	VW PV 3.10.7:2005-02
Result	Test passed

## Degree of protection (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
Result, degree of protection, IP code	IP40

## Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

## PCB data

Number of PCB holders	1
Type of PCB mount	Bolt mounting
Thickness of the PCB	0.8 mm ... 3 mm
Note on PCB holders	This product is prepared for a printed-circuit board. Additional printed-circuit boards can be mounted using adhesive pads (accessories).

## Mounting

Mounting type	Screw mounting
Tightening torque / speed	Screw connection between housing halves: 1.2 - 1.4 Nm / 500 - 1000 rpm
	Mounting of PCB on corner feeder: 0.4 - 0.5 Nm / 500 - 1000 rpm

## Packaging specifications

# UCS CCD 5015 - Corner inlay

1056065

<https://www.phoenixcontact.com/gb/products/1056065>



Type of packaging	PE bag
-------------------	--------

# UCS CCD 5015 - Corner inlay

1056065

<https://www.phoenixcontact.com/gb/products/1056065>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1056065>



**UL Recognized**

Approval ID: E240868

# UCS CCD 5015 - Corner inlay



1056065

<https://www.phoenixcontact.com/gb/products/1056065>

## Classifications

### ECLASS

ECLASS-13.0	27190605
-------------	----------

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UCS CCD 5015 - Corner inlay

1056065

<https://www.phoenixcontact.com/gb/products/1056065>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)