




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 11

Terminal Block Connector Type: Plug

Connector System: Wire-to-Board

Centerline (Pitch): 5.08 mm [.2 in]

Number of Rows: 1

Features

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Stacking Configuration	Side Stackable
Stacked Levels	Without
Number of Positions	11
Number of Rows	1
Wire Entry Angle	90°
Wire Entry Location	Side

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features



Primary Product Color	Green
Product Orientation	Vertical

Contact Features

Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	15 A

Mechanical Attachment

Screw Plating Material	Nickel
Screw Material	Brass
Thread Size	M3

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Dimensions

Wire Size	30 – 12 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Box
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold:



Pb (3% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.





Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2342083-1 11POS HDR 90 DEG,HT,5.08MM PITCH,TL2.6MM	 TE Part # 1-796636-1 11POS 5.08MM CE VRT HDR,TRM BK	 TE Part # 1-282825-1 TERMI-BLOK HEADER,ASSY90 11P.5	 TE Part # 1-284053-1 11P TERMI-BLOK HDR 90,5.08MM
 TE Part # 1-2342084-1 11POS HDR ST, HT, 5.08MM PITCH, TL 2.6MM	 TE Part # 1-796638-1 11POS 5.08MM CE R/A HDR,TRM BK	 TE Part # 1-796639-1 11POS 5.08MM CE R/A HDR,TRM BK	 TE Part # 1-796637-1 11POS 5.08MM CE VRT HDR,TRM BK



TE Part # 1-282815-1
TERMI-BLOK HEADER,ASSY90 11P.

TE Part # 1-1546105-1
11 POS 5.08MM LH PLUG BLCK

TE Part # 1-284061-1
TERMI-BLOK HDR 90, 5,08MM P. M

Customers Also Bought

TE Part #2-1971845-4
4P, RAST 5 Tab Header, THV

TE Part #1744429-9
3.96 EP HDR ASSY 9P W/PEGS, GW

TE Part #2029265-4
4P VAL-U-LOK VRTHDR W/PGS GW

TE Part #1971845-2
2P, RAST 5 Tab Header, THV

TE Part #1744429-6
3.96 EP HDR ASSY 6P W/PEGS, GW

TE Part #2029181-5
5P VAL-U-LOK VRTHDR W/PGS GW

TE Part #2029181-3
3P VAL-U-LOK VRTHDR W/PGS GW

TE Part #1-2232511-4
4P, RAST 5 TAB HEADER, TH, VER, SEL

TE Part #2029265-8
8P VAL-U-LOK VRTHDR W/PGS GW

TE Part #2-1744435-8
EP 08P V-HDR ASY NO 3 PIN

Documents

Product Drawings
TERMINAL BLOCK VERTICAL PLUG S
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_1-284041-1_C1.3d_igs.zip



English

Customer View Model

[ENG_CVM_1-284041-1_C1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-284041-1_C1.2d_dxf.zip](#)

English

3D PDF

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-284041-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-284041-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-284041-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)

English

[BUCHANAN PCB TERMINAL BLOCKS](#)

English

[1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG](#)

English

Product Specifications

[Application Specification](#)

English