

ANTI-SEIZE PASTE #118-0573

Chemwatch Independent Material Safety Data Sheet
Issue Date: 20-Nov-2012
9317SP

CHEMWATCH 4834-91
Version No:5.1.1.1
CD 2012/4 Page 1 of 7

Section 1 - CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME

ANTI-SEIZE PASTE #118-0573

SYNONYMS

"Manufacturer's Code: 118-0573"

PRODUCT USE

Lubricant.

SUPPLIER

Company: RS Components Pty Ltd
Address:
Units 30 & 31, 761 Great South Road
Penrose
Auckland, 1006
New Zealand
Telephone: +64 9 526 1600
Fax: +64 9 579 1700

Company: RS Components Pty Ltd
Address:
25 Pavesi Street
Smithfield
NSW, 2164
Australia
Telephone: +1 300 656 636
Emergency Tel: 1800 039 008 (24 hours)
Emergency Tel: +61 3 9573 3112
Fax: +1 300 656 696

Section 2 - HAZARDS IDENTIFICATION

STATEMENT OF HAZARDOUS NATURE

NON-HAZARDOUS SUBSTANCE. NON-DANGEROUS GOODS. According to NOHSC Criteria, and ADG Code.

RISK

■ Repeated exposure may cause skin dryness and cracking.

SAFETY

•None under normal operating conditions.

Section 3 - COMPOSITION / INFORMATION ON INGREDIENTS

NAME	CAS RN	%
distillates, petroleum, light, hydrotreated	64742-47-8	10-30
copper	7440-50-8	10-30
propylene carbonate	108-32-7	1-5

Section 4 - FIRST AID MEASURES

SWALLOWED

- Immediately give a glass of water.
- First aid is not generally required. If in doubt, contact a Poisons Information Centre or a doctor.

EYE

- If this product comes in contact with eyes:
- Wash out immediately with water.
- If irritation continues, seek medical attention.
- Removal of contact lenses after an eye injury should only be undertaken by skilled personnel.

SKIN

- If skin or hair contact occurs:
- Flush skin and hair with running water (and soap if available).
- Seek medical attention in event of irritation.

INHALED

- If fumes, aerosols or combustion products are inhaled remove from contaminated area.
- Other measures are usually unnecessary.

continued...

ANTI-SEIZE PASTE #118-0573

Chemwatch Independent Material Safety Data Sheet
Issue Date: 20-Nov-2012
9317SP

CHEMWATCH 4834-91
Version No:5.1.1.1
CD 2012/4 Page 2 of 7
Section 4 - FIRST AID MEASURES

NOTES TO PHYSICIAN

- Treat symptomatically.

Section 5 - FIRE FIGHTING MEASURES

EXTINGUISHING MEDIA

- Foam.
- Dry chemical powder.
- BCF (where regulations permit).
- Carbon dioxide.

FIRE FIGHTING

- Alert Fire Brigade and tell them location and nature of hazard.
- Wear breathing apparatus plus protective gloves.
- Prevent, by any means available, spillage from entering drains or water courses.
- Use water delivered as a fine spray to control fire and cool adjacent area.

FIRE/EXPLOSION HAZARD

- Combustible.
- Slight fire hazard when exposed to heat or flame.
- Heating may cause expansion or decomposition leading to violent rupture of containers.
- On combustion, may emit toxic fumes of carbon monoxide (CO).

Combustion products include: carbon dioxide (CO₂), other pyrolysis products typical of burning organic material.
May emit poisonous fumes.

FIRE INCOMPATIBILITY

- Avoid contamination with oxidising agents i.e. nitrates, oxidising acids, chlorine bleaches, pool chlorine etc. as ignition may result.

HAZCHEM

None

Section 6 - ACCIDENTAL RELEASE MEASURES

MINOR SPILLS

- Clean up all spills immediately.
- Avoid contact with skin and eyes.
- Wear impervious gloves and safety goggles.
- Trowel up/scrape up.

MAJOR SPILLS

- Minor hazard.
- Clear area of personnel.
- Alert Fire Brigade and tell them location and nature of hazard.
- Control personal contact with the substance, by using protective equipment as required.
- Prevent spillage from entering drains or water ways.

Personal Protective Equipment advice is contained in Section 8 of the MSDS.

Section 7 - HANDLING AND STORAGE

PROCEDURE FOR HANDLING

- Containers, even those that have been emptied, may contain explosive vapours.
- Do NOT cut, drill, grind, weld or perform similar operations on or near containers.
- Electrostatic discharge may be generated during pumping - this may result in fire.
- Ensure electrical continuity by bonding and grounding (earthing) all equipment.
- Restrict line velocity during pumping in order to avoid generation of electrostatic discharge (≤ 1 m/sec until fill pipe submerged to twice its diameter, then ≤ 7 m/sec).
- Avoid splash filling.
- Avoid all personal contact, including inhalation.
- Wear protective clothing when risk of exposure occurs.
- Use in a well-ventilated area.
- Prevent concentration in hollows and sumps.

continued...

ANTI-SEIZE PASTE #118-0573

Chemwatch Independent Material Safety Data Sheet
Issue Date: 20-Nov-2012
9317SP

CHEMWATCH 4834-91
Version No:5.1.1.1
CD 2012/4 Page 3 of 7
Section 7 - HANDLING AND STORAGE

SUITABLE CONTAINER

- Metal can or drum
- Packaging as recommended by manufacturer.
- Check all containers are clearly labelled and free from leaks.

STORAGE INCOMPATIBILITY

- Avoid reaction with oxidising agents.
- Avoid strong acids, acid chlorides, acid anhydrides and chloroformates.

STORAGE REQUIREMENTS

- Store in original containers.
- Keep containers securely sealed.
- Store in a cool, dry, well-ventilated area.
- Store away from incompatible materials and foodstuff containers.

Section 8 - EXPOSURE CONTROLS / PERSONAL PROTECTION

EXPOSURE CONTROLS

Source	Material	TWA mg/m ³
Australia Exposure Standards	distillates, petroleum, light, hydrotreated (Oil mist, refined mineral)	5
Australia Exposure Standards	copper (Copper, dusts & mists (as Cu))	1
Australia Exposure Standards	copper (Copper (fume))	0.2
Australia Exposure Standards	copper (Inspirable dust (not otherwise classified))	10

The following materials had no OELs on our records

- propylene carbonate: CAS:108- 32- 7

MATERIAL DATA

ANTI-SEIZE PASTE #118-0573:

DISTILLATES, PETROLEUM, LIGHT, HYDROTREATED:

- for petroleum distillates:
CEL TWA: 500 ppm, 2000 mg/m³ (compare OSHA TWA)
(CEL = Chemwatch Exposure Limit).

ANTI-SEIZE PASTE #118-0573:

DISTILLATES, PETROLEUM, LIGHT, HYDROTREATED:

- for kerosene CAS 8008-20-6
TLV TWA: 100 mg/m³ as total hydrocarbon vapour Skin A3
OEL TWA: 14 ppm, 100 mg/m³ [NIOSH, 1985]
REL TWA: 150 ppm [Shell]
CEL TWA: 300 ppm, 900 mg/m³
(CEL = Chemwatch Exposure Limit).

DISTILLATES, PETROLEUM, LIGHT, HYDROTREATED:

■ Sensory irritants are chemicals that produce temporary and undesirable side-effects on the eyes, nose or throat. Historically occupational exposure standards for these irritants have been based on observation of workers' responses to various airborne concentrations.

PROPYLENE CARBONATE:

- for propylene oxide:
Odour threshold Level 35 ppm
Propylene oxide is a strong irritant of the eyes, mucous membranes and skin. High concentrations produce central nervous system depression.
Although propylene oxide is a rodent nasal carcinogen, no evidence for genetic damage or excess cancer risk could be detected in workers exposed at TWA concentrations of up to 20 ppm.
CEL STEL: 7 mg/m³ compare USSR

PERSONAL PROTECTION

RESPIRATOR

- Type A-P Filter of sufficient capacity. (AS/NZS 1716 & 1715, EN 143:2000 & 149:2001, ANSI Z88 or national equivalent)

continued...

ANTI-SEIZE PASTE #118-0573

Chemwatch Independent Material Safety Data Sheet

Issue Date: 20-Nov-2012

9317SP

CHEMWATCH 4834-91

Version No:5.1.1.1

CD 2012/4 Page 4 of 7

Section 8 - EXPOSURE CONTROLS / PERSONAL PROTECTION

EYE

- Safety glasses with side shields
- Chemical goggles.
- Contact lenses may pose a special hazard; soft contact lenses may absorb and concentrate irritants. A written policy document, describing the wearing of lens or restrictions on use, should be created for each workplace or task. This should include a review of lens absorption and adsorption for the class of chemicals in use and an account of injury experience. Medical and first-aid personnel should be trained in their removal and suitable equipment should be readily available. In the event of chemical exposure, begin eye irrigation immediately and remove contact lens as soon as practicable. Lens should be removed at the first signs of eye redness or irritation - lens should be removed in a clean environment only after workers have washed hands thoroughly. [CDC NIOSH Current Intelligence Bulletin 59], [AS/NZS 1336 or national equivalent].

HANDS/FEET

- Wear chemical protective gloves, e.g. PVC.
- Wear safety footwear or safety gumboots, e.g. Rubber.

OTHER

- Overalls.
- P.V.C. apron.
- Barrier cream.
- Skin cleansing cream.

ENGINEERING CONTROLS

■ Engineering controls are used to remove a hazard or place a barrier between the worker and the hazard. Well-designed engineering controls can be highly effective in protecting workers and will typically be independent of worker interactions to provide this high level of protection.

The basic types of engineering controls are:

Process controls which involve changing the way a job activity or process is done to reduce the risk.

Enclosure and/or isolation of emission source which keeps a selected hazard "physically" away from the worker and ventilation that strategically "adds" and "removes" air in the work environment.

Section 9 - PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE

Red brown odourless paste; insoluble in water.

PHYSICAL PROPERTIES

Does not mix with water.

Sinks in water.

State	Non Slump Paste	Molecular Weight	Not Applicable
Melting Range (°C)	1093	Viscosity	Not Available
Boiling Range (°C)	>250	Solubility in water (g/L)	Immiscible
Flash Point (°C)	230 (base oil)	pH (1% solution)	Not Applicable
Decomposition Temp (°C)	Not Available	pH (as supplied)	Not Applicable
Autoignition Temp (°C)	425 (base oil)	Vapour Pressure (kPa)	Not Available
Upper Explosive Limit (%)	Not Available	Specific Gravity (water=1)	1.12 @ 20C
Lower Explosive Limit (%)	Not Available	Relative Vapour Density (air=1)	Not Available
Volatile Component (%vol)	Not Available	Evaporation Rate	Not Available

Section 10 - STABILITY AND REACTIVITY

CONDITIONS CONTRIBUTING TO INSTABILITY

■ Product is considered stable and hazardous polymerisation will not occur.

For incompatible materials - refer to Section 7 - Handling and Storage.

Section 11 - TOXICOLOGICAL INFORMATION

POTENTIAL HEALTH EFFECTS

ACUTE HEALTH EFFECTS

continued...

ANTI-SEIZE PASTE #118-0573

Chemwatch Independent Material Safety Data Sheet

Issue Date: 20-Nov-2012

9317SP

CHEMWATCH 4834-91

Version No:5.1.1.1

CD 2012/4 Page 5 of 7

Section 11 - TOXICOLOGICAL INFORMATION

SWALLOWED

■ The material has NOT been classified by EC Directives or other classification systems as "harmful by ingestion". This is because of the lack of corroborating animal or human evidence. The material may still be damaging to the health of the individual, following ingestion, especially where pre-existing organ (eg. liver, kidney) damage is evident. Present definitions of harmful or toxic substances are generally based on doses producing mortality rather than those producing morbidity (disease, ill-health). Gastrointestinal tract discomfort may produce nausea and vomiting. In an occupational setting however, ingestion of insignificant quantities is not thought to be cause for concern.

EYE

■ Although the material is not thought to be an irritant (as classified by EC Directives), direct contact with the eye may produce transient discomfort characterised by tearing or conjunctival redness (as with windburn).

SKIN

■ Repeated exposure may cause skin cracking, flaking or drying following normal handling and use. Open cuts, abraded or irritated skin should not be exposed to this material. Entry into the blood-stream, through, for example, cuts, abrasions or lesions, may produce systemic injury with harmful effects. Examine the skin prior to the use of the material and ensure that any external damage is suitably protected.

INHALED

■ The material is not thought to produce adverse health effects or irritation of the respiratory tract (as classified by EC Directives using animal models). Nevertheless, good hygiene practice requires that exposure be kept to a minimum and that suitable control measures be used in an occupational setting.

CHRONIC HEALTH EFFECTS

■ Prolonged or repeated skin contact may cause drying with cracking, irritation and possible dermatitis following. Substance accumulation, in the human body, may occur and may cause some concern following repeated or long-term occupational exposure. Chronic solvent inhalation exposures may result in nervous system impairment and liver and blood changes. [PATTYS]. Constant or exposure over long periods to mixed hydrocarbons may produce stupor with dizziness, weakness and visual disturbance, weight loss and anaemia, and reduced liver and kidney function. Skin exposure may result in drying and cracking and redness of the skin. Chronic exposure to lighter hydrocarbons can cause nerve damage, peripheral neuropathy, bone marrow dysfunction and psychiatric disorders as well as damage the liver and kidneys.

TOXICITY AND IRRITATION

■ No significant acute toxicological data identified in literature search. Kerosene may produce varying ranges of skin irritation, and a reversible eye irritation (if eyes are washed). Skin may be cracked or flaky and/or leathery, with crusts and/or hair loss. It may worsen skin cancers. There may also be loss of weight, discharge from the nose, excessive tiredness, and wheezing. The individual may be pale. There may be increase in the weight of body organs. There was no evidence of harm to pregnancy.

SKIN

propylene carbonate	GESAMP/EHS Composite List - GESAMP Hazard Profiles	D1: skin irritation/corrosion	2
---------------------	--	-------------------------------	---

Section 12 - ECOLOGICAL INFORMATION

No data

Ecotoxicity

Ingredient	Persistence: Water/Soil	Persistence: Air	Bioaccumulation	Mobility
distillates, petroleum, light, hydrotreated	No Data Available	No Data Available	No Data Available	No Data Available
copper	No Data Available	No Data Available	LOW	No Data Available
propylene carbonate	HIGH	No Data Available	LOW	HIGH

Section 13 - DISPOSAL CONSIDERATIONS

- Recycle wherever possible or consult manufacturer for recycling options.
- Consult State Land Waste Authority for disposal.
- Bury or incinerate residue at an approved site.
- Recycle containers if possible, or dispose of in an authorised landfill.

continued...

ANTI-SEIZE PASTE #118-0573

Chemwatch Independent Material Safety Data Sheet

Issue Date: 20-Nov-2012

9317SP

CHEMWATCH 4834-91

Version No:5.1.1.1

CD 2012/4 Page 6 of 7

Section 14 - TRANSPORTATION INFORMATION

HAZCHEM:

None (ADG7)

NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS: ADG7, UN, IATA, IMDG

Section 15 - REGULATORY INFORMATION

POISONS SCHEDULE None

REGULATIONS

Regulations for ingredients

distillates, petroleum, light, hydrotreated (CAS: 64742-47-8) is found on the following regulatory lists;

"Australia Exposure Standards", "Australia Hazardous Substances", "Australia High Volume Industrial Chemical List (HVICL)", "Australia Inventory of Chemical Substances (AICS)", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Appendix E (Part 2)", "Australia Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP) - Schedule 5", "International Council of Chemical Associations (ICCA) - High Production Volume List", "International Fragrance Association (IFRA) Survey: Transparency List", "OECD List of High Production Volume (HPV) Chemicals", "OSPAR National List of Candidates for Substitution – Norway"

copper (CAS: 7440-50-8) is found on the following regulatory lists;

"Australia - Australian Capital Territory - Environment Protection Regulation: Ambient environmental standards (AQUA/1 to 6 - inorganic chemicals)", "Australia - Australian Capital Territory - Environment Protection Regulation: Ambient environmental standards (Domestic water supply - inorganic chemicals)", "Australia - Australian Capital Territory - Environment Protection Regulation: Ambient environmental standards (IRRIG - inorganic chemicals)", "Australia - Australian Capital Territory - Environment Protection Regulation: Ambient environmental standards (STOCK - inorganic chemicals)", "Australia - Australian Capital Territory - Environment Protection Regulation: Pollutants entering waterways taken to cause environmental harm - Domestic water supply quality", "Australia - Australian Capital Territory - Environment Protection Regulation: Pollutants entering waterways taken to cause environmental harm (Aquatic habitat)", "Australia - Australian Capital Territory - Environment Protection Regulation: Pollutants entering waterways taken to cause environmental harm (IRRIG)", "Australia - Australian Capital Territory - Environment Protection Regulation: Pollutants entering waterways taken to cause environmental harm (STOCK)", "Australia ADI list - Acceptable daily intakes for agricultural and veterinary chemicals", "Australia Drinking Water Guideline Values For Physical and Chemical Characteristics", "Australia Exposure Standards", "Australia Hazardous Substances", "Australia High Volume Industrial Chemical List (HVICL)", "Australia Inventory of Chemical Substances (AICS)", "Australia National Pollutant Inventory", "International Maritime Dangerous Goods Requirements (IMDG Code) - Marine Pollutants", "International Maritime Dangerous Goods Requirements (IMDG Code) - Substance Index", "OECD List of High Production Volume (HPV) Chemicals", "OSPAR National List of Candidates for Substitution – Norway", "United Nations Consolidated List of Products Whose Consumption and/or Sale Have Been Banned, Withdrawn, Severely Restricted or Not Approved by Governments", "WHO Guidelines for Drinking-water Quality - Guideline values for chemicals that are of health significance in drinking-water"

propylene carbonate (CAS: 108-32-7) is found on the following regulatory lists;

"Australia Hazardous Substances", "Australia Inventory of Chemical Substances (AICS)", "Australia National Pollutant Inventory", "GESAMP/EHS Composite List - GESAMP Hazard Profiles", "IMO IBC Code Chapter 17: Summary of minimum requirements", "IMO IBC Code Chapter 18: List of products to which the Code does not apply", "International Council of Chemical Associations (ICCA) - High Production Volume List", "OECD List of High Production Volume (HPV) Chemicals"

No data for Anti-Seize Paste #118-0573 (CW: 4834-91)

Section 16 - OTHER INFORMATION

■ Classification of the preparation and its individual components has drawn on official and authoritative sources as well as independent review by the Chemwatch Classification committee using available literature references.

A list of reference resources used to assist the committee may be found at:

www.chemwatch.net/references.

■ The (M)SDS is a Hazard Communication tool and should be used to assist in the Risk Assessment. Many factors determine whether the reported Hazards are Risks in the workplace or other settings.

This document is copyright. Apart from any fair dealing for the purposes of private study, research, review or criticism, as permitted under the Copyright Act, no part may be reproduced by any process without written permission from CHEMWATCH. TEL (+61 3) 9572 4700.

Issue Date: 20-Nov-2012

Print Date: 22-Nov-2012

continued...

ANTI-SEIZE PASTE #118-0573

Chemwatch Independent Material Safety Data Sheet

Issue Date: 20-Nov-2012

9317SP

CHEMWATCH 4834-91

Version No:5.1.1.1

CD 2012/4 Page 7 of 7

Section 16 - OTHER INFORMATION

This is the end of the MSDS.