

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,1996 .

© COPYRIGHT 1996






BY AMP INCORPORATED,ALL RIGHTS RESERVED.

LOC
J

DIST


REVISIONS

REV	P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
0			RELEASED	FJ00-4343-96	4/JUL/96	K.I.Y.	I
A			REVISED	FJ00-0096-97	3/FEB/97	K.I.Y.	I
B			REVISED	FJD0-0025-03	21/FEB/03	T.S.S.M	
C			REVISED	FJD0-0039-03	6/2/03	T.S.S.M	



NOTES

1. MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC ,POLYESTER(94V-0),COLOR:BLACK
TAB CONTACT:COPPER ALLOY
RETENTION LEG:BRASS
2. FINISH(CONTACT AREA):0.38 μ mMIN GOLD PLATING OVER Ni PLATING
3. FINISH(CONTACT AREA):0.76 μ mMIN GOLD PLATING OVER Ni PLATING
4. FINISH(RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL



推奨基板取付け寸法 (公差:±0.05)

PC 基板厚:1.6~2.4±0.1
(コネクタ搭載面)PC 基板厚:3.2±0.1
6-353080-2 ONLY


RECOMENDED PC BOARD HOLE PATTERN(TOL:±0.05)

PC BOARD THICKNESS:1.6~2.4±0.1
(CONNECTOR MOUNT SIDE)PC BOARD THICKNESS:3.2±0.1
6-353080-2 ONLY

注記

1. 材料:ハウジング: ガラス入り熱可塑性
ポリエステル樹脂 (94V-0),色: 黒
タブ コンタクト: 銅合金
リテンション レグ: 黄銅
2. めっき: コンタクト: 全面Ni下地
接触部: 0.38 μ m MIN金めっき
3. めっき: コンタクト: 全面Ni下地
接触部: 0.76 μ m MIN金めっき
4. めっき: リテンションレグとコンタクト半田付部
: ニッケル下地の上にスズめっき

Y	4	3	2-353080-3
	4	2	2-353080-2
X	4	3	1-353080-3
	4	2	6-353080-2
	4	2	1-353080-2
KEY TYPE	コンタクトのめっき (FINISH)		製品番号 (PART NO.)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS:
単位 寸
mmMATERIAL
材料注記参照
SEE NOTETOLERANCES UNLESS
OTHERWISE SPECIFIED

一般公差

1 ϕ : ±0.3

3 ϕ : >10 : ±0.35

10 ϕ : >30 : ±0.4

ANGLE : ±3°

FINISH
仕上注記参照
SEE NOTEDWN
K.IKEDA 4/JUL/'96CHK
Y.ISHIKAWA 4/JUL/'96APVD
S.MANABE 4/JUL/'96

PRODUCT SPEC

製品規格

108-5453

APPLICATION SPEC

取付適用規格

114-5246

WEIGHT

CUSTOMER DRAWING

WIRE RANGE
絶合電線断面積INSULATION DIA
絶縁外径tyco
ElectronicsTyco Electronics AMP K.K.
Kawasaki, Japan

NAME

名称

1列 ヘッダーアセンブリ 2P

(垂直 タイプ)

SINGLE ROW HEADER ASS'Y 2P("V"TYPE)

<DYNAMIC D-5200 S>

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=353080

SCALE

1-1

SHEET

1 OF 1

REV

C