

# Housing - HC-B 10-SFQD-52/M1PG16 - 1771406


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Box mounting base, for double locking latch, height 52 mm, with screw connection, 1x Pg16, with protective covers



## Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 036133
Weight per Piece (excluding packing)	258.3 g
Custom tariff number	85389099
Country of origin	Germany

## Technical data

### Dimensions

Height	52 mm
Width	52 mm
Length	93 mm
Wrench size, union nut	22 mm
External cable diameter	7.5 mm ... 15 mm

### Ambient conditions

Degree of protection of housing (IP)	IP65 (When plugged in)
Ambient temperature (operation)	-40 °C ... 125 °C

### General

Note	For contact inserts HC-B10, BB18, DD42, M, K8/24
Type	B10
Housing type	Box mounting bases
Locking type	For double locking latch
No. of cable outlets	1
Cable exit	Left (view of the opened protective cover)
Screw connection	with

# Housing - HC-B 10-SFQD-52/M1PG16 - 1771406

## Technical data

### General

Type of the screw connection	1x Pg16
Protective cover	Yes
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Cable gland material	Nickel-plated brass
Cable seal material	NBR
Material, protective cover	Polyamide

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

EAC

---

# Housing - HC-B 10-SFQD-52/M1PG16 - 1771406

## Approvals

Ex Approvals

---

Approvals submitted

---

Approval details

EAC
-----

## Drawings

Dimensional drawing

