



Part Number : 346960100

Product Description : Stac64 Single Bay Right-Angle Power Header, 10 Circuits, Polarization A, Black, Tray

Series Number : 34696

Status : Active

Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[346960100_sd.pdf](#)

[PK-31300-892-000.pdf](#)

3D Models and Design Files

[346960100_stp.zip](#)

Specifications

[347290200-AS-CH-000.pdf](#)

[AS-34729-020-001.pdf](#)

[PS-31372-100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	34696
Description	Stac64 Single Bay Right-Angle Power Header, 10 Circuits, Polarization A, Black, Tray
Application	Automotive, Power, Wire-to-Board
Comments	Polarization A
Component Type	PCB Header
Product Name	Stac64
UPC	800756894454

Electrical

Current - Maximum per Contact	18.0A, 30.0A
Voltage - Maximum	500V

Physical

Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No

Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	High Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	10.300/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
PC Tail Length	3.36mm
Pitch - Mating Interface	2.54mm, 5.25mm
Pitch - Termination Interface	2.54mm, 5.25mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Temperature Range - Operating	-40° to +100°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	WAVE
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number

This document was generated on Jul 09, 2025