

ENGLISH

Datasheet

Stock No: 476-797

RS Pro SPDT PCB Mount Non-Latching Relay Through Hole, 6V dc



Product Details

Low Profile Relays

Low profile: 15.7mm max height

8 and 16A versions have 5mm pinning, 12A has 3.5mm pinning

5kV dielectric strength (between coil and contacts)

Surge voltage up to 10kV (between coil and contacts)

Wash tight

Creepage distance 10mm

Conforms to VDE 0435/ 0631/ 0700

Approvals

UL (File no. E134517), VDE (File no. 116934), CQC (File no. CQC02001001951)

Standards

IEC 60335-1



ENGLISH

Specifications:

| Coil Voltage | 6V dc |
|-------------------------------|--------------------|
| Contact Configuration | SPDT |
| Mounting Type | PCB |
| Terminal Type | Through Hole |
| Coil Resistance | 90 Ω |
| Application | Power |
| Length | 29mm |
| Depth | 12.7mm |
| Height | 15.7mm |
| Dimensions | 29 x 12.7 x 15.7mm |
| Contact Material | Silver Tin Oxide |
| Maximum Switching Power AC | 4 kVA |
| Maximum Operating Temperature | +85°C |
| Minimum Operating Temperature | -40°C |
| Operating Temperature Range | -40 → +85°C |