

# Product datasheet

Specifications



## SmartX Controller I/O Module, 8 Analog Voltage/Current Outputs With Hand Control/Override Switches

SXWAOV8HX10001

EAN Code: 7332552009648

### Main

Flame retardance	UL94V0-5VB
Width	90 mm
Product certifications	ICES-003 FCC part 15 class B CE RCM
Net weight	156 g
Product or component type	I/O module
Device short name	AO-8-V-H
Height	114 mm
Ambient air temperature for storage	-20...70 °C
Depth	64 mm
Ambient air temperature for operation	0...50 °C
IP degree of protection	IP20
Power consumption in W	0.7 W
Relative humidity	0...95 % non-condensing
Number of outputs	8 analog output
[Us] rated supply voltage	24 V DC
Product name	I/O Modules
Product brand	Schneider Electric
Range	EcoStruxure Building Operation

### Complementary

Mounting support	DIN rail Wall
Electrical connection	Plug-in sub-base
Control type	With integrated switch for off/on/automatic
Analogue input type	Configurable voltage 0...10 V input voltage
Range compatibility	EcoStruxure Building Operation TB-IO-W1 terminal base
Standards	UL 864 UL 916 FCC CFR47 part 15
Material	ABS + PC

## Packing Units

---

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.2 cm
Package 1 Width	9 cm
Package 1 Length	5.8 cm
Package 1 Weight	180 g

---

## Logistical informations

---

Country of origin	SE
-------------------	----

---

## Contractual warranty

---

Warranty (in months)	18
----------------------	----

---



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	32 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	6 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	25 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.5 kg CO2 eq.

## Use Better



### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
SCIP Number	08bd611f-8419-43db-ad4e-34d847346717
Halogen-free status	Halogen free plastic parts & cables product
PVC free	Yes

## Use Longer



### Lifetime extension

Repair	No
--------	----

## Use Again



### Repack and remanufacture

Recyclability potential, in %	0
End of life manual availability	<a href="#">End of Life Information</a>
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins