


## FEATURES

- **High Chemical Resistance:** Suitable for use with a wide range of chemicals, enhancing versatility.
- **Temperature Range:** Operates effectively from -20 °C to 140 °C, making it suitable for various environments.
- **Durable Material:** Constructed from Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton for enhanced longevity.
- **Standard Compliance:** Meets BS ISO 3601-1, AS 568, and other key standards for quality assurance.
- **Precision Fit:** Inside diameter of 66.04 mm and outside diameter of 76.7 mm ensure a precise fit.

## RS PRO 66.04 mm Black O-Ring Seal

RS Stock No: 731-385



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in a variety of industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton, it offers excellent resistance to chemicals and high temperatures. Ideal for use in environments where durability and performance are critical, this O-Ring Seal ensures a secure fit and long-lasting service.

## General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

## Mechanical Specifications

Inside Diameter	66.04 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	76.7 mm
Thickness	5.33 mm

## Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

## Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

