


## FEATURES

- **High hardness (Shore A 90 to 95):** Provides excellent durability and wear resistance
- **Wide temperature range (-20 °C to 140 °C):** Suitable for use in extreme conditions
- **Chemical resistance:** Withstands exposure to harsh chemicals, enhancing longevity
- **Precision dimensions (75.57 mm ID, 86.23 mm OD):** Ensures a perfect fit for reliable sealing
- **Compliant with standards:** Meets BS ISO 3601-1, AS 568, and other key standards for quality assurance

## RS PRO 75.57 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-389



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO O-Ring Seal is designed to provide reliable sealing solutions in various industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton, it offers excellent resistance to chemicals and extreme temperatures. Ideal for use in demanding environments, this O-Ring ensures optimal performance and longevity.

## General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

## Mechanical Specifications

Inside Diameter	75.57 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	86.23 mm
Thickness	5.33 mm

## Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

## Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

