




All Nylon Gold Plated Receptacle: 2.54 mm, no Mating Alignment (89)

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                            |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                   |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




## Customers Also Bought



TE Part #640550-2  
02P MTA100 COVER



TE Part #3-647001-2  
02P MTA100 PSTD CONN ASSY SN




TE Part #NB18844001  
RNF-100-1/16-RD-SP




TE Part #3-641191-2  
02P MTA100 CONN ASSY WHT LF




TE Part #86-500G-R  
500 PSIG RIBBON CABLE MV  
PRESSURE SENSOR



TE Part #CAT-104MTA-NGPMR  
Nylon Gold Plated Receptacle: 2.54  
mm, with Mating Alignment, MTA 100



TE Part #643067-8  
08P MTA156 MOLDED COVER



TE Part #643077-2  
02P MTA100 MOLDED COVER F/T

## Documents

### Product Drawings

12P MTA100 CONN ASSY GRN 15AU

English

### CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-641193-2\_Z\_c-1-641193-2-z.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-641193-2\_Z\_c-1-641193-2-z.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-641193-2\_Z\_c-1-641193-2-z.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

Product Specification

English

### Agency Approvals

Agency Approval Document

English

1-641193-2

12P MTA100 CONN ASSY GRN 15AU

