



**Part Number :** [1725018002](#)  
**Product Description :** zSFP+ Stacked Ganged Assembly with Metal Spring Fingers, 2-by-8, with Enhanced Airflow, 320 Circuits  
**Series Number :** 172501  
**Status :** Active  
**Product Category :** High-Speed I/O Connectors



Documents & Resources

Drawings


- [1725018002 sd.pdf](#)
- [EE-170071-0001-001.pdf](#)
- [SP-170426-1000-001.zip](#)

Specifications

- [PS-170071-0001-001.pdf](#)
- [TS-170071-0001-001.pdf](#)

Product Environment Compliance

Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Compliant with Exemption 44; 34; 33   |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)4165-DC (25 June 2025)   |
| EU RoHS            | Compliant per EU 2015/863   |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|                |  |
|----------------|--|
| Status         | Active   |
| Category       | High-Speed I/O Connectors  |
| Series         | 172501   |
| Description    | zSFP+ Stacked Ganged Assembly with Metal Spring Fingers, 2-by-8, with Enhanced Airflow, 320 Circuits |
| Application    | Module-to-Board  |
| Component Type | Receptacle   |
| Product Name   | zSFP Plus,zSFP+  |
| Type           | Pluggable  |
| UPC            | 889056079679   |

### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

### Electrical

|                               |                 |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.5A            |
| Data Rate                     | 28.0 Gbps       |
| Shielded                      | Yes             |
| Shield Type                   | EMI Fingers     |
| Voltage - Maximum             | 30V AC (RMS)/DC |

### Physical

|                                |                                |
|--------------------------------|--------------------------------|
| Circuits (Loaded)              | 320                            |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 100                            |
| Flammability                   | 94V-0                          |
| Gender                         | Female                         |
| Lock to Mating Part            | Yes                            |
| Material - Metal               | High Performance Alloy (HPA)   |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Matte Tin                      |
| Material - Resin               | High Performance Thermoplastic |
| Net Weight                     | 153.860/g                      |
| Number of Rows                 | 2                              |
| Orientation                    | Right Angle                    |
| Packaging Type                 | Tray                           |
| Panel Mount                    | No                             |
| PCB Locator                    | Yes                            |
| PCB Retention                  | Yes                            |
| PCB Thickness - Recommended    | 1.57mm                         |
| PC Tail Length                 | 1.70mm                         |
| Pitch - Mating Interface       | 0.80mm                         |
| Pitch - Termination Interface  | 0.80mm                         |
| Plating min - Mating           | 0.762µm                        |
| Plating min - Termination      | 0.762µm                        |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | Yes                            |
| Ports                          | 16                             |
| Temperature Range - Operating  | -40° to +85°C                  |
| Termination Interface Style    | Through Hole - Compliant Pin   |

### Solder Process Data

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|