

DRS Series Modular Surge Protective Device



The DRS Series Surge Protective Device (SPD) is designed to be easily installed in power and control panels using standard DIN-rail mounting brackets. This series of product offers 40,000 amps of both normal and common mode surge protection. The DRS series is available in single phase, split phase, three phase (3 wires) and three phase (4 wires) configurations.

Replaceable modules allow for easy maintenance and mount directly into the DRS base assembly, simplifying the replacement process. The status of the surge protector modules can be monitored through the indicator lenses or remotely through the alarm terminals.

Standard Features:

- Effectively handle high-energy transients on type TT, TN-C, TN-S, and TN-C-S power systems.
- SPD rated Type 2 in accordance with EN 61643-11; Class I & II in accordance with IEC 61643-1.
- Built-in thermal components disconnect SPD from the power source to avoid thermal runaway conditions.
- Visual inspection windows on each module provide continuous status indication.
- Three position terminals provide remote status monitoring capability.
- DIN-rail mounting and plug-in module design allow for easy installation and maintenance.
- Gas tube module option for type TT grounding systems
- 5 year warranty.

Specifications

DRS Series		
Nominal Discharge Current (8x20μs)	I _n	20kA
Maximum Discharge Current (8x20μs)	I _{max}	40kA
Nominal Voltage	U _n	120, 230, 240, 277, 346, 480, 600 volts
Maximum Continuous Operating Voltage	U _c	150, 320, 380, 420, 580, 680, 1000 volts
Voltage Protection Level	U _p	1.2 kV, 1.6 kV, 1.8 kV, 2.0 kV, 2.4 kV
Response Time	T _s	25ns
Relative Humidity		95%
Insulation Resistance		>10 ³ M Ω
Temperature Range		-40°C to +85°C
Degree of Protection		IP20
Housing		ABS / PA UL94V0
Warranty		5 years

How to Specify the Appropriate Model


Example: DRS 120 3 1 Q

DRS	Nominal Voltage (U _n) (XXX)	# of Metal Oxide Varistor Modules* (X)	# of Gas Tube Modules** (X)	Higher Rated Voltage*** (Optional)
	120	0	0	Q
	230	1	1	
	240	2		
	277	3		
	346	4		
	480			
	600			


- * MOV modules are typically one module per phase and may be wired L-N, L-G or N-G.
- ** Gas tube modules typically used in the N-G mode for type TT grounding systems.
- *** Certain applications require higher rated components in order to survive frequent voltage rises. In this case, order a unit with a "Q" at the end of the part number.

Replacement modules available: Order DRS + U_n + M (for MOV) or G (for Gas tube)


Typical MOV Model



Typical MOV/Gas Tube Model



Dimensional Data:



Mounting: Symetrical rail EN50022/DIN 46277-3

I/O Connections: By screw terminal 4-25mm² by connection bus

Contact

Surge Protection
100 Emerson Parkway
Binghamton, NY 13905
T: 607-721-8840
T: 800-288-6169
F: 607-722-8713
E: SurgeTech@Emerson.com

Technical Support

800 288 6169 Toll-Free (U.S. & Canada Only)
607 721 8840 Phone (Outside U.S.)
607 722 8713 Fax

While every precaution has been taken to ensure accuracy and completeness in this literature, Emerson Network Power assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions.

© 2014 Emerson Network Power. All rights reserved throughout the world. Specifications subject to change without notice.

All names referred to are trademarks or registered trademarks of their respective owners.

SL-22110 (R01/14) Printed in USA

Emerson Network Power.
The global leader in enabling
Business-Critical Continuity™.

- AC Power
- Connectivity
- DC Power
- Embedded Computing
- Embedded Power
- Industrial Power
- Infrastructure Management & Monitoring
- Outside Plant
- **Power Switching & Controls**
- Thermal Management
- Racks & Integrated Cabinets
- Service

Emerson Network Power.com/Surge

Business-Critical Continuity™, Emerson Network Power and the Emerson Network Power logo are trademarks and service marks of Emerson Electric Co. ©2014 Emerson Electric Co.