

Rebar Tying Tool LXT®

DTR180

18V

Quick rebar tie for rebars and underfloor heating cables

An easy-to-use cordless rebar tie for rebars and underfloor heating cables. Single-handed operation allows positioning of rebars. The strength of tying can be adjusted between 1 and 6, depending on the material.



Technical specifications

Nominal Battery Voltage	18 V
Brushless Motor	✓
Voltage LXT	✓
Wire diameter	0,8 mm
Maximum tying capacity 2 rebars	16 x 16 mm
Maximum tying capacity 3 rebars	(2 x 13) x 13 mm
Maximum tying capacity 4 rebars	(2 x 13) x (2 x 13) mm
Sound Power Level (L _{WA})	85 dB(A)
Sound Pressure Level (L _{pA})	78 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Tool weight with battery	2,3 - 2,6 kg
Product Dimensions (L x W x H):	304 x 93 x 318 mm

User benefits

- Brushless maintenance-free and long-life motor
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Optional AC

191A57-9

Electro-Galvanized Rebar Tie Wire



199137-9

Tie Wire Set 0,8 mm Standard, 50



783208-8

Hex Wrench 2,5 mm



821552-6

Makpac case (4)



Other

User manual

Parts drawing