


## AC-DC 60W


6A-601DBXX

DESKTOP  
(AC Inlet C14 )

## Features:

- IEC/EN/UL/CUL 62368 & 60950
- Universal AC Input 90~264Vac
- Regulated Output With Low Ripple Noise
- 100% burn in test
- 1 year warranty
- CEC, DoE Level VI, ErP Stage 2, CoC Tier 2, GEMS
- WEEE / ROHS 2.0 / REACH 2.0
- Safety : UL/CUL, CB, CE, FCC, CCC, PSE, RCM

## Dimension:



| Model No.  | O/P Voltage | O/P Current |
|------------|-------------|-------------|
| 6A-601DB12 | 12V         | 5.0A        |
| 6A-601DB15 | 15V         | 4.0A        |
| 6A-601DB19 | 19V         | 3.42A       |
| 6A-601DB24 | 24V         | 2.7A        |

## Specification:

|                   |                                                                 |                                                     |
|-------------------|-----------------------------------------------------------------|-----------------------------------------------------|
| Input             | Voltage                                                         | AC 90V~264V Universal Full Range                    |
|                   | Frequency                                                       | 47-63Hz                                             |
|                   | Current                                                         | 1.5A                                                |
|                   | Leakage Current                                                 | < 3.5mA                                             |
| Others Protection | Start up time                                                   | < 3000mS @115VAC Full Load                          |
|                   | Rise time                                                       | <20mS                                               |
|                   | Hold up time                                                    | >20mS @ 230Vac/50Hz input                           |
|                   | Protection                                                      | OCP/OVP/SCP                                         |
|                   | Cooling                                                         | Natural Convection Cooling                          |
| Environment       | Temperature                                                     | Operating: 0~40℃;Storage: -10~+70℃                  |
|                   | Humidity                                                        | Operating: 20%~85%;Storage: 10%~95%(Non Condensing) |
| M.T.B.F           | 50k Hours MIL-HDBK-217F @115VAC/ 230VAC Full Load Ambient : 25℃ |                                                     |
| Safety Regulation | UL 62368-1, CSA C22.2 No.62368-1, IEC62368-1, EN62368-1         |                                                     |
|                   | UL 60950-1, CSA C22.2 No.60950-1, IEC60950-1, EN60950-1         |                                                     |
| EMC               | EMI                                                             | FCC CFR 47 PART 15B, EN55032, EN61000-3             |
|                   | EMS                                                             | EN55024(EN61204-3), EN61000-4                       |

