





Straight Male Stud Fitting with 24° Taper / O-Ring		134-137
FI-EGED		
	Whitworth Parallel Pipe Thread (BSPP) / Profile Sealing Ring FI-EGED-...-R-WD	134
	Metric Parallel Thread / Profile Sealing Ring FI-EGED-...-M-WD	136
	NPT Thread FI-EGED-...-N	137
Straight Fitting with 24° Taper / O-Ring		138
FI-SNV		
	Straight Reducer with 24° Taper / O-Ring FI-SNV	140
	Straight Reducer for Tube Ends with 24° Taper / O-Ring FI-REDSO	144
	Distance Adaptors with 24° Taper / O-Ring FI-REDSO	148
	Adjustable Elbow (90°) with 24° Taper / O-Ring FI-EWD	150
	Adjustable Elbow (45°) with 24° Taper / O-Ring FI-EVD	151
	Adjustable Branch Tee with 24° Taper / O-Ring FI-ETD	152
	Adjustable Barrel Tee with 24° Taper / O-Ring FI-ELD	153



Straight Male Stud Fitting with 24° Taper / O-Ring Type FI-EGED-...-R-WD • Series L



Whitworth Parallel Pipe Thread (BSPP)

Profile Sealing Ring

Ordering Codes

***FI-EGED*-10*L*R*-WD*-BV*-W3*-DKO**

* Straight Male Stud Fitting with 24° Taper / O-Ring (DKO) **FI-EGED**

* Outside Tube Diameter D1 (in mm) **-10**

* Series Light Series (page 134) **L**
Heavy Series (page 135) **S**

* Thread Type Whitworth Parallel Pipe Thread (BSPP) **R**

If required, please indicate special sizes, e.g. R3/8!

* Seal Type Profile Sealing Ring **-WD**

* Seal Material Male Stud: NBR (Buna-N®) **-BV**
24° Taper: FKM (Viton®) **-V**
FKM (Viton®)

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nut and O-ring **-DKO**

Series	Tube OD mm D1	PN bar	Dimensions mm Thread T	D2	i	L1	S1	S2	Torque N-m Thread T	Weight kg ca. per 100	Ordering Codes
L	6	500	G 1/8	2,5	8	24,5	14	14	18	3,74	FI-EGED-06LR-WD-BV-W3-DKO
	6	500	G 1/4	2,5	12	27,5	19	14	35	5,42	FI-EGED-06LR1/4-WD-BV-W3-DKO
	8	500	G 1/8	4	8	25,5	14	17	18	3,96	FI-EGED-08LR1/8-WD-BV-W3-DKO
	8	500	G 1/4	4	12	29,5	19	17	35	5,23	FI-EGED-08LR-WD-BV-W3-DKO
	8	400	G 3/8	5	12	28,5	22	17	70	7,16	FI-EGED-08LR3/8-WD-BV-W3-DKO
	10	500	G 1/4	6	12	27,5	19	19	35	5,68	FI-EGED-10LR-WD-BV-W3-DKO
	10	400	G 3/8	6,5	12	34,5	22	19	70	7,69	FI-EGED-10LR3/8-WD-BV-W3-DKO
	10	400	G 1/2	6,5	14	36	27	19	90	13,5	FI-EGED-10LR1/2-WD-BV-W3-DKO
	12	500	G 1/4	6	12	28	19	22	35	7,02	FI-EGED-12LR1/4-WD-BV-W3-DKO
	12	400	G 3/8	8	12	34	22	22	70	9,78	FI-EGED-12LR-WD-BV-W3-DKO
	12	400	G 1/2	8	14	29,5	27	22	90	11,71	FI-EGED-12LR1/2-WD-BV-W3-DKO
	15	400	G 3/8	9	12	31,5	22	27	70	10,74	FI-EGED-15LR3/8-WD-BV-W3-DKO
	15	400	G 1/2	10	14	32	27	27	90	13,70	FI-EGED-15LR-WD-BV-W3-DKO
	15	250	G 3/4	11	16	31	32	27	180	14,89	FI-EGED-15LR3/4-WD-BV-W3-DKO
	18	400	G 1/2	13	14	31,5	27	32	90	14,86	FI-EGED-18LR-WD-BV-W3-DKO
	18	250	G 3/4	13	16	31	32	32	180	17,92	FI-EGED-18LR3/4-WD-BV-W3-DKO
	22	250	G 1/2	17	14	34,5	32	36	90	19	FI-EGED-22LR1/2-WD-BV-W3-DKO
	22	250	G 3/4	17	16	32,5	32	36	180	20,98	FI-EGED-22LR-WD-BV-W3-DKO
	22	250	G 1	17	18	34,5	41	36	310	31,66	FI-EGED-22LR1-WD-BV-W3-DKO
	28	250	G 3/4	23	16	35	36	41	180	22,99	FI-EGED-28LR3/4-WD-BV-W3-DKO
	28	250	G 1	22	18	35	41	41	310	22,78	FI-EGED-28LR-WD-BV-W3-DKO
	35	250	G 1 1/4	28	20	42,5	50	50	450	51,00	FI-EGED-35LR-WD-BV-W3-DKO
	35	250	G 1 1/2	28	22	46,5	55	50	540	61,3	FI-EGED-35LR1-1/2-WD-BV-W3-DKO
	42	250	G 1 1/4	35	20	47	55	60	450	62,8	FI-EGED-42LR1-1/4-WD-BV-W3-DKO
	42	250	G 1 1/2	34	22	46,5	55	60	540	68,60	FI-EGED-42LR-WD-BV-W3-DKO

Spare Parts / Accessories



O-Ring
Type **O-RING** Page 239



Profile Sealing Ring
Type **WDG** Page 238

Standard seal material: See Ordering Code BV.

Male threaded studs were designed for female threaded ports in components made of steel. For applications with components made of softer mating materials (e.g. Aluminium), the use of connectors with additionally rolled male threads is recommended.


Please contact STAUFF prior to the assembly for further information.

Male stud acc. to ISO 1179-2 (Type E)
Port acc. to ISO 1179-1

Torque recommendations for Steel mating material.



Straight Male Stud Fitting with 24° Taper / O-Ring Type FI-EGED-...-R-WD ▪ Series S



Whitworth Parallel Pipe Thread (BSPP)

Profile Sealing Ring

Series	Tube OD mm D1	PN bar	Dimensions mm Thread T	D2	i	L1	S1	S2	Torque N-m Thread T	Weight kg ca. per 100	Ordering Codes
S	6	800	G 1/4	2,5	12	27	19	17	55	5,55	FI-EGED-06SR-WD-BV-W3-DKO
	8	800	G 1/4	4	12	29,5	19	19	55	6,52	FI-EGED-08SR-WD-BV-W3-DKO
	8	800	G 3/8	4	12	32	22	19	80	8,25	FI-EGED-08SR3/8-WD-BV-W3-DKO
	10	800	G 1/4	6	12	29,5	19	22	55	7,19	FI-EGED-10SR1/4-WD-BV-W3-DKO
	10	800	G 3/8	6	12	32	22	22	80	9,63	FI-EGED-10SR-WD-BV-W3-DKO
	12	630	G 1/4	5	12	33	19	24	55	9,05	FI-EGED-12SR1/4-WD-BV-W3-DKO
	12	630	G 3/8	8	12	34	22	24	80	7,03	FI-EGED-12SR-WD-BV-W3-DKO
	12	630	G 1/2	8	14	36	27	24	115	6,36	FI-EGED-12SR1/2-WD-BV-W3-DKO
	14	630	G 1/2	9	14	37	27	27	115	14,39	FI-EGED-14SR-WD-BV-W3-DKO
	16	630	G 3/8	8	12	37,5	27	30	80	16,88	FI-EGED-16SR3/8-WD-BV-W3-DKO
	16	630	G 1/2	11	14	37	27	30	115	17,03	FI-EGED-16SR-WD-BV-W3-DKO
	16	420	G 3/4	11	16	39,5	32	30	180	23,9	FI-EGED-16SR3/4-WD-BV-W3-DKO
	20	420	G 1/2	12	14	40,5	27	36	115	22,47	FI-EGED-20SR1/2-WD-BV-W3-DKO
	20	420	G 3/4	14	16	43	32	36	180	27,34	FI-EGED-20SR-WD-BV-W3-DKO
	25	420	G 3/4	17	16	49	36	46	180	42,11	FI-EGED-25SR3/4-WD-BV-W3-DKO
	25	420	G 1	18	18	48	41	46	310	50,20	FI-EGED-25SR-WD-BV-W3-DKO
	30	420	G 1 1/4	23	20	51	50	50	450	70,40	FI-EGED-30SR-WD-BV-W3-DKO
	30	420	G 1 1/2	22	22	53,5	55	50	540	83,5	FI-EGED-30SR1-1/2-WD-BV-W3-DKO
	30	420	G 1	20	18	50,5	41	50	310	54,7	FI-EGED-30SR1-WD-BV-W3-DKO
	38	420	G 1 1/4	30	20	56	55	60	450	92,4	FI-EGED-38SR1-1/4-WD-BV-W3-DKO
	38	420	G 1 1/2	30	22	60	55	60	540	93,50	FI-EGED-38SR-WD-BV-W3-DKO

Standard seal material: See Ordering Code BV.

Male threaded studs were designed for female threaded ports in components made of steel. For applications with components made of softer mating materials (e.g. Aluminium), the use of connectors with additionally rolled male threads is recommended.

Please contact STAUFF prior to the assembly for further information.

Male stud acc. to ISO 1179-2 (Type E)
Port acc. to ISO 1179-1

Torque recommendations for Steel mating material.

Ordering Codes

***FI-EGED*-10*S*R*-WD*-BV*-W3*-DKO**

* Straight Male Stud Fitting with 24° Taper / O-Ring (DKO) **FI-EGED**

* Outside Tube Diameter D1 (in mm) **-10**

* Series Light Series (page 134) **L**
Heavy Series (page 135) **S**

* Thread Type Whitworth Parallel Pipe Thread (BSPP) **R**

If required, please indicate special sizes, e.g. R3/8!

* Seal Type Profile Sealing Ring **-WD**

* Seal Material Male Stud: NBR (Buna-N®) **-BV**
24° Taper: FKM (Viton®)
FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.


* Assembling / Kitting Fitting body supplied with swivel nut and O-ring **-DKO**

Spare Parts / Accessories

	O-Ring Type O-RING	Page 239
	Profile Sealing Ring Type WDG	Page 238



Straight Male Stud Fitting with 24° Taper / O-Ring Type FI-EGED-...-M-WD ▪ Series L / S



Profile Sealing Ring

Metric Parallel Thread

Ordering Codes

***FI-EGED*-10*L*M*-WD*-BV*-W3*-DK0**

* Straight Male Stud Fitting with 24° Taper / O-Ring (DK0) **FI-EGED**

* Outside Tube Diameter D1 (in mm) **-10**

* Series Light Series **L**
Heavy Series **S**

* Thread Type Metric Parallel Thread **M**

If required, please indicate special sizes, e.g. M12x1.5!

* Seal Type Profile Sealing Ring **-WD**

* Seal Material Male Stud: NBR (Buna-N®) **-BV**
24° Taper: FKM (Viton®) **-V**
FKM (Viton®)

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nut and O-ring **-DK0**

Series	Tube OD mm D1	PN bar	Dimensions mm Thread T	D2	i	L1	S1	S2	Torque N-m Thread T	Weight kg ca. per 100	Ordering Codes
L	6	500	M10x1	2,5	8	24,5	14	14	18	3,76	FI-EGED-06LM-WD-BV-W3-DK0
	8	500	M12x1,5	4	12	26,5	17	17	25	4,64	FI-EGED-08LM-WD-BV-W3-DK0
	10	500	M14x1,5	6	12	27,5	19	19	45	5,97	FI-EGED-10LM-WD-BV-W3-DK0
	12	400	M16x1,5	8	12	30,5	22	22	55	9,58	FI-EGED-12LM-WD-BV-W3-DK0
	12	400	M18x1,5	8	12	31	24	22	70	9,78	FI-EGED-12LM18x1.5-WD-BV-W3-DK0
	12	400	M22x1,5	8	14	29	27	22	125	10,12	FI-EGED-12LM22x1.5-WD-BV-W3-DK0
	15	400	M18x1,5	10	12	31,5	24	27	70	12,62	FI-EGED-15LM-WD-BV-W3-DK0
	15	400	M22x1,5	11	14	34	27	27	125	14,26	FI-EGED-15LM22x1.5-WD-BV-W3-DK0
	18	400	M22x1,5	13	14	31,5	27	32	125	15,28	FI-EGED-18LM-WD-BV-W3-DK0
	22	250	M26x1,5	17	16	32,5	32	36	180	20,75	FI-EGED-22LM-WD-BV-W3-DK0
	28	250	M33x2	22	18	35	41	41	310	28,61	FI-EGED-28LM-WD-BV-W3-DK0
	35	250	M42x2	28	20	42,5	50	50	450	52,30	FI-EGED-35LM-WD-BV-W3-DK0
	42	250	M48x2	34	22	46,5	55	60	540	72,56	FI-EGED-42LM-WD-BV-W3-DK0
S	6	800	M12x1,5	2,5	12	27	17	17	35	4,88	FI-EGED-06SM-WD-BV-W3-DK0
	8	800	M14x1,5	4	12	29,5	19	19	55	6,59	FI-EGED-08SM-WD-BV-W3-DK0
	10	800	M16x1,5	6	12	32	22	22	70	9,34	FI-EGED-10SM-WD-BV-W3-DK0
	12	630	M18x1,5	8	12	34	24	24	90	10,44	FI-EGED-12SM-WD-BV-W3-DK0
	14	630	M20x1,5	9	14	36,5	27	27	125	16,00	FI-EGED-14SM-WD-BV-W3-DK0
	16	630	M22x1,5	11	14	37	27	30	135	17,32	FI-EGED-16SM-WD-BV-W3-DK0
	20	420	M27x2	14	16	43	32	36	180	27,99	FI-EGED-20SM-WD-BV-W3-DK0
	25	420	M33x2	18	18	48	41	46	310	50,00	FI-EGED-25SM-WD-BV-W3-DK0
	30	420	M42x2	23	20	51	50	50	450	70,30	FI-EGED-30SM-WD-BV-W3-DK0
	38	420	M48x2	30	22	60	55	60	540	94,50	FI-EGED-38SM-WD-BV-W3-DK0

Spare Parts / Accessories



O-Ring
Type **O-RING** Page 239



Profile Sealing Ring
Type **WDG** Page 238

Standard seal material: See Ordering Code BV.

Male threaded studs were designed for female threaded ports in components made of steel. For applications with components made of softer mating materials (e.g. Aluminium), the use of connectors with additionally rolled male threads is recommended.

Please contact STAUFF prior to the assembly for further information.


Male stud acc. to ISO 9974-2 (Type E)

Port acc. to ISO 9974-1

Torque recommendations for Steel mating material.



Straight Male Stud Fitting with 24° Taper / O-Ring Type FI-EGED-...-N • Series L / S



NPT Thread

Series	Tube OD mm D1	PN bar	Dimensions mm Thread T	D2	i	L1	S1	S2	Weight kg ca. per 100	Ordering Codes
L	6	315	1/8 NPT	3	10	33	14	14	3,75	FI-EGED-06L1/8N-V-W3-DK0
	8	315	1/4 NPT	5	15	41,5	14	17	4,53	FI-EGED-08L1/4N-V-W3-DK0
	10	315	1/4 NPT	6,5	15	41,5	17	19	5,34	FI-EGED-10L1/4N-V-W3-DK0
	12	315	3/8 NPT	8	15	46	19	22	8,42	FI-EGED-12L3/8N-V-W3-DK0
	15	315	1/2 NPT	11	20	50	22	27	12,06	FI-EGED-15L1/2N-V-W3-DK0
	18	315	1/2 NPT	12	20	48	27	32	15,73	FI-EGED-18L1/2N-V-W3-DK0
	22	160	3/4 NPT	17	20	51	30	36	20,22	FI-EGED-22L3/4N-V-W3-DK0
	28	160	1 NPT	23	25	60	41	41	29,5	FI-EGED-28L1N-V-W3-DK0
	35	160	1 1/4 NPT	28	26	66,5	50	50	53,2	FI-EGED-35L1-1/4N-V-W3-DK0
	42	160	1 1/2 NPT	35	26	70	55	66	69,45	FI-EGED-42L1-1/2N-V-W3-DK0
S	6	630	1/4 NPT	3	15	42	17	17	4,2	FI-EGED-06S1/4N-V-W3-DK0
	8	630	1/4 NPT	4	15	43	17	19	5,94	FI-EGED-08S1/4N-V-W3-DK0
	10	630	3/8 NPT	6,5	15	44,5	19	22	8,42	FI-EGED-10S3/8N-V-W3-DK0
	12	630	3/8 NPT	8	15	47	19	24	9,34	FI-EGED-12S3/8N-V-W3-DK0
	14	630	1/2 NPT	9	20	54	24	27	15,1	FI-EGED-14S1/2N-V-W3-DK0
	16	400	1/2 NPT	11	20	54	24	27	15,63	FI-EGED-16S1/2N-V-W3-DK0
	20	400	3/4 NPT	14	20	57	30	36	25,5	FI-EGED-20S3/4N-V-W3-DK0
	25	400	1 NPT	18	25	67	36	46	44,71	FI-EGED-25S1N-V-W3-DK0
	30	400	1 1/4 NPT	22	26	71	50	50	72,11	FI-EGED-30S1-1/4N-V-W3-DK0
	38	315	1 1/2 NPT	30	26	79	55	60	95	FI-EGED-38S1-1/2N-V-W3-DK0

Standard seal material: See Ordering Code V.

Male threaded studs were designed for female threaded ports in components made of steel. For applications with components made of softer mating materials (e.g. Aluminium), the use of connectors with additionally rolled male threads is recommended.

Please contact STAUFF prior to the assembly for further information.

Male stud acc. to ANSI/ASME B1.20.1-1983

Port acc. to ANSI/ASME B1.20.1-1983

Suitable liquid / plastic sealant required.

Torque recommendations for Steel mating material.

Ordering Codes

***FI-EGED*-10*L*1/4*N*-V*-W3*-DK0**

* Straight Male Stud Fitting with 24° Taper / O-Ring (DK0) **FI-EGED**

* Outside Tube Diameter D1 (in mm) **-10**

* Series Light Series **L**
Heavy Series **S**

* Thread Size acc. to dimension table **1/4**

Please always indicate thread sizes, e.g. 1/4!

* Thread Type NPT Thread **N**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nut and O-ring **-DK0**

Spare Parts / Accessories




O-Ring
Type **O-RING**

Page 239



Straight Fitting with 24° Taper / O-Ring Type FI-SNV - Series L



Ordering Codes

FI-SNV-10*L*-V*-W3*-DKO

* Straight Fitting with 24° Taper / O-Ring (DKO) **FI-SNV**

* Outside Tube Diameter D1 (in mm) **-10**

* Series Light Series (page 138) **L**
Heavy Series (page 139) **S**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nuts and O-rings **-DKO**

* Total length dimension see table **-GLA**
dimension see table **-GLB**

Spare Parts / Accessories



O-Ring
Type **O-RING**


Page 239

Series	Tube OD mm D1	PN bar	Dimensions mm				Weight kg ca. per 100	Ordering Codes
			D2	L1	L2	S1		
L	6	500	3	30,8	33,5	14	2,81	FI-SNV-06L-V-W3-DKO-GLB
	6	500	3	34	36,7	14	3,82	FI-SNV-06L-V-W3-DKO
	6	500	3	36,3	39	14	2,99	FI-SNV-06L-V-W3-DKO-GLA
	8	500	5	30,8	33,5	17	4,19	FI-SNV-08L-V-W3-DKO-GLB
	8	500	5	34	36,7	17	4,29	FI-SNV-08L-V-W3-DKO
	8	500	5	36,8	39,5	17	4,45	FI-SNV-08L-V-W3-DKO-GLA
	10	500	6	32,2	34	19	5,56	FI-SNV-10L-V-W3-DKO-GLB
	10	500	6	36	37,8	19	5,78	FI-SNV-10L-V-W3-DKO
	10	500	6	37,7	39,5	19	6	FI-SNV-10L-V-W3-DKO-GLA
	12	400	8	32,2	34	22	7,5	FI-SNV-12L-V-W3-DKO-GLB
	12	400	8	36	37,8	22	7	FI-SNV-12L-V-W3-DKO
	12	400	8	39,5	41,3	22	8,04	FI-SNV-12L-V-W3-DKO-GLA
	15	400	11	39	40,8	27	12,58	FI-SNV-15L-V-W3-DKO
	15	400	11	40,7	42,5	27	12,62	FI-SNV-15L-V-W3-DKO-GLA
	18	400	13	36,2	39	32	17	FI-SNV-18L-V-W3-DKO-GLB
	18	400	13	40,5	43,3	32	17,59	FI-SNV-18L-V-W3-DKO
	18	400	13	42,2	45	32	18,16	FI-SNV-18L-V-W3-DKO-GLA
	22	250	17	41,2	44	36	24,12	FI-SNV-22L-V-W3-DKO-GLB
	22	250	17	45	47,8	36	24,91	FI-SNV-22L-V-W3-DKO
	22	250	17	46,7	49,5	36	25,4	FI-SNV-22L-V-W3-DKO-GLA
	28	250	23	46	48,8	41	27,4	FI-SNV-28L-V-W3-DKO
	28	250	23	48,7	51,5	41	28,57	FI-SNV-28L-V-W3-DKO-GLA
	35	250	28	46	52	50	43,36	FI-SNV-35L-V-W3-DKO-GLB
	35	250	28	53	59	50	45,98	FI-SNV-35L-V-W3-DKO
	35	250	28	55	61	50	47,1	FI-SNV-35L-V-W3-DKO-GLA
	42	250	35	53	60	60	69,5	FI-SNV-42L-V-W3-DKO
	42	250	34	55,5	62,5	60	71,5	FI-SNV-42L-V-W3-DKO-GLA

Standard seal material is FKM (Viton®).



Straight Fitting with 24° Taper / O-Ring Type FI-SNV - Series S



Series	Tube OD mm D1	PN bar	Dimensions mm D2	L1	L2	S1	Weight kg ca. per 100	Ordering Codes
S	6	800	3	30,3	33	17	4,21	FI-SNV-06S-V-W3-DK0-GLB
	6	800	3	37	39,7	17	4,52	FI-SNV-06S-V-W3-DK0
	6	800	3	37,8	40,5	17	0,46	FI-SNV-06S-V-W3-DK0-GLA
	8	800	4	31,3	34	19	5,63	FI-SNV-08S-V-W3-DK0-GLB
	8	800	4	37	39,7	19	6,03	FI-SNV-08S-V-W3-DK0
	8	800	4	37,8	40,5	19	6,13	FI-SNV-08S-V-W3-DK0-GLA
	10	800	6	32,2	35	22	7,63	FI-SNV-10S-V-W3-DK0-GLB
	10	800	6	41	43,8	22	8,39	FI-SNV-10S-V-W3-DK0
	12	630	8	35,2	38	24	6,52	FI-SNV-12S-V-W3-DK0-GLB
	12	630	8	42	44,8	24	10,51	FI-SNV-12S-V-W3-DK0
	14	630	9	37,2	41	27	2,9	FI-SNV-14S-V-W3-DK0-GLB
	14	630	9	45	48,8	27	13,9	FI-SNV-14S-V-W3-DK0
	16	630	10	37,2	42	30	16,09	FI-SNV-16S-V-W3-DK0-GLB
	16	630	10	46	50,8	30	17,57	FI-SNV-16S-V-W3-DK0
	20	420	13	42	48	36	26,3	FI-SNV-20S-V-W3-DK0-GLB
	20	420	13	55	61	36	24,36	FI-SNV-20S-V-W3-DK0
	25	420	18	45,5	54,4	46	45,05	FI-SNV-25S-V-W3-DK0-GLB
	25	420	18	56,5	65,4	46	50,1	FI-SNV-25S-V-W3-DK0-GLA
	25	420	18	58	67	46	49,45	FI-SNV-25S-V-W3-DK0
	30	420	20	50	62	50	57,2	FI-SNV-30S-V-W3-DK0-GLB
	30	420	20	62	74	50	61,4	FI-SNV-30S-V-W3-DK0
	38	420	30	50	67	60	74,2	FI-SNV-38S-V-W3-DK0-GLB
	38	420	30	67	84	60	86,7	FI-SNV-38S-V-W3-DK0

Standard seal material is FKM (Viton®).

Ordering Codes

FI-SNV-10*S*-V*-W3*-DK0

* Straight Fitting with 24° Taper / O-Ring (DKO)	FI-SNV
* Outside Tube Diameter D1 (in mm)	-10
* Series	Light Series (page 138) Heavy Series (page 139)
	L S
* Seal Material	FKM (Viton®)
	-V
* Material Code	Steel, zinc/nickel-plated
	-W3
Please contact STAUFF for alternative materials and surface finishings.	
* Assembling / Kitting	Fitting body supplied with swivel nuts and O-rings
	-DK0
* Total length	dimension see table
	-GLA
	-GLB

Spare Parts / Accessories




O-Ring
Type **O-RING**

Page 239



Straight Reducer with 24° Taper / O-Ring Type FI-SNV - Series L



Ordering Codes

***FI-SNV*-10/*08*L*-V*-W3*-DKO**

★ Straight Reducer with 24° Taper / O-Ring (DKO) **FI-SNV**

★ Outside Tube Diameter D1 (in mm) **-10**

★ Outside Tube Diameter D2 (in mm) **08**

★ Series Light Series (pages 140/141) **L**
Heavy Series (page 142) **S**

★ Seal Material FKM (Viton®) **-V**

★ Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

★ Assembling / Kitting Fitting body supplied with swivel nuts and O-rings **-DKO**

★ Total length dimension see table **-GLB**

Series	Tube OD mm		PN bar	Dimensions mm						Version	Weight kg ca. per 100	Ordering Codes
	D1	D2		D3	D4	L1	L2	S1	S2			
L	8 L	6 L	500	3	3	34	36,7	17	14	A	4,72	FI-SNV-08/06L-V-W3-DKO
	10 L	6 L	500	3	3	35	37,3	19	14	A	5,50	FI-SNV-10/06L-V-W3-DKO
	10 L	8 L	500	5	5	35	37,3	19	17	A	5,21	FI-SNV-10/08L-V-W3-DKO
	12 L	6 L	400	3	3	35	37,3	22	14	B	18,04	FI-SNV-12/06L-V-W3-DKO
	12 L	8 L	400	5	5	36	38,3	22	17	B	6,22	FI-SNV-12/08L-V-W3-DKO
	12 L	10 L	400	6,5	6,5	36,5	38,3	22	19	A	6,96	FI-SNV-12/10L-V-W3-DKO
	12 L	12 S	400	8	8	39	41,3	24	22	B	9,42	FI-SNV-12L/12S-V-W3-DKO
	15 L	8 L	400	5	5	36,5	38,8	27	17	B	1,96	FI-SNV-15/08L-V-W3-DKO
	15 L	10 L	400	6,5	6,5	37,5	39,3	27	19	B	4,40	FI-SNV-15/10L-V-W3-DKO
	15 L	12 L	400	8	8	37	38,8	27	22	B	11,06	FI-SNV-15/12L-V-W3-DKO-GLB
	15 L	12 L	400	8	8	44	45,8	27	22	A	11,69	FI-SNV-15/12L-V-W3-DKO
	18 L	10 L	400	6,5	6,5	38	40,3	32	19	B	12,68	FI-SNV-18/10L-V-W3-DKO
	18 L	12 L	400	8	8	38	40,3	32	22	B	13,51	FI-SNV-18/12L-V-W3-DKO
	18 L	15 L	400	11	11	42,5	44,8	32	27	A	15,38	FI-SNV-18/15L-V-W3-DKO-GLB
	18 L	15 L	400	11	11	45	47,3	32	27	A	16,60	FI-SNV-18/15L-V-W3-DKO
	18 L	16 S	400	11	11	43,5	47,3	32	30	A	17,95	FI-SNV-18L/16S-V-W3-DKO

Standard seal material is FKM (Viton®).


Spare Parts / Accessories



O-Ring
Type **O-RING**

Page 239





Straight Reducer with 24° Taper / O-Ring Type FI-SNV - Series L



Series	Tube OD mm	PN bar	Dimensions mm				Version				Weight kg ca. per 100	Ordering Codes
	D1	D2	D3	D4	L1	L2	S1	S2				
L	22 L	12 L	250	8	8	40,5	42,8	36	22	B	17,52	FI-SNV-22/12L-V-W3-DK0
	22 L	15 L	250	11	11	42	44,3	36	27	B	19,83	FI-SNV-22/15L-V-W3-DK0
	22 L	18 L	250	13	13	45	47,8	36	32	A	23,35	FI-SNV-22/18L-V-W3-DK0
	22 L	20 S	250	14	14	50	54,4	36	32	A	27,82	FI-SNV-22L/20S-V-W3-DK0
	28 L	15 L	250	11	11	43	45,3	41	27	B	23,86	FI-SNV-28/15L-V-W3-DK0
	28 L	18 L	250	13	13	45	47,8	41	32	B	26,44	FI-SNV-28/18L-V-W3-DK0
	28 L	22 L	250	17	17	46	48,8	41	36	B	28,93	FI-SNV-28/22L-V-W3-DK0
	28 L	25 S	250	18	18	52,5	58,4	41	46	A	41,48	FI-SNV-28L/25S-V-W3-DK0
	35 L	18 L	250	13	13	48	52,4	50	32	B	39,52	FI-SNV-35/18L-V-W3-DK0
	35 L	22 L	250	17	17	49,5	53,9	50	36	B	41,34	FI-SNV-35/22L-V-W3-DK0
	35 L	28 L	250	23	23	50	54,4	50	41	B	40,71	FI-SNV-35/28L-V-W3-DK0
	35 L	30 S	250	22	22	61	70	50	50	A	59,77	FI-SNV-35L/30S-V-W3-DK0
	42 L	22 L	250	17	17	49,5	54,4	60	36	B	56,50	FI-SNV-42/22L-V-W3-DK0
	42 L	28 L	250	23	23	50	54,9	60	41	B	56,10	FI-SNV-42/28L-V-W3-DK0
	42 L	35 L	250	28	28	53	59,5	60	50	B	60,70	FI-SNV-42/35L-V-W3-DK0
	42 L	38 S	250	30	30	55	67	60	60	A	78,2	FI-SNV-42L/38S-V-W3-DK0

Standard seal material is FKM (Viton®).

Ordering Codes

***FI-SNV*-10/*08*L*-V*-W3*-DK0**

* Straight Reducer with 24° Taper / O-Ring (DK0) **FI-SNV**

* Outside Tube Diameter D1 (in mm) **-10**

* Outside Tube Diameter D2 (in mm) **08**

* Series Light Series (pages 140/141) **L**
Heavy Series (page 142) **S**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nuts and O-rings **-DK0**

Spare Parts / Accessories



O-Ring
Type **O-RING**


Page 239




Straight Reducer with 24° Taper / O-Ring Type FI-SNV - Series S



Version A



Version B



Ordering Codes

***FI-SNV*-10/*08*S*-V*-W3*-DKO**

* Straight Reducer with 24° Taper / O-Ring (DKO) **FI-SNV**

* Outside Tube Diameter D1 (in mm) **-10**

* Outside Tube Diameter D2 (in mm) **08**

* Series Light Series (pages 140/141) **L**
Heavy Series (page 142) **S**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nuts and O-rings **-DKO**

* Total length dimension see table **-GLB**

Spare Parts / Accessories




O-Ring
Type **O-RING**

Page 239

Series	Tube OD mm		PN bar	Dimensions mm						Version	Weight kg ca. per 100	Ordering Codes
	D1	D2		D3	D4	L1	L2	S1	S2			
S	6S	6L	500	3	3	35,5	38,2	17	14	A	3,70	FI-SNV-06S/06L-V-W3-DKO
	8 S	6S	800	3	3	37	39,7	19	17	A	5,43	FI-SNV-08/06S-V-W3-DKO
	8 S	8 L	500	4	4	35,5	38,2	17	19	A	5,27	FI-SNV-08S/08L-V-W3-DKO
	10 S	6 S	800	3	3	40,5	43,2	22	17	A	6,30	FI-SNV-10/06S-V-W3-DKO
	10 S	8 S	800	4	4	39	41,7	22	19	A	7,60	FI-SNV-10/08S-V-W3-DKO
	10 S	10 L	500	6,5	6,5	38,5	40,8	22	19	A	6,98	FI-SNV-10S/10L-V-W3-DKO
	12 S	6 S	630	3	3	39	41,7	24	17	B	7,79	FI-SNV-12/06S-V-W3-DKO
	12 S	8 S	630	4	4	44	46,7	24	19	A	9,42	FI-SNV-12/08S-V-W3-DKO
	12 S	10 S	630	6,5	6,5	41,5	44,3	24	22	A	9,73	FI-SNV-12/10S-V-W3-DKO
	16 S	10 S	630	6,5	6,5	43,5	47,3	30	22	B	14,11	FI-SNV-16/10S-V-W3-DKO
	16 S	12 S	630	8	8	47,5	51,3	30	24	A	15,32	FI-SNV-16/12S-V-W3-DKO
	16 S	15 L	400	11	11	42,5	45,8	30	27	A	14,66	FI-SNV-16S/15L-V-W3-DKO
	20 S	12 S	400	8	8	48,5	52,9	36	24	B	21,90	FI-SNV-20/12S-V-W3-DKO
	20 S	16 S	400	11	11	52,5	57,9	36	30	A	24,68	FI-SNV-20/16S-V-W3-DKO
	20 S	18 L	400	13	13	47,5	51,9	36	32	A	23,43	FI-SNV-20S/18L-V-W3-DKO
	25 S	16 S	400	11	11	52	58,9	46	30	A	34,02	FI-SNV-25/16S-V-W3-DKO
	25 S	18 L	400	13	13	41,5	47,5	46	32	B	36,2	FI-SNV-25S/18L-V-W3-DKO-GLB
	25 S	18 L	400	13	13	50	56,3	46	32		38,4	FI-SNV-25S/18L-V-W3-DKO
	25 S	20 S	400	14	14	58	65,5	46	36	A	39,77	FI-SNV-25/20S-V-W3-DKO
	25 S	22 L	250	17	17	57	62,9	46	36	A	39,15	FI-SNV-25S/22L-V-W3-DKO
	30 S	16 S	400	11	11	54	62,4	50	30	B	47,00	FI-SNV-30/16S-V-W3-DKO
	30 S	20 S	400	14	14	58,5	67,5	50	36	B	51,00	FI-SNV-30/20S-V-W3-DKO
	30 S	25 S	400	17	17	60	70,5	50	46	A	56,80	FI-SNV-30/25S-V-W3-DKO
	30 S	28 L	250	22	22	59	66,4	50	41	A	45,5	FI-SNV-30S/28L-V-W3-DKO
	38 S	20 S	400	14	14	61	72,5	60	36	B	71,30	FI-SNV-38/20S-V-W3-DKO
	38 S	25 S	400	17	17	62,5	75,5	60	46	B	80,70	FI-SNV-38/25S-V-W3-DKO
	38 S	30 S	400	22	22	64,5	79	60	50	A	76,90	FI-SNV-38/30S-V-W3-DKO
	38 S	35 L	250	28	28	62	73,5	60	50	A	69,86	FI-SNV-38S/35L-V-W3-DKO

Standard seal material is FKM (Viton®).







H



Straight Reducer for Tube Ends with 24° Taper / O-Ring Type FI-REDSO - Series L



Ordering Codes

FI-REDSO-10/*08*L*-V*-W3*-DKO*-MS

* Straight Reducer for Tube Ends with 24° Taper / O-Ring (DKO) **FI-REDSO**

* Outside Tube Diameter D1 (in mm) **-10**

* Outside Tube Diameter D2 (in mm) **08**

* Series Light Series (pages 144/145) **L**
Heavy Series (pages 146/147) **S**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nut and O-ring **-DKO**

Fitting body supplied with cutting ring and union nut **-MS**

Fitting body supplied with soft-sealing cutting ring and union nut **-MSV**

Connecting Parts



Cutting Ring
Type **FI-DS** Page 28



Soft-Sealing Cutting Ring
Type **FI-WDDS** Page 29



Support Sleeve
Type **FI-VH** Page 31



STAUFF Form EVO Sealing Ring
Type **FI-FD** Page 32



Union Nut
Type **FI-M** Page 33



37° Flared Tube Fitting Set
Type **FI-AB** Page 37

Spare Parts / Accessories



O-Ring
Type **O-RING** Page 239

Series	Tube OD mm		PN bar	Dimensions mm								Weight kg ca. per 100	Ordering Codes ³
	D1	D2		D3	D4	L	L ¹	L2	S1	S2	S3		
L	8	6	500	4	4	30,5	38,5	23,5	12	17	14	3,01	FI-REDSO-08/06L-V-W3-DKO
	10	6	500	4	4	32	40	25	14	19	14	3,80	FI-REDSO-10/06L-V-W3-DKO
	10	8	500	6	6	32	40	25	14	19	17	3,99	FI-REDSO-10/08L-V-W3-DKO
	10	12	400	10	6,5	34	45	27	19	19	22	5,01	FI-REDSO-10/12L-V-W3-DKO
	12	6	400	4	4	32	40	25	17	22	14	5,69	FI-REDSO-12/06L-V-W3-DKO
	12	8	400	6	6	32	40	25	17	22	17	5,53	FI-REDSO-12/08L-V-W3-DKO
	12	10	400	8	8	33	41	26	17	22	19	5,33	FI-REDSO-12/10L-V-W3-DKO
	12	15	400	12	8	34,5	44	27,5	24	22	27	7,16	FI-REDSO-12/15L-V-W3-DKO
	15	6	400	4	11	35,5	43,5	28,5	22	27	14	8,83	FI-REDSO-15/06L-V-W3-DKO
	15	8	400	6	11	35,5	44	28,5	22	27	17	9,08	FI-REDSO-15/08L-V-W3-DKO
	15	10	400	8	8	36,5	44,5	29,5	22	27	19	9,61	FI-REDSO-15/10L-V-W3-DKO
	15	12	400	10	10	36,5	44,5	29,5	22	27	22	9,25	FI-REDSO-15/12L-V-W3-DKO
	18	6	400	4	13	35	43	28	24	32	14	11,07	FI-REDSO-18/06L-V-W3-DKO
	18	8	400	6	13	35	43	28	24	32	17	7,57	FI-REDSO-18/08L-V-W3-DKO
	18	10	400	8	8	36	44	29	24	32	19	12,64	FI-REDSO-18/10L-V-W3-DKO
	18	12	400	10	10	36	44	29	24	32	22	12,24	FI-REDSO-18/12L-V-W3-DKO
	18	15	400	12	12	37	45	30	24	32	27	12,27	FI-REDSO-18/15L-V-W3-DKO
	22	6	250	4	17	39	47	32	27	36	14	16,34	FI-REDSO-22/06L-V-W3-DKO
	22	8	250	6	17	39	48	32	27	36	17	16,27	FI-REDSO-22/08L-V-W3-DKO
	22	10	250	8	17	40	49	33	27	36	19	16,33	FI-REDSO-22/10L-V-W3-DKO
	22	12	250	10	17	40	49	33	27	36	22	16,30	FI-REDSO-22/12L-V-W3-DKO
	22	15	250	12	12	41	50	34	27	36	27	19,01	FI-REDSO-22/15L-V-W3-DKO
	22	18	250	15	15	41	50	33,5	27	36	32	18,13	FI-REDSO-22/18L-V-W3-DKO
	22	20	250	16	16	47,5	60	37	36	32	36	22,22	FI-REDSO-22L/20S-V-W3-DKO
	28	6	250	4	23	41	49	34	36	41	14	22,90	FI-REDSO-28/06L-V-W3-DKO
	28	8	250	6	23	41	50	34	36	41	17	20,95	FI-REDSO-28/08L-V-W3-DKO
	28	10	250	8	23	42	51	35	36	41	19	21,74	FI-REDSO-28/10L-V-W3-DKO
	28	12	250	10	23	42	51	35	36	41	22	10,22	FI-REDSO-28/12L-V-W3-DKO
	28	15	250	12	23	43	52	36	36	41	27	18,85	FI-REDSO-28/15L-V-W3-DKO
	28	18	250	15	23	43	52	35,5	36	41	32	22,50	FI-REDSO-28/18L-V-W3-DKO
	28	22	250	19	23	45	54	37,5	36	41	36	22,80	FI-REDSO-28/22L-V-W3-DKO

¹ Approximate dimension in assembled condition.



² Weight excluding cutting ring and union nut.

³ Standard scope of delivery: Fitting body only.

Standard seal material is FKM (Viton®).



Straight Reducer for Tube Ends with 24° Taper / O-Ring Type FI-REDSO - Series L



Series	Tube OD mm		PN bar	Dimensions mm									Weight kg ca. per 100	Ordering Codes ³
	D1	D2		D3	D4	L	L1 ¹	L2	S1	S2	S3			
L	35	6	250	4	28	44	52,5	37	46	50	14	7,82	FI-REDSO-35/06L-V-W3-DKO	
	35	8	250	6	28	44	52,5	37	46	50	17	35,43	FI-REDSO-35/08L-V-W3-DKO	
	35	10	250	8	28	45	53,5	38	46	50	19	35,35	FI-REDSO-35/10L-V-W3-DKO	
	35	12	250	10	28	45	56	38	46	50	22	33,34	FI-REDSO-35/12L-V-W3-DKO	
	35	15	250	12	28	46	55,5	39	46	50	27	15,22	FI-REDSO-35/15L-V-W3-DKO	
	35	18	250	15	28	46	57	38,5	46	50	32	34,32	FI-REDSO-35/18L-V-W3-DKO	
	35	22	250	19	28	48	59	40,5	46	50	36	34,80	FI-REDSO-35/22L-V-W3-DKO	
	35	28	250	24	24	48	59	40,5	46	50	41	38,10	FI-REDSO-35/28L-V-W3-DKO	
	42	6	250	4	35	47,5	56	40,5	50	60	14	52,66	FI-REDSO-42/06L-V-W3-DKO	
	42	8	250	6	35	47,5	59,5	40,5	50	60	17	52,58	FI-REDSO-42/08L-V-W3-DKO	
	42	10	250	8	35	48,5	60,5	41,5	50	60	19	52,58	FI-REDSO-42/10L-V-W3-DKO	
	42	12	250	10	35	48,5	60,5	41,5	50	60	22	52,60	FI-REDSO-42/12L-V-W3-DKO	
	42	15	250	12	35	49,5	61,5	42,5	50	60	27	52,30	FI-REDSO-42/15L-V-W3-DKO	
	42	18	250	15	35	49,5	61,5	42	50	60	32	52,00	FI-REDSO-42/18L-V-W3-DKO	
	42	22	250	19	35	51,5	63,5	44	50	60	36	50,10	FI-REDSO-42/22L-V-W3-DKO	
	42	28	250	24	35	51,5	63,5	44	50	60	41	50,19	FI-REDSO-42/28L-V-W3-DKO	
42	35	250	30	30	53,5	65,5	43	50	60	50	55,90	FI-REDSO-42/35L-V-W3-DKO		

¹ Approximate dimension in assembled condition.

² Weight excluding cutting ring and union nut.

³ Standard scope of delivery: Fitting body only.

Standard seal material is FKM (Viton®).

Ordering Codes

***FI-REDSO*-10/*08*L*-V*-W3*-DKO*-MS**

* Straight Reducer for Tube Ends with 24° Taper / O-Ring (DKO) **FI-REDSO**

* Outside Tube Diameter D1 (in mm) **-10**

* Outside Tube Diameter D2 (in mm) **08**

* Series Light Series (pages 144/145) **L**
Heavy Series (pages 146/147) **S**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nut and O-ring **-DKO**

Fitting body supplied with cutting ring and union nut **-MS**

Fitting body supplied with soft-sealing cutting ring and union nut **-MSV**

Connecting Parts



Cutting Ring
Type **FI-DS** Page 28



Soft-Sealing Cutting Ring
Type **FI-WDDS** Page 29



Support Sleeve
Type **FI-VH** Page 31



STAUFF Form EVO Sealing Ring
Type **FI-FD** Page 32



Union Nut
Type **FI-M** Page 33



37° Flared Tube Fitting Set
Type **FI-AB** Page 37



Spare Parts / Accessories



O-Ring
Type **O-RING** Page 239



Straight Reducer for Tube Ends with 24° Taper / O-Ring Type FI-REDSO - Series S



Ordering Codes

FI-REDSO-10/*08*S*-V*-W3*-DKO*-MS

* Straight Reducer for Tube Ends with 24° Taper / O-Ring (DKO) **FI-REDSO**

* Outside Tube Diameter D1 (in mm) **-10**

* Outside Tube Diameter D2 (in mm) **08**

* Series Light Series (pages 144/145) **L**
Heavy Series (pages 146/147) **S**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nut and O-ring **-DKO**

Fitting body supplied with cutting ring and union nut **-MS**

Fitting body supplied with soft-sealing cutting ring and union nut **-MSV**

Series	Tube OD mm	PN bar	Dimensions mm									Weight kg ca. per 100	Ordering Codes ³
	D1	D2	D3	D4	L	L1 ¹	L2	S1	S2	S3			
S	8	6	800	4	4	34	42	27	14	19	17	4,46	FI-REDSO-08/06S-V-W3-DKO
	10	6	800	4	4	34,5	42,5	27,5	17	22	17	5,93	FI-REDSO-10/06S-V-W3-DKO
	10	8	800	5	5	34,5	42,5	27,5	17	22	19	6,07	FI-REDSO-10/08S-V-W3-DKO
	12	6	630	4	4	37	48	30	19	24	17	7,96	FI-REDSO-12/06S-V-W3-DKO
	12	8	630	5	5	37	48	30	19	24	19	8,04	FI-REDSO-12/08S-V-W3-DKO
	12	10	630	7	7	37	48	29,5	19	24	22	7,90	FI-REDSO-12/10S-V-W3-DKO
	14	6	630	4	4	38,5	47	31,5	22	27	17	10,46	FI-REDSO-14/06S-V-W3-DKO
	14	8	630	5	5	38,5	47	31,5	22	27	19	10,53	FI-REDSO-14/08S-V-W3-DKO
	14	10	630	7	7	37,5	47	30	22	27	22	10,12	FI-REDSO-14/10S-V-W3-DKO
	14	12	630	8	8	38,5	49	31	22	27	24	10,44	FI-REDSO-14/12S-V-W3-DKO
	16	6	630	4	11	39	49	32	22	30	17	10,79	FI-REDSO-16/06S-V-W3-DKO
	16	8	630	5	11	39	49	31,5	22	30	19	11,04	FI-REDSO-16/08S-V-W3-DKO
	16	10	630	7	7	39	49	31,5	22	30	22	7,67	FI-REDSO-16/10S-V-W3-DKO
	16	12	630	8	8	39	49	31,5	22	30	24	12,07	FI-REDSO-16/12S-V-W3-DKO
	16	14	630	10	10	41	52	33	24	30	27	12,64	FI-REDSO-16/14S-V-W3-DKO
S / L	16	15	400	11	11	39	48	31,5	24	30	27	11,66	FI-REDSO-16S/15L-V-W3-DKO
	20	6	420	4	14	43	54	36	27	36	17	17,16	FI-REDSO-20/06S-V-W3-DKO
	20	8	420	5	14	43	54	36	27	36	19	17,61	FI-REDSO-20/08S-V-W3-DKO
	20	10	420	7	14	43	54	35,5	27	36	22	17,49	FI-REDSO-20/10S-V-W3-DKO
	20	12	420	8	14	43	54	35,5	27	36	24	17,76	FI-REDSO-20/12S-V-W3-DKO
S / L	20	14	420	10	14	45	56,5	37	27	36	27	19,83	FI-REDSO-20/14S-V-W3-DKO
	20	15	400	12	12	43	52,5	35,5	27	36	30	18,38	FI-REDSO-20S/15L-V-W3-DKO
S / L	20	16	420	12	12	45	56	36,5	27	36	30	19,34	FI-REDSO-20/16S-V-W3-DKO
	20	18	400	14	14	43	53	35,5	27	36	32	18,10	FI-REDSO-20S/18L-V-W3-DKO

¹ Approximate dimension in assembled condition.

² Weight excluding cutting ring and union nut.

³ Standard scope of delivery: Fitting body only.

Standard seal material is FKM (Viton®).

Connecting Parts



Cutting Ring
Type **FI-DS** Page 28



Soft-Sealing Cutting Ring
Type **FI-WDDS** Page 29



Support Sleeve
Type **FI-VH** Page 31



STAUFF Form EVO Sealing Ring
Type **FI-FD** Page 32



Union Nut
Type **FI-M** Page 33



37° Flared Tube Fitting Set
Type **FI-AB** Page 37



Spare Parts / Accessories



O-Ring
Type **O-RING** Page 239



Straight Reducer for Tube Ends with 24° Taper / O-Ring Type FI-REDSO - Series S



Series	Tube OD mm		PN bar	Dimensions mm							Weight kg ca. per 100	Ordering Codes ³	
	D1	D2		D3	D4	L	L ¹	L2	S1	S2			S3
S	25	6	420	4	18	45,5	57,5	38,5	36	46	17	29,87	FI-REDSO-25/06S-V-W3-DKO
	25	8	420	5	18	45,5	57,5	38,5	36	46	19	30,39	FI-REDSO-25/08S-V-W3-DKO
	25	10	420	7	18	45,5	57,5	38,5	36	46	22	16,95	FI-REDSO-25/10S-V-W3-DKO
	25	12	420	8	18	45,5	57,5	38,5	36	46	24	30,41	FI-REDSO-25/12S-V-W3-DKO
	25	14	420	10	18	47,5	59	39,5	36	46	27	30,95	FI-REDSO-25/14S-V-W3-DKO
S / L	25	16	420	12	18	47,5	59,5	39	36	46	30	30,29	FI-REDSO-25/16S-V-W3-DKO
	25	18	400	15	18	45,5	55,5	38	36	46	32	30,54	FI-REDSO-25S/18L-V-W3-DKO
	25	20	420	16	16	49,5	61,5	39	36	46	36	32,97	FI-REDSO-25/20S-V-W3-DKO
	30	6	420	4	22	51	64	44	41	50	17	37,93	FI-REDSO-30/06S-V-W3-DKO
	30	8	420	5	22	51	64	44	41	50	19	31,17	FI-REDSO-30/08S-V-W3-DKO
	30	10	420	7	22	51	64	43,5	41	50	22	38,28	FI-REDSO-30/10S-V-W3-DKO
	30	12	420	8	22	51	64	43,5	41	50	24	38,65	FI-REDSO-30/12S-V-W3-DKO
	30	14	420	10	22	53	64,5	45	41	50	27	38,88	FI-REDSO-30/14S-V-W3-DKO
	30	16	420	12	22	53	66	44,5	41	50	30	38,59	FI-REDSO-30/16S-V-W3-DKO
	30	20	420	16	22	55	58	44,5	41	50	36	39,86	FI-REDSO-30/20S-V-W3-DKO
	30	25	420	20	20	57	70	45	41	50	46	42,96	FI-REDSO-30/25S-V-W3-DKO
	38	6	420	4	30	54,5	69,5	47,5	50	60	17	55,50	FI-REDSO-38/06S-V-W3-DKO
	38	8	420	5	30	54,5	69,5	47,5	50	60	19	55,50	FI-REDSO-38/08S-V-W3-DKO
	38	10	420	7	30	54,5	69,5	47	50	60	22	56,40	FI-REDSO-38/10S-V-W3-DKO
	38	12	420	8	30	54,5	69,5	47	50	60	24	55,50	FI-REDSO-38/12S-V-W3-DKO
	38	14	420	10	30	56,5	68	48,5	50	60	27	62,87	FI-REDSO-38/14S-V-W3-DKO
	38	16	420	12	30	56,5	71,5	48	50	60	30	55,80	FI-REDSO-38/16S-V-W3-DKO
	38	20	420	16	30	58,5	73,5	48	50	60	36	57,40	FI-REDSO-38/20S-V-W3-DKO
	38	25	420	20	30	60,5	75,5	48,5	50	60	46	59,30	FI-REDSO-38/25S-V-W3-DKO
	38	30	420	25	25	62,5	77,5	49	50	60	50	63,70	FI-REDSO-38/30S-V-W3-DKO

¹ Approximate dimension in assembled condition.

² Weight excluding cutting ring and union nut.

³ Standard scope of delivery: Fitting body only.

Standard seal material is FKM (Viton®).

Ordering Codes

***FI-REDSO*-10/*08*S*-V*-W3*-DKO*-MS**

* Straight Reducer for Tube Ends with 24° Taper / O-Ring (DKO) **FI-REDSO**

* Outside Tube Diameter D1 (in mm) **-10**

* Outside Tube Diameter D2 (in mm) **08**

* Series Light Series (pages 144/145) **L**
Heavy Series (pages 146/147) **S**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nut and O-ring **-DKO**

Fitting body supplied with cutting ring and union nut **-MS**

Fitting body supplied with soft-sealing cutting ring and union nut **-MSV**

Connecting Parts


Cutting Ring
Type **FI-DS** Page 28

Soft-Sealing Cutting Ring
Type **FI-WDDS** Page 29

Support Sleeve
Type **FI-VH** Page 31

STAUFF Form EVO Sealing Ring
Type **FI-FD** Page 32



Union Nut
Type **FI-M** Page 33

37° Flared Tube Fitting Set
Type **FI-AB** Page 37

Spare Parts / Accessories


O-Ring
Type **O-RING** Page 239


Distance Adaptors with 24° Taper / O-Ring Type FI-REDSO • Series L / S



Ordering Codes

FI-REDSO-08*L*-V*-W3*-DKO*-MS

* Distance Adaptors with 24° Taper /
O-Ring (DKO)

FI-REDSO

* Outside Tube Diameter D1/D2 (in mm)

-08

* Series
Light Series

L

Heavy Series

S

* Seal Material
FKM (Viton®)

-V

* Material Code
Steel, zinc/nickel-plated

-W3

Please contact STAUFF for alternative
materials and surface finishings.

* Assembling / Kitting
Fitting body supplied with
swivel nut and O-ring

-DKO

Fitting body supplied with
cutting ring and union nut

-MS

Fitting body supplied with
soft-sealing cutting ring
and union nut

-MSV

Series	Tube OD mm		PN bar	Dimensions mm									Weight kg ca. per 100	Ordering Codes ³
	D1	D2		D3	D4	L	L1 ¹	L2	S1	S2	S3			
L	6	6	500	3	3	43	51	36	12	14	14	4,33	FI-RESD-06L-V-W3-DKO	
	8	8	500	5	5	43	51	36	14	17	17	4,63	FI-RESD-08L-V-W3-DKO	
	10	10	500	6,5	6,5	43	51	36	17	19	19	6,15	FI-RESD-10L-V-W3-DKO	
	12	12	400	8	8	43	52	36	19	22	22	7,85	FI-RESD-12L-V-W3-DKO	
	15	15	400	11	11	43	52	36	24	27	27	12,05	FI-RESD-15L-V-W3-DKO	
	18	18	400	13	13	43,5	53	36	27	32	32	15,61	FI-RESD-18L-V-W3-DKO	
	22	22	250	17	17	47,5	58,5	40	32	36	36	21,63	FI-RESD-22L-V-W3-DKO	
	28	28	250	23	23	47,5	58,5	40	41	41	41	27,45	FI-RESD-28L-V-W3-DKO	
	35	35	250	24	24	60,5	73,5	50	46	50	50	53,4	FI-RESD-35L-V-W3-DKO	
	42	42	250	35	35	71	84,5	60	55	60	60	77,7	FI-RESD-42L-V-W3-DKO	
S	6	6	800	3	3	43	51	36	14	17	17	4,91	FI-RESD-06S-V-W3-DKO	
	8	8	800	4	4	43	51	36	17	19	19	6,64	FI-RESD-08S-V-W3-DKO	
	10	10	800	6,5	6,5	43,5	53	36	19	22	22	8,18	FI-RESD-10S-V-W3-DKO	
	12	12	630	8	8	43,5	54	36	22	24	24	10,28	FI-RESD-12S-V-W3-DKO	
	14	14	630	9	9	48	59	40	24	27	27	13,75	FI-RESD-14S-V-W3-DKO	
	16	16	630	11	11	48,5	60	40	27	30	30	16,53	FI-RESD-16S-V-W3-DKO	
	20	20	420	14	14	56,5	69	46	32	36	36	26,97	FI-RESD-20S-V-W3-DKO	
	25	25	420	18	18	62	75	50	41	46	46	46,37	FI-RESD-25S-V-W3-DKO	
	30	30	420	22	22	69,5	84,5	56	46	50	50	60	FI-RESD-30S-V-W3-DKO	
38	38	420	32	32	76	93	60	55	60	60	82,5	FI-RESD-38S-V-W3-DKO		

¹ Approximate dimension in assembled condition.

² Weight excluding cutting ring and union nut.

³ Standard scope of delivery: Fitting body only.

Standard seal material is FKM (Viton®).

Connecting Parts



Cutting Ring
Type **FI-DS**

Page 28



Soft-Sealing Cutting Ring
Type **FI-WDDS**

Page 29



Support Sleeve
Type **FI-VH**

Page 31



STAUFF Form EVO Sealing Ring
Type **FI-FD**

Page 32



Union Nut
Type **FI-M**

Page 33



37° Flared Tube Fitting Set
Type **FI-AB**

Page 37


Spare Parts / Accessories



O-Ring
Type **O-RING**

Page 239






H



Adjustable Elbow (90°) with 24° Taper / O-Ring Type FI-EWD ▪ Series L / S



Ordering Codes

FI-EWD-10*L*-V*-W3*-DKO*-MS

* Adjustable Elbow (90°)
with 24° Taper / O-Ring (DKO) **FI-EWD**

* Outside Tube Diameter D1 (in mm) **-10**

* Series Light Series **L**
Heavy Series **S**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nut and O-ring **-DKO**
Fitting body supplied with cutting ring and union nut **-MS**
Fitting body supplied with soft-sealing cutting ring and union nut **-MSV**

Series	Tube OD mm D1	PN bar	Dimensions									Weight kg ca. per 100	Ordering Codes ³
			mm D2	L	L1 ¹	L2	L3	S1	S2	S3			
L	6	500	4	19	27	12	26	12	14	14	4,00	FI-EWD-06L-V-W3-DKO	
	8	500	6	21	29	14	27,5	12	17	17	4,03	FI-EWD-08L-V-W3-DKO	
	10	500	8	22	30	15	29	14	19	19	5,36	FI-EWD-10L-V-W3-DKO	
	12	400	10	24	32	17	29,5	17	22	22	7,60	FI-EWD-12L-V-W3-DKO	
	15	400	12	28	36	21	32,5	19	27	27	12,50	FI-EWD-15L-V-W3-DKO	
	18	400	15	31	40	23,5	35,5	24	32	32	18,23	FI-EWD-18L-V-W3-DKO	
	22	400	19	35	44	27,5	38,5	27	36	36	24,57	FI-EWD-22L-V-W3-DKO	
	28	250	24	38	47	30,5	41,5	36	41	41	34,95	FI-EWD-28L-V-W3-DKO	
	35	250	30	45	56	34,5	51	41	50	50	56,50	FI-EWD-35L-V-W3-DKO	
	42	250	36	51	63	40	56	50	60	60	85,10	FI-EWD-42L-V-W3-DKO	
S	6	800	4	23	31	16	27	12	17	17	4,67	FI-EWD-06S-V-W3-DKO	
	8	800	5	24	32	17	27,5	14	19	19	6,29	FI-EWD-08S-V-W3-DKO	
	10	800	7	25	34	17,5	30	17	22	22	8,58	FI-EWD-10S-V-W3-DKO	
	12	630	8	29	38	21,5	31	17	24	24	11,02	FI-EWD-12S-V-W3-DKO	
	14	630	10	30	40	22	35	19	27	27	14,34	FI-EWD-14S-V-W3-DKO	
	16	630	12	33	43	24,5	36,5	24	30	30	19,26	FI-EWD-16S-V-W3-DKO	
	20	420	16	37	48	26,5	44,5	27	36	36	29,86	FI-EWD-20S-V-W3-DKO	
	25	420	20	42	54	30	50	36	46	46	53,20	FI-EWD-25S-V-W3-DKO	
	30	420	25	49	62	35,5	55	41	50	50	72,50	FI-EWD-30S-V-W3-DKO	
	38	420	32	57	72	41	63	50	60	60	109,40	FI-EWD-38S-V-W3-DKO	

¹ Approximate dimension in assembled condition.

² Weight excluding cutting ring and union nut.

³ Standard scope of delivery: Fitting body only.



Typical application with a
Straight Male Stud Fitting FI-GE-...

Standard seal material is FKM (Viton®).

Connecting Parts



Cutting Ring
Type **FI-DS** Page 28



Soft-Sealing Cutting Ring
Type **FI-WDDS** Page 29



Support Sleeve
Type **FI-VH** Page 31



STAUFF Form EVO Sealing Ring
Type **FI-FD** Page 32



Union Nut
Type **FI-M** Page 33




37° Flared Tube Fitting Set
Type **FI-AB** Page 37

Spare Parts / Accessories



O-Ring
Type **O-RING** Page 239





Adjustable Elbow (45°) with 24° Taper / O-Ring Type FI-EVD ▪ Series L / S



Series	Tube OD mm D1	PN bar	Dimensions									Weight kg.ca. per 100	Ordering Codes ³
			D2	L	L1 ¹	L2	L3	S1	S2	S3			
L	6	500	4	16	24	9	26	14	14	14	4,63	FI-EVD-06L-V-W3-DKO	
	8	500	6	19	27	12	27,5	14	17	17	4,72	FI-EVD-08L-V-W3-DKO	
	10	500	8	19	27	12	29	19	19	19	7,56	FI-EVD-10L-V-W3-DKO	
	12	400	10	21	29	14	29,5	19	22	22	8,66	FI-EVD-12L-V-W3-DKO	
	15	400	12	24	32	17	32,5	22	27	27	12,96	FI-EVD-15L-V-W3-DKO	
	18	400	15	24	33	17	35,5	27	32	32	20,64	FI-EVD-18L-V-W3-DKO	
	22	400	19	26	35	19	38,5	30	36	36	26,41	FI-EVD-22L-V-W3-DKO	
	28	250	24	30,5	40	23	41,5	36	41	41	34,69	FI-EVD-28L-V-W3-DKO	
	35	250	30	37	48	27	51	50	50	50	79,60	FI-EVD-35L-V-W3-DKO	
	42	250	36	37	49	26	56	50	60	60	83,20	FI-EVD-42L-V-W3-DKO	
	S	6	630	4	16	24	9	27	14	17	17	4,90	FI-EVD-06S-V-W3-DKO
		8	630	5	19	27	12	27,5	19	19	19	5,17	FI-EVD-08S-V-W3-DKO
10		630	7	21	30	13	30	19	22	22	9,44	FI-EVD-10S-V-W3-DKO	
12		630	8	24	33	17	31	22	24	24	12,90	FI-EVD-12S-V-W3-DKO	
14		400	10	24	34	16	33,5	22	27	27	14,4	FI-EVD-14S-V-W3-DKO	
16		400	12	24	34	16	36,5	27	30	30	16,76	FI-EVD-16S-V-W3-DKO	
20		400	16	26,5	37,5	16	44,5	30	36	36	30,72	FI-EVD-20S-V-W3-DKO	
25		400	20	30,5	42,5	19	50	36	46	46	50,10	FI-EVD-25S-V-W3-DKO	
30		400	25	37	50	24	55	50	50	50	92,90	FI-EVD-30S-V-W3-DKO	
38		315	32	37	52	21	63	50	60	60	98,50	FI-EVD-38S-V-W3-DKO	

¹ Approx.imate dimension in assembled condition.

²Weight excluding cutting ring and union nut.

³ Standard scope of delivery: Fitting body only.



Typical application with a
Straight Male Stud Fitting FI-GE-...

Standard seal material is FKM (Viton®).

Ordering Codes

***FI-EVD*-10*L*-V*-W3*-DK0*-MS**

* Adjustable Elbow (45°)
with 24° Taper / O-Ring (DKO)

* Outside Tube Diameter D1 (in mm) -10

* Series	Light Series	L
	Heavy Series	S

* Seal Material	FKM (Viton®)	-V
-----------------	--------------	----

* Material Code Steel, zinc/nickel-plated -W3

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nut and O-ring -DKO

Fitting body supplied with
cutting ring and union nut

Fitting body supplied with
soft-sealing cutting ring
and union nut **-MSV**

Connecting Parts

Cutting Ring
Type **FI-DS** Page 28Soft-Sealing Cutting Ring
Type **FI-WDDS** Page 29Support Sleeve
Type **FI-VH** Page 31


STAUFF Form EVO Sealing Ring
Type **FI-FD** Page 32

Union Nut
Type **FI-M** Page 3337° Flared Tube Fitting Set
Type **FI-AB** Page 37

Spare Parts / Accessories

O-Ring
Type **O-RING** Page 239

Adjustable Branch Tee with 24° Taper / O-Ring (DKO) Type FI-ETD • Series L / S



Ordering Codes

FI-ETD-10*L*-V*-W3*-DKO*-MS

* Adjustable Branch Tee with 24° Taper / O-Ring (DKO) **FI-ETD**

* Outside Tube Diameter D1 (in mm) **-10**

* Series Light Series **L**
Heavy Series **S**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative materials and surface finishings.

* Assembling / Kitting Fitting body supplied with swivel nut and O-ring **-DKO**
Fitting body supplied with cutting ring and union nut **-MS**
Fitting body supplied with soft-sealing cutting ring and union nut **-MSV**

Series	Tube OD mm D1	PN bar	Dimensions mm							Weight kg ca. per 100			Ordering Codes ³
			D2	L	L1 ¹	L2	L3	S1	S2	S3			
L	6	500	4	19	27	12	26	12	14	14	3,02		FI-ETD-06L-V-W3-DKO
	8	500	6	21	29	14	27,5	12	17	17	4,82		FI-ETD-08L-V-W3-DKO
	10	500	8	22	30	15	29	14	19	19	6,27		FI-ETD-10L-V-W3-DKO
	12	400	10	24	32	17	29,5	17	22	22	8,73		FI-ETD-12L-V-W3-DKO
	15	400	12	28	36	21	32,5	19	27	27	14,55		FI-ETD-15L-V-W3-DKO
	18	400	15	31	40	23,5	35,5	24	32	32	20,89		FI-ETD-18L-V-W3-DKO
	22	400	19	35	44	27,5	38,5	27	36	36	28,27		FI-ETD-22L-V-W3-DKO
	28	250	24	38	47	30,5	41,5	36	41	41	39,85		FI-ETD-28L-V-W3-DKO
	35	250	30	45	56	34,5	51	41	50	50	64,20		FI-ETD-35L-V-W3-DKO
	42	250	36	51	63	40	56	50	60	60	94,90		FI-ETD-42L-V-W3-DKO
S	6	800	4	23	31	16	27	12	17	17	5,99		FI-ETD-06S-V-W3-DKO
	8	800	5	24	32	17	27,5	14	19	19	7,80		FI-ETD-08S-V-W3-DKO
	10	800	7	25	34	17,5	30	17	22	22	10,60		FI-ETD-10S-V-W3-DKO
	12	630	8	29	38	21,5	31	17	24	24	13,63		FI-ETD-12S-V-W3-DKO
	14	630	10	30	40	22	35	19	27	27	17,37		FI-ETD-14S-V-W3-DKO
	16	630	12	33	43	24,5	36,5	24	30	30	22,95		FI-ETD-16S-V-W3-DKO
	20	420	16	37	48	26,5	44,5	27	36	36	35,51		FI-ETD-20S-V-W3-DKO
	25	420	20	42	54	30	50	36	46	46	62,40		FI-ETD-25S-V-W3-DKO
	30	420	25	49	62	35,5	55	41	50	50	85,60		FI-ETD-30S-V-W3-DKO
	38	420	32	57	72	41	63	50	60	60	128,10		FI-ETD-38S-V-W3-DKO

¹ Approximate dimension in assembled condition.

² Weight excluding cutting ring and union nut.

³ Standard scope of delivery: Fitting body only.



Typical application with a
Straight Male Stud Fitting FI-GE-...

Standard seal material is FKM (Viton®).


Connecting Parts

	Cutting Ring Type FI-DS	Page 28
	Soft-Sealing Cutting Ring Type FI-WDDS	Page 29
	Support Sleeve Type FI-VH	Page 31
	STAUFF Form EVO Sealing Ring Type FI-FD	Page 32
	Union Nut Type FI-M	Page 33
	37° Flared Tube Fitting Set Type FI-AB	Page 37

Spare Parts / Accessories

	O-Ring Type O-RING	Page 239
--	------------------------------	----------





Adjustable Barrel Tee with 24° Taper / O-Ring (DKO) Type FI-ELD - Series L / S



Series	Tube OD mm D1	PN bar	Dimensions mm D2	L	L ¹	L2	L3	S1	S2	S3	Weight kg ca. per 100	Ordering Codes ³
L	6	500	4	19	27	12	26	12	14	14	4,79	FI-ELD-06L-V-W3-DK0
	8	500	6	21	29	14	27,5	12	17	17	4,88	FI-ELD-08L-V-W3-DK0
	10	500	8	22	30	15	29	14	19	19	6,45	FI-ELD-10L-V-W3-DK0
	12	400	10	24	32	17	29,5	17	22	22	8,58	FI-ELD-12L-V-W3-DK0
	15	400	12	28	36	21	32,5	19	27	27	14,60	FI-ELD-15L-V-W3-DK0
	18	400	15	31	40	23,5	35,5	24	32	32	20,83	FI-ELD-18L-V-W3-DK0
	22	400	19	35	44	27,5	38,5	27	36	36	28,02	FI-ELD-22L-V-W3-DK0
	28	250	24	38	47	30,5	41,5	36	41	41	39,66	FI-ELD-28L-V-W3-DK0
	35	250	30	45	56	34,5	51	41	50	50	64,60	FI-ELD-35L-V-W3-DK0
	42	250	36	51	63	40	56	50	60	60	94,70	FI-ELD-42L-V-W3-DK0
S	6	800	4	23	31	16	27	12	17	17	6,04	FI-ELD-06S-V-W3-DK0
	8	800	5	24	32	17	27,5	14	19	19	8,14	FI-ELD-08S-V-W3-DK0
	10	800	7	25	34	17,5	30	17	22	22	10,53	FI-ELD-10S-V-W3-DK0
	12	630	8	29	38	21,5	31	17	24	24	13,80	FI-ELD-12S-V-W3-DK0
	14	630	10	30	40	22	35	19	27	27	20,27	FI-ELD-14S-V-W3-DK0
	16	630	12	33	43	24,5	36,5	24	30	30	23,13	FI-ELD-16S-V-W3-DK0
	20	420	16	37	48	26,5	44,5	27	36	36	35,53	FI-ELD-20S-V-W3-DK0
	25	420	20	42	54	30	50	36	46	46	61,90	FI-ELD-25S-V-W3-DK0
	30	420	25	49	62	35,5	55	41	50	50	85,10	FI-ELD-30S-V-W3-DK0
	38	420	32	57	72	41	63	50	60	60	128,00	FI-ELD-38S-V-W3-DK0

¹ Approximate dimension in assembled condition.

² Weight excluding cutting ring and union nut.

³ Standard scope of delivery: Fitting body only.

Standard seal material is FKM (Viton®).


Typical application with a
Straight Male Stud Fitting FI-GE-...

Ordering Codes

***FI-ELD*-10*L*-V*-W3*-DK0*-MS**

* Adjustable Barrel Tee
with 24° Taper / O-Ring (DKO) **FI-ELD**

* Outside Tube Diameter D1 (in mm) **-10**

* Series Light Series **L**
Heavy Series **S**

* Seal Material FKM (Viton®) **-V**

* Material Code Steel, zinc/nickel-plated **-W3**

Please contact STAUFF for alternative
materials and surface finishings.

* Assembling / Kitting Fitting body supplied with
swivel nut and O-ring **-DK0**

Fitting body supplied with
cutting ring and union nut **-MS**

Fitting body supplied with
soft-sealing cutting ring
and union nut **-MSV**

Connecting Parts

 Cutting Ring
Type **FI-DS** Page 28

 Soft-Sealing Cutting Ring
Type **FI-WDDS** Page 29

 Support Sleeve
Type **FI-VH** Page 31

 STAUFF Form EVO Sealing Ring
Type **FI-FD** Page 32

 Union Nut
Type **FI-M** Page 33

 37° Flared Tube Fitting Set
Type **FI-AB** Page 37

Spare Parts / Accessories

 O-Ring
Type **O-RING** Page 239
