



TE Internal #: 1-1337562-0

Between Series Adapter, Straight, FME Side A, Plug Side A, BNC Side B, Plug Side B, 1 Position

[View on TE.com >](#)

Connectors > Connector Accessories > Connector Adapters & Connector Savers



Connector Interface Adapter Type: **Between Series Adapter**

Body Orientation: **Straight**

Side A Interface: **FME**

Side A Gender: **Plug**

Side B Interface: **BNC**

Features

Product Type Features

Connector Interface Adapter Type	Between Series Adapter
Side A Interface	FME
Side A Gender	Plug
Side B Interface	BNC
Side B Gender	Plug
Connector System	Wire-to-Wire
Sealable	No

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Plating Material	Nickel
Body Material	Brass

Contact Features



RF Connector Center Contact Material	Brass
RF Connector Center Contact Plating Material	Gold (Au)

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Housing Features

Body Orientation	Straight
------------------	----------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Operating Frequency	2 GHz
Circuit Application	Power & Signal

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-1337552-0

FME Str Jk Hex Nickel Pltd RG58C/U,
141A

Customers Also Bought



TE Part #163307-4

MATE-N-LOK PIN



TE Part #180905

FF 250 REC HSG 1P NYLON NAT



TE Part #163007

FF 250 REC HSG 8P NYLON CLEAR



TE Part #6-160449-2

FF 250 REC 1.0-2.5MM2 TPPB LP




TE Part #926539-6

250 FASTON HSG. REC. 1P NATURAL



TE Part #160458-2

FF 250 TAB 18-16AWG TPPB LP



TE Part #180924

FF 250 TAB HSG 2P NYLON NAT



TE Part #1-480319-0

02P CMNL CAP HSG NATL



TE Part #1393315-9

V23132B2002A200=HCR



TE Part #163306-4

SOCKET M-N-L

Documents

Product Drawings

FME Str Plg-BNCP Adp Nickel Pltd

English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1337562-0_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1337562-0_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1337562-0_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RF Between Series Adapters

English