**K3G146-AC15-01**

# EC centrifugal fan combination

forward-curved

with housing



**ebm-papst Mulfingen GmbH & Co. KG**
Bachmühle 2 · D-74673 Mulfingen
Phone +49 7938 81-0
Fax +49 7938 81-110
info1@de.ebmpapst.com
www.ebmpapst.com

Limited partnership · Headquarters Mulfingen
Amtsgericht (court of registration) Stuttgart · HRA 590344

General partner Elektrobau Mulfingen GmbH · Headquarters Mulfingen
Amtsgericht (court of registration) Stuttgart · HRB 590142

## Nominal data

| | |
|---|---|
| **Type** | **K3G146-AC15-01** |
| **Motor** | **M3G055-DF** |

| | | |
|---|---|---|
| Phase | | 1~ |
| Nominal voltage | VAC | 230 |
| Frequency | Hz | 50/60 |
| Method of obtaining data | | ml |
| Speed (rpm) | $min^{-1}$ | 910 |
| Power consumption | W | 60 |
| Current draw | A | 0.5 |
| Min. back pressure | Pa | 25 |
| Min. back pressure | in. wg | 0.1 |
| Min. ambient temperature | °C | -25 |
| Max. ambient temperature | °C | 50 |

ml = Max. load · me = Max. efficiency · fa = Free air · cs = Customer specification · ce = Customer equipment
Subject to change

# EC centrifugal fan combination

forward-curved

with housing

## Technical description

| | |
|---|---|
| **Weight** | 3.4 kg |
| **Size** | 146 mm |
| **Motor size** | 55 |
| **Rotor surface** | Galvanized |
| **Electronics housing material** | PP plastic, black |
| **Impeller material** | PP plastic |
| **Housing material** | PP plastic, black |
| **Motor suspension** | Motor vibration-damped on both sides |
| **Direction of rotation** | Clockwise, viewed toward rotor |
| **Degree of protection** | Motor IP44, electronics IP20; installation- and position-dependent |
| **Insulation class** | "F" |
| **Moisture (F) / Environmental (H) protection class** | H0+ |
| **Max. permitted ambient temp. for motor (transport/storage)** | + 80 °C |
| **Min. permitted ambient temp. for motor (transport/storage)** | - 40 °C |
| **Installation position** | Any |
| **Condensation drainage holes** | None, open rotor |
| **Mode** | S1 |
| **Motor bearing** | Ball bearing |
| **Technical features** | - Output 10 VDC, max. 1.1 mA<br>- Tach output<br>- Motor current limitation<br>- Soft start<br>- Control input 0-10 VDC / PWM<br>- Control interface with SELV potential safely disconnected from supply<br>- Thermal overload protection for motor |
| **EMC immunity to interference** | According to EN 61000-6-2 (industrial environment) |
| **EMC circuit feedback** | According to EN 61000-3-2/3 |
| **EMC interference emission** | According to EN 61000-6-3 (household environment) |
| **Touch current according to IEC 60990 (measuring circuit Fig. 4, TN system)** | <= 3.5 mA |
| **Electrical hookup** | Plug |
| **Motor protection** | Thermal switch auto reset, internally connected |
| **With cable** | Variable |
| **Protection class assignment** | I; If a protective earth is connected by the customer<br>This component for installation may have several local protection classes. This information relates to this component's basic design.<br>The final protection class is based on the component's intended installation and connection. |
| **Conformity with standards** | EN 60034-1; EN 60204-1; EN 60335-1; CE |
| **Comment on CE** | Ecodesign Directive 2009/125/EC + Fan Directive (EC) No. 327/2011 does not apply, as power consumption <125W. |
| **Approval** | UL 1004-7 + 60730-1; CSA C22.2 No. 77 + CAN/CSA-E60730-1 |




ebm-papst Mulfingen GmbH & Co. KG · Bachmühle 2 · D-74673 Mulfingen · Phone +49 (0) 7938 81-0 · Fax +49 (0) 7938 81-110 · info1@de.ebmpapst.com · www.ebmpapst.com

# EC centrifugal fan combination

forward-curved

with housing

## Product drawing




| | |
|---|---|
| 1 | Header Molex Micro Fit 3.0 04365 00400 (pluggable with 04364 50400) |
| 1.1 | 10V |
| 1.2 | Tach |
| 1.3 | 0-10V lin. / PWM |
| 1.4 | GND |
| 2 | Connector Lumberg 3642 03 K01 (pluggable with 3626 03 K01) |
| 2.1 | PE |
| 2.2 | L |
| 2.3 | N |
| 3 | 8x sheet metal nut for thread EN ISO 1478-ST4.8 (min. screw length 14.5 mm plus material thickness of attachment) |




ebm-papst Mulfingen GmbH & Co. KG · Bachmühle 2 · D-74673 Mulfingen · Phone +49 (0) 7938 81-0 · Fax +49 (0) 7938 81-110 · info1@de.ebmpapst.com · www.ebmpapst.com

# EC centrifugal fan combination

forward-curved

with housing

## Connection diagram




| No. | Conn. | Designation | Color | Function/assignment |
|---|---|---|---|---|
| CON10 | 10.1 | PE | green/yellow | Protective earth |
| CON10 | 10.2 | L | black | Power supply 230 VAC, 50-60 Hz, see nameplate for voltage range |
| CON10 | 10.3 | N | blue | Neutral conductor |
| CON11 | 11.1 | 10 V/max. 1.1 mA | red | Voltage output 10 V, 1.1 mA, electrically isolated, not short-circuit-proof |
| CON11 | 11.2 | Tach | white | Tach output: Open collector, 1 pulse per revolution, electrically isolated, Isink max = 10 mA |
| CON11 | 11.3 | 0-10 V PWM | yellow | Control input 0-10 V or PWM, electrically isolated |
| CON11 | 11.4 | GND | blue | GND connection for control interface |




ebm-papst Mulfingen GmbH & Co. KG · Bachmühle 2 · D-74673 Mulfingen · Phone +49 (0) 7938 81-0 · Fax +49 (0) 7938 81-110 · info1@de.ebmpapst.com · www.ebmpapst.com

# EC centrifugal fan combination

forward-curved

with housing

## Curves: Air performance 50 Hz




ρ = 1.15 kg/m³ ± 2 %

Measurement: LU-132605-1
Measurement: LU-132537-1
Measurement: LU-132538-1
Measurement: LU-132540-1

Air performance measured according to ISO 5801 installation category A. For detailed information on the measurement setup, contact ebm-papst. Intake sound level: Sound power level according to ISO 13347 / sound pressure level measured at 1 m distance from fan axis. The values given are valid under the specified measuring conditions and may vary due to conditions of installation. For deviations from the standard configuration, the parameters have to be checked on the installed unit.

## Measured values

| | Wired | U | f | n | $P_{ed}$ | I | $LpA_{in}$ | $LwA_{in}$ | $q_V$ | $p_{fs}$ | $q_V$ | $p_{fs}$ |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| | | V | Hz | $min^{-1}$ | W | A | dB(A) | dB(A) | $m^3/h$ | Pa | cfm | in. wg |
| 1 | 1~ | 230 | 50 | 910 | 60 | 0.50 | 45 | 58 | 1100 | 25 | 645 | 0.10 |
| 2 | 1~ | 230 | 50 | 1030 | 52 | 0.48 | 43 | 56 | 890 | 50 | 525 | 0.20 |
| 3 | 1~ | 230 | 50 | 1180 | 41 | 0.38 | 44 | 56 | 570 | 75 | 335 | 0.30 |
| 4 | 1~ | 230 | 50 | 1340 | 31 | 0.29 | 47 | 59 | 305 | 100 | 180 | 0.40 |
| 5 | 1~ | 230 | 50 | 830 | 44 | 0.39 | | | 990 | 21 | 585 | 0.08 |
| 6 | 1~ | 230 | 50 | 920 | 38 | 0.35 | | | 790 | 40 | 465 | 0.16 |
| 7 | 1~ | 230 | 50 | 1045 | 29 | 0.28 | | | 510 | 60 | 300 | 0.24 |
| 8 | 1~ | 230 | 50 | 1170 | 22 | 0.21 | | | 270 | 77 | 160 | 0.31 |
| 9 | 1~ | 230 | 50 | 695 | 25 | 0.24 | | | 825 | 14 | 485 | 0.06 |
| 10 | 1~ | 230 | 50 | 760 | 22 | 0.20 | | | 660 | 28 | 385 | 0.11 |
| 11 | 1~ | 230 | 50 | 855 | 17 | 0.16 | | | 415 | 39 | 245 | 0.16 |
| 12 | 1~ | 230 | 50 | 945 | 13 | 0.12 | | | 215 | 50 | 130 | 0.20 |
| 13 | 1~ | 230 | 50 | 545 | 12 | 0.12 | | | 640 | 9 | 375 | 0.04 |
| 14 | 1~ | 230 | 50 | 595 | 11 | 0.11 | | | 505 | 16 | 300 | 0.06 |
| 15 | 1~ | 230 | 50 | 650 | 9.0 | 0.09 | | | 310 | 22 | 185 | 0.09 |
| 16 | 1~ | 230 | 50 | 710 | 7.0 | 0.08 | | | 160 | 28 | 95 | 0.11 |

Wired = Wiring · U = Voltage · f = Frequency · n = Speed (rpm) · $P_{ed}$ = Power consumption · I = Current draw · $LpA_{in}$ = Sound pressure level intake side · $LwA_{in}$ = Sound power level intake side
$q_V$ = Air flow · $p_{fs}$ = Pressure increase



ebm-papst Mulfingen GmbH & Co. KG · Bachmühle 2 · D-74673 Mulfingen · Phone +49 (0) 7938 81-0 · Fax +49 (0) 7938 81-110 · info1@de.ebmpapst.com · www.ebmpapst.com