

## Features

- Medium Duty
- Industrial castor
- Fixed
- Fixing Plate
- Rubber
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

## RS PRO Castor Wheels

RS Stock No.: 0631155



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description








Grey no-marking rubber wheel 83 Shore A with black thermoplastic material centre. Hub on plain bore. In zinc-chromium plated pressed steel. Assembled with self-locking nut.

## General Specifications

<b>Rotation</b>	Fixed
<b>Weight Class</b>	Medium Duty
<b>Load Capacity (Kg)</b>	50
<b>Load Capacity / 4pcs (Kg)</b>	200
<b>Tyre Material</b>	Rubber
<b>Hub Material</b>	Thermoplastic
<b>Bracket Material</b>	Pressed Steel
<b>Includes Brake</b>	No
<b>Features</b>	Corrosion Resistant, Impact Resistant, Shock Absorbing
<b>Applications</b>	Industrial castor

## Operation Environment Specifications

<b>Operating Temperature (Celsius)</b>	-20° to 80°
--	-------------

						
80x30	100x85	80x60	8,5x12	108	70	90

## Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	100
Wheel / Tread Width (mm)	30
Overall Height (mm)	108
Number of Fixing Holes	4
Fixing Hole Size (mm)	8.5x12
Hub Bearing Type	Plain Bore
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	83
Levelling Extent (mm)	
Offset (mm)	
Castor Weight (Kg)	0.5

### Fixing Centres Specifications

Fixing Centres (mm)	80x60
Fixing Centres Length (mm)	80
Fixing Centres Width (mm)	60

### Fixing Plate Specifications

Fixing Plate Dimensions (mm)	100x85
Fixing Plate Length (mm)	100
Fixing Plate Width (mm)	85