



Datasheet

RS PRO Metric Type Cable Glands, Nickel Plated Brass, IP68, With Locknut

Stock No. 2100611, 2100596, 2100592, 2100602, 2100606, 2100598

EN



Applications

Nickel-plated brass cable glands are robust and extremely suitable for industrial use. They are widely used for New Energy Vehicles, Rail Transit, Wind and Solar, Electric complete set, Automation, TBS, LED and etc.

Specification

Material: Nickel-plated brass
Fixture material: PA (NYLON), UL94V-2
Seal: NBR
O-Ring: EPDM
Working temperature: -40 to 100 degree centigrade

Attributes

RS Article No.	Thread Size	Material	Max. Cable Dia. mm	Min. Cable Dia. mm	GL mm	Spanner Size mm	IP Rating	Minimum Operating Temp.	Maximum Operating Temp.	Locknut Included
2100592	M12x 1.5	Nickel Plated Brass	6.5	3	6.5	14	IP68	-40°C	+100°C	Yes
2100596	M16x 1.5	Nickel Plated Brass	10	5	6	20	IP68	-40°C	+100°C	Yes
2100598	M20x 1.5	Nickel Plated Brass	12	6	6	22	IP68	-40°C	+100°C	Yes
2100602	M25x 1.5	Nickel Plated Brass	16	9	7	30	IP68	-40°C	+100°C	Yes
2100606	M32x 1.5	Nickel Plated Brass	20	13	8	40	IP68	-40°C	+100°C	Yes
2100611	M40x 1.5	Nickel Plated Brass	26	20	8	50	IP68	-40°C	+100°C	Yes