

PRODUCT DATASHEET

ST8V-EM 7.6 W/830 600 mm EM

SubstiTUBE Value | Economic LED tubes for electromagnetic control gears



AREAS OF APPLICATION

- General illumination within ambient temperatures from -20...+45 °C
- Corridors, stairways, parking garages
- Cooling and storage rooms
- Domestic applications
- Industry
- Warehouses
- Supermarkets and department stores

PRODUCT BENEFITS

- Quick, simple and safe replacement without rewiring
- Energy savings of up to 65 % (compared to T8 fluorescent lamp on CCG)
- Instant-on light, therefore ideally suitable in combination with sensor technology
- Very high resistance to switching loads
- Also suitable for operation at low temperatures

PRODUCT FEATURES

- LED alternative to classic T8 fluorescent lamps in CCG luminaires
- Integrated ECG with high power factor
- Uniform illumination
- Lifetime: up to 30,000 h
- Wide beam angle: 220°
- Mercury-free and RoHS compliant
- Luminous efficacy: up to 105 lm/W



- Tube made of glass

TECHNICAL DATA

Electrical data

| | |
|------------------------|-------------|
| Nominal wattage | 7.60 W |
| Rated wattage | 7.60 W |
| Nominal voltage | 220...240 V |
| Operating frequency | 50...60 Hz |
| Nominal current | 0.037 A |
| Type of current | AC |
| Power factor λ | > 0.90 |

Photometrical data

| | |
|---|---------------------------|
| Light color (designation) | Warm White |
| Rated color temperature | 3000 K |
| Nominal luminous flux | 720 lm |
| Rated luminous flux | 720 lm |
| Color rendering index Ra | >80 |
| Lumen main.fact.at end of nom.life time | 0.70 |
| Standard deviation of color matching | ≤ 6 sdc _m |

Light technical data

| | |
|------------------------------------|----------|
| Starting time | < 0.5 s |
| Warm-up time (60 %) | < 0.50 s |
| Rated beam angle (half peak value) | 190.00 ° |

Dimensions & weight



| | |
|---|-----------|
| Length with base excl. base pins/connection | 590.00 mm |
| Tube diameter | 25.6 mm |
| Base diameter | 25.5 mm |

| | |
|-----------------------|----------|
| Product weight | 100.00 g |
| Overall length | 602.0 mm |

Temperatures & operating conditions

| | |
|----------------------------------|--------------|
| Ambient temperature range | -20...+45 °C |
|----------------------------------|--------------|

Lifespan

| | |
|-----------------------------------|---------|
| Lifespan | 30000 h |
| Nominal lamp life time | 30000 h |
| Rated lamp life time | 30000 h |
| Number of switching cycles | 200000 |

Additional product data

| | |
|------------------------------------|-----|
| Base (standard designation) | G13 |
| Mercury-free | Yes |

Capabilities

| | |
|-----------------|----|
| Dimmable | No |
|-----------------|----|

Certificates & standards

| | |
|--------------------------------|-------------|
| Type of protection | IP20 |
| Standards | CE/CB |
| Energy efficiency class | A+ |
| Energy consumption | 8 kWh/1000h |

Country specific categorizations

| | |
|------------------------|-------------------------|
| ILCOS | DR-7.6/830-G13-25.5/590 |
| Order reference | ST8V-0.6M 7,6W/ |

Logistical data

| | |
|-------------------------------------|-------------|
| Temperature range at storage | -20...80 °C |
|-------------------------------------|-------------|

EQUIPMENT / ACCESSORIES

- Suitable for operation with low-loss and conventional control gears

SAFETY ADVICE

Not suitable for operation with electronic control gear.
 Operation in outdoor applications in suitable damp-proof luminaires possible according to data sheet and installation instruction.

LOGISTICAL DATA

| Product code | Product description | Packaging unit (Pieces/Unit) | Dimensions (length x width x height) | Volume | Gross weight |
|---------------|--------------------------------|---------------------------------|---|----------------------|--------------|
| 4058075024618 | ST8V-EM 7.6 W/830 600 mm EM | Shipping carton box 10 | 668 mm x 154 mm x 65 mm | 6.69 dm ³ | 1345.00 g |

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For current information see

▶ www.ledvance.com/substitute

LEGAL ADVICE

When used to replace a T8 fluorescent lamp the total energy efficiency and light distribution depends on the design of the lighting system.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.