

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Triphenyl phosphate (TPP) (5% in M-46009-1) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1340060130-000
H6B-TGH-M30



TE Part # T1310060106-000
H6B-TS-M16



TE Part # T1340060121-000
H6B-TGH-PG21



TE Part # T1320060132-000
H6B-TG-M32



TE Part # T1340060132-000
H6B-TGH-M32



TE Part # T1310060111-000
H6B-TS-PG11



TE Part # T1340060120-000
H6B-TGH-M20



TE Part # T1340067134-000
H6B-TGH-NPT3/4



TE Part # T1330060113-000
H6B-TSH-PG13.5



TE Part # T1320060121-000
H6B-TG-PG21



TE Part # T1310060113-000
H6B-TS-PG13.5



TE Part # T1310060125-000
H6B-TS-M25



TE Part # T1320060116-000
H6B-TG-PG16



TE Part # T1320060120-000
H6B-TG-M20



TE Part # T1330060120-000
H6B-TSH-M20



TE Part # T1340065125-000
H6B-TGH-EMC-M25



TE Part # T1330060106-000
H6B-TSH-M16



TE Part # T1340060140-000
H6B-TGH-M40



TE Part # T1330060140-000
H6B-TSH-M40



TE Part # T1323060120-000
H6B-TG-M20

Customers Also Bought



Documents

Product Drawings

H6B-KDTPM

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_T1010061400-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1010061400-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1010061400-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[Heavy Duty Connectors](#)

English

[Product Specifications](#)

[Application Specification](#)

English