

Endress+Hauser Capacitance level switch FTW31-A1A3CA2A

Simple and safe point level switch for a wide range of applications in liquids. The rod probe offers multipoint detection for up to 5 switch points.



Picture for reference only. Product appearance may vary based on configuration

The Liquipoint FTW31 is a rod probe for point level detection in conductive liquids. With up to 5 rods, it offers numerous measuring possibilities such as overfill prevention, dry running protection, two-point control of pumps or multiple point detection. The device does not require calibration.

- Detect up to five point levels with one probe
- Two-point control and additional MAX and MIN detection

Configuration of FTW31-A1A3CA2A:

Approval:	A	Non-hazardous area
Process Connection:	1	Thread ISO228 G1-1/2, PPS
Sensing Point:	A3	3x rod, 316L
Probe Length:	C	1000mm L, 316L
Cable Entry:	A	Gland M20
Electronics; Output:	2	FEW52; PNP 10.8-45VDC
Additional Option:	A	Basic version

Alternative part number: FTW31-A1A3CA2A