



FAG

6048-M

Deep groove ball bearing

Deep groove ball bearing 60.-M, single row,
solid brass cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	M	Solid brass cage, rolling element guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S1	Rings dimensional stabilized up to 200°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	240 mm	Bore diameter
D	360 mm	Outside diameter
B	56 mm	Width
C _r	255,000 N	Basic dynamic load rating, radial
C _{0r}	315,000 N	Basic static load rating, radial
C _{ur}	11,700 N	Fatigue load limit, radial
n _G	3,100 1/min	Limiting speed
n _{gr}	2,450 1/min	Reference speed
≈m	20.5 kg	Weight



Mounting dimensions

d _{a min}	252.4 mm	Minimum diameter shaft shoulder
D _{a max}	347.6 mm	Maximum diameter of housing shoulder
r _{a max}	2.5 mm	Maximum fillet radius

Dimensions

r _{min}	3 mm	Minimum chamfer dimension
D ₁	321.85 mm	Shoulder diameter outer ring
d ₁	278.8 mm	Shoulder diameter inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

f ₀	15.8	Calculation factor
----------------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed
	Large bearing