

## CPG1500 0 ... 40 bar gauge G 1/2 B

### CPG1500 0 ... 40 bar gauge G 1/2 B

Item number: 48693260

Quantity: 1 pcs.

Order code: CPG1500-ST-Z-S-BG440-GDSZ-13-CZHZ-Z-ZZZZ Z W  
CERT-PR-DE1-AP03B1B-Z-C12-ZZ-Z 1

Overview: CPG1500 0 ... 40 bar gauge G 1/2 B  
Precision digital pressure gauge - Model CPG1500  
Specifications according to data sheet: CT 10.51  
Explosion protection: without  
Measuring range: 0 ... 40 bar gauge  
Process connection: G 1/2 B  
Wetted parts: stainless steel  
Accuracy: 0.1 % FS  
Type of certificate: Acceptance test certificate 3.1 in accordance with DIN EN 10204  
Communication: Bluetooth®  
Info Bluetooth®: Please bear in mind the relevant radio approvals in your country.  
incl. protective housing cap

#### Calibration of pressure measuring instruments

Type of certificate: Acceptance test certificate 3.1 in accordance with DIN EN 10204  
Type of device under test: Electrical measuring device with display (digital pressure gauge, pressure controller, etc.)  
Accuracy:  $\geq 0,1 \%$  ...  $\leq 0,6 \%$   
Numbers of measurement series: 2  
Number of measuring points per measurement series: 9  
Pressure type - pressure: Relative pressure (over- or underpressure)  
Calibration range - pressure:  $> 10 \text{ mbar}$  ...  $\leq 400 \text{ bar}$

Conformity assessment is carried out in accordance with IN00.60, unless otherwise specified by the orderer.

Documentation: Calibration (documentation of the values)

1. Language of certificate: DE
2. Language of certificate: GB

Further information about our services can be found in our Technical Information section at [www.wika.de](http://www.wika.de) → Download → Technical Information → Service.

Details: CPG1500 0 ... 40 bar gauge G 1/2 B  
Precision digital pressure gauge - Model CPG1500

Specifications according to data sheet: CT 10.51

Explosion protection: without

Measuring range: 0 ... 40 bar gauge

Process connection: G 1/2 B

Wetted parts: stainless steel

Accuracy: 0.1 % FS

Type of certificate: Acceptance test certificate 3.1 in accordance with DIN EN 10204

Communication: Bluetooth®

Info Bluetooth®: Please bear in mind the relevant radio approvals in your country.  
incl. protective housing cap

Calibration of pressure measuring instruments

Type of certificate: Acceptance test certificate 3.1 in accordance with DIN EN 10204

Type of device under test: Electrical measuring device with display (digital pressure gauge, pressure controller, etc.)

Accuracy:  $\geq 0,1 \%$  ...  $\leq 0,6 \%$

Numbers of measurement series: 2

Number of measuring points per measurement series: 9

Pressure type - pressure: Relative pressure (over- or underpressure)

Calibration range - pressure:  $> 10 \text{ mbar}$  ...  $\leq 400 \text{ bar}$

Conformity assessment is carried out in accordance with IN00.60, unless otherwise specified by the orderer.

Documentation: Calibration (documentation of the values)

1. Language of certificate: DE

2. Language of certificate: GB

Further information about our services can be found in our Technical Information section at [www.wika.de](http://www.wika.de) → Download → Technical Information → Service.