

TBN 10 G

Breaking torque wrench TBN KNICKER

0.4-200 Nm / pre-set

Code ETIM
7090770 EC002132

EAN UNSPSC
4002805760017 27-11-17-15

Country of origin eCl@ss
Germany 21-04-02-22

Customs tariff number
82041100



Article description

- Use:
- Controlled screw tightening in the range of 2 - 10 Nm
- Serial / production-line
- Extremely long-term work
- Features:
- Pre-set torque wrench - without scale
- With 9x12 mm Internal Square Drive
- For bi-directional tightening (the wrench only has to be turned by 180°!)
- Working accuracy: +/- 4 % tolerance of set torque
- Acc. to DIN EN ISO 6789, traceable to national standards
- Breaking of the handgrip by 20° when the pre-set torque value is achieved makes over-tightening unlikely
- Automatic resetting to the starting position
- Lightweight, but robust and corrosion-resistant construction design
- Very convenient non-slip rubber handgrip
- No. TBN 2 G: EPA (Electrostatic Protected Area) compliant, for use in electrostatically sensitive applications
- The pre-setting can be made at the factory or by the user on suitable torque testers • If fixed setting at the factory is desired is required, please state the Nm value when ordering (price on request)
- Scope of delivery:
- Torque wrench TBN Breaking Torque wrench
- Special adjusting key for changing the pre-set torque value
- Test certificate acc. to DIN EN ISO 6789
- Delivery in sturdy cardboard packaging

Article information

| | | | |
|-----------------------------|----------------------------|-------------------------|------------------------|
| Contents (Qty of pieces) | 1 | Torque (max.) [lbf·in] | 17,8 lbf·in |
| Net weight [kg] | 0,15 kg | Torque (min.) [lbf·in] | 89 lbf·in |
| Total length [mm] | 133 mm | Backup | Catch lock |
| Material | Tubular steel construction | Trigger mechanism | Long travel triggering |
| Drive type/drive | Rectangular cavity | Precision +/- | +/- 6 % |
| Torque (min.) [N·m] | 2 Nm | Direction of tightening | Left and right |
| Torque (max.) [N·m] | 10 Nm | Fixed setting | yes |
| Epa-/Esd-Model | yes | Test certificate | DIN EN ISO 6789-2:2017 |
| Drive connector rectangular | 9 x 12 mm | | |