

X20PS3310

1 General information

The supply module is equipped with a feed for the X2X Link as well as the internal I/O supply. The module has an integrated replaceable fuse for the I/O supply.

- Feed for X2X Link and internal I/O supply
- Electrical isolation of feed and X2X Link supply
- Redundancy of X2X Link supply possible by operating multiple supply modules simultaneously
- Fuse for I/O supply integrated in module

1.1 Other applicable documents

For additional and supplementary information, see the following documents.

Other applicable documents

Document name	Title
MAX20	X20 system user's manual
MAEMV	Installation / EMC guide

2 Order data


Order number	Short description	Figure
	Power supplies	
X20PS3310	X20 power supply module, for X2X Link and internal I/O power supply, integrated fine-wire fuse	
	Required accessories	
	Bus modules	
X20BM01	X20 power supply bus module, 24 VDC keyed, internal I/O power supply interrupted to the left	
X20BM05	X20 power supply bus module, with node number switch, 24 VDC keyed, internal I/O power supply interrupted to the left	
	Terminal blocks	
X20TB12	X20 terminal block, 12-pin, 24 VDC keyed	

Table 1: X20PS3310 - Order data

3 Technical description

3.1 Technical data

Order number	X20PS3310
Short description	
Power supply module	24 VDC supply module for I/O and bus
General information	
B&R ID code	0x2017
Status indicators	Overload, operating state, module status
Diagnostics	
Module run/error	Yes, using LED status indicator and software
Overload	Yes, using LED status indicator and software
Power consumption for X2X Link power supply ¹⁾	1.42 W
Power consumption ¹⁾	
Internal I/O	0.82 W
Additional power dissipation caused by actuators (resistive) [W]	-
Certifications	
CE	Yes
UKCA	Yes
ATEX	Zone 2, II 3G Ex nA nC IIA T5 Gc IP20, Ta (see X20 user's manual) FTZÜ 09 ATEX 0083X
UL	cULus E115267 Industrial control equipment
HazLoc	cCSAus 244665 Process control equipment for hazardous locations Class I, Division 2, Groups ABCD, T5
EAC	Yes
KC	Yes
X2X Link power supply input	
Input voltage	24 VDC -15% / +20%
Input current	Max. 0.7 A
Fuse	Integrated, cannot be replaced
Reverse polarity protection	Yes
X2X Link power supply output	
Nominal output power	7 W
Parallel connection	Yes ²⁾
Redundant operation	Yes
Overload characteristics	Short-circuit proof, temporary overload
Input I/O power supply	
Input voltage	24 VDC -15% / +20%
Input current	Max. 6 A
Fuse	Integrated 6.3 A, slow-blow, can be replaced
Reverse polarity protection	No
Output I/O power supply	
Nominal output voltage	24 VDC
Behavior on short circuit	Integrated fuse
Permissible contact load	6 A
Electrical properties	
Electrical isolation	X2X Link supply isolated from X2X Link power supply I/O supply not isolated from I/O power supply
Operating conditions	
Mounting orientation	
Horizontal	Yes
Vertical	Yes
Installation elevation above sea level	
0 to 2000 m	No limitation
>2000 m	Reduction of ambient temperature by 0.5°C per 100 m
Degree of protection per EN 60529	IP20
Ambient conditions	
Temperature	
Operation	
Horizontal mounting orientation	-25 to 60°C
Vertical mounting orientation	-25 to 50°C
Derating	See section "Derating".
Storage	-40 to 85°C
Transport	-40 to 85°C

Table 2: X20PS3310 - Technical data


Order number	X20PS3310
Relative humidity	
Operation	5 to 95%, non-condensing
Storage	5 to 95%, non-condensing
Transport	5 to 95%, non-condensing
Mechanical properties	
Note	Order 1x terminal block X20TB12 separately. Order 1x power supply bus module X20BM01 separately
Pitch	12.5 ^{+0.2} mm

Table 2: X20PS3310 - Technical data


- 1) The specified values are maximum values. For examples of the exact calculation, see section "Mechanical and electrical configuration" in the X20 system user's manual.
- 2) In parallel operation, it is only permitted to expect 75% of the nominal power. It is important to make sure that all power supply units operated in parallel are switched on and off at the same time.

3.2 LED status indicators

For a description of the various operating modes, see section "Additional information - Diagnostic LEDs" in the X20 system user's manual.


Figure	LED	Color	Status	Description
	r	Green	Off	No power to module
			Single flash	RESET mode
			Blinking	PREOPERATIONAL mode
			On	RUN mode
	e	Red	Off	No power to module or everything OK
			Double flash	LED indicates one of the following states: <ul style="list-style-type: none"> • The X2X Link supply for the power supply is overloaded • I/O supply too low • Input voltage for X2X Link supply too low
	e + r	Red on / Green single flash		Invalid firmware
	l	Red	Off	The X2X Link supply is within the valid limits
			On	The X2X Link supply for the power supply is overloaded

3.3 Pinout




3.4 Connection examples

With 2 separate supplies



- 1) Supply for the X2X Link power supply
- 2) Supply for the I/O power supply


With a supply and jumper



- 1) Supply for the I/O power supply
- 2) Jumper

3.5 Derating


The nominal output power for the power supply is 7 W. Depending on the mounting orientation, derating must be taken into account.



3.6 Replacing the built-in fuse

The module is equipped with a 6.3 A built-in fuse. Proceed as follows to replace a defective fuse:

- 1) Remove the fuse cover with the fuse on the right side of the module using a screwdriver.
- 2) Slide the cylindrical fuse out of the fuse holder and slide the new fuse in.



4 Register description

4.1 General data points

In addition to the registers described in the register description, the module has additional general data points. These are not module-specific but contain general information such as serial number and hardware variant.

General data points are described in section "Additional information - General data points" in the X20 system user's manual.

4.2 Function model 0 - Standard

Register	Fixed offset	Name	Data type	Read		Write	
				Cyclic	Acyclic	Cyclic	Acyclic
0	1	Status of the module	USINT	•			
		StatusInput01	Bit 0				
		StatusInput02	Bit 2				
2	2	SupplyCurrent	USINT	•			
4	3	SupplyVoltage	USINT	•			

Fixed modules require their data points to be in a specific order in the X2X frame. Cyclic access occurs according to a predefined offset, not based on the register address.

Acyclic access continues to be based on the register numbers.

4.3 Function model 254 - Bus controller

Register	Offset ¹⁾	Name	Data type	Read		Write	
				Cyclic	Acyclic	Cyclic	Acyclic
0	0	Status of the module	UINT	•			
		StatusInput01	Bit 0				
		StatusInput02	Bit 2				
2	2	SupplyCurrent	UINT	•			
4	4	SupplyVoltage	UINT	•			

1) The offset specifies the position of the register within the CAN object.

4.3.1 Using the module on the bus controller

Function model 254 "Bus controller" is used by default only by non-configurable bus controllers. All other bus controllers can use other registers and functions depending on the fieldbus used.

For detailed information, see section "Additional information - Using I/O modules on the bus controller" in the X20 user's manual (version 3.50 or later).

4.3.2 CAN I/O bus controller

The module occupies 1 analog logical slot on CAN I/O.

4.4 Status of the module

Name:

Module status

The following voltage and current states of the module are monitored in this register:

Bus power supply current:	Bus power supply current >2.3 A is displayed as a warning.
Bus supply voltage:	Bus supply voltage <4.7 V is displayed as a warning.
24 VDC I/O supply voltage:	I/O supply voltage <20.4 V is displayed as a warning.

Function model	Data type	Values
0 - Standard	USINT	See the bit structure.
254 - Bus controller	UINT	See the bit structure.

Bit structure:

Bit	Description	Value	Information
0	StatusInput01	0	No error
		1	Warning in the event of overcurrent (>2.3 A) or undervoltage (<4.7 V)
1	Reserved	0	
2	StatusInput02	0	I/O power supply above the warning limit of 20.4 V
		1	I/O power supply below the warning limit of 20.4 V
3 - x	Reserved	0	

4.5 Bus power supply current

Name:

SupplyCurrent

This register displays the bus power supply current measured at a resolution of 0.1 A.

Function model	Data type
0 - Standard	USINT
254 - Bus controller	UINT

4.6 Bus supply voltage

Name:

SupplyVoltage

This register indicates the bus supply voltage measured at a resolution of 0.1 V.

Information:

The nominal bus supply voltage is 5 V and should not fall below 4.7 V.

Function model	Data type
0 - Standard	USINT
254 - Bus controller	UINT

4.7 Minimum cycle time

The minimum cycle time specifies how far the bus cycle can be reduced without communication errors occurring. It is important to note that very fast cycles reduce the idle time available for handling monitoring, diagnostics and acyclic commands.

Minimum cycle time
100 µs

4.8 Minimum I/O update time

The minimum I/O update time specifies how far the bus cycle can be reduced so that an I/O update is performed in each cycle.

Minimum I/O update time
2 ms